ABB BALDOR RELIANCE

Customer information packet

CSWDM3541

.75HP, 3450RPM, 3PH, 60HZ, 56C, 3518M, TENV, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/3/2026 2:29:52 AM

Specifications

Enclosure	TENV
Frame	56C
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
	208.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.300 A @ 208.0 V
	2.200 A @ 230.0 V
	1.100 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	80.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	Q
Type	AC
Mech. spec.	35S630
Base	
Status	PRD/A
Elec. spec.	35WGT097
Layout	35LYS630
Eff. date	09-11-2023
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	02-19-2010

Heater Indicator	No Heater
High Voltage Full Load Amps	1.1 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3518M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	11.06 IN
Power Factor	80
Product Family	Wash Down Paint Free
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1496L									
CAT.NO.	CSWDM3541								
SPEC.	35S630T097G1								
HP	.75								
VOLTS	208-230/460								
AMP	2.3-2.2/1.1								
RPM	3450								
FRAME	56C		**HZ**	60			**PH**	3	
SER.F.	1.25	**CODE**	N	**DES**	B	**CLASS**		F	
NEMA-NOM-EFF	80	**PF**	80						
RATING	40C AMB-CONT								
CC									
DE	6205		**ODE**	6203					
ENCL	TENV	**SN**							
	SFA 2.8-2.6/1.3								

AC Induction Motor Performance Data
Record # 36638
Typical performance - not guaranteed values

Winding: 35WGT097-R002	**Type:** 3518M	**Enclosure:** TENV

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			.75	**Full Load Torque**	1.1 LB-FT
Volts			208-230/460	**Start Configuration**	direct on line
Full Load Amps			2.3-2.2/1.1	**Breakdown Torque**	7.6 LB-FT
R.P.M.			3450	**Pull-up Torque**	4.1 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	5.6 LB-FT
NEMA Design Code	B	**KVA Code**	N	**Starting Current**	11.7 A
Service Factor (S.F.)			1.25	**No-load Current**	0.61 A
NEMA Nom. Eff.	80	**Power Factor**	80	**Line-line Res. @ 25ºC**	15.3 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	65°C
S.F. Amps			2.8-2.6/1.3	**Temp. Rise @ S.F. Load**	76°C
				Locked-rotor Power Factor	58
				Rotor inertia	0.0498 LB-FT2

Load Characteristics 460 V, 60 Hz, 0.75 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	42	61	72	78	81	82	81
Efficiency	62.6	74.5	78.8	80.4	81	80.1	81
Speed	3571	3536	3509	3477	3444	3406	3444
Line amperes	0.66	0.76	0.91	1.09	1.29	1.52	1.29


ABB Motors and Mechanical Inc.


WINDING # 35WGT097

0.75 HP 3 PH 60 HZ 3450 RPM 460 V 3518M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=7.6 PU=4.1 LR=5.6 LRA=11.7




35LYS630
510-520 = 11.06
521-528 = 12.06
529-535 = 12.93
536-546 = 14.31
2.59
2.06
1.88
.13
(4) .125" NPT HOLES
3 W/PLUGS
@ 3, 9, & 1:00
.19 KEY
1.38 LONG
NAMEPLATE
Ø6.49
Ø4.500
4.497
Ø.6250
.6245
4 SLOTS
.34 WIDE
3.00
2.75
.75
4.50
JM CLIPPER
SEAL
(4) .125" NPT HOLES
3 W/PLUGS
@ 3, 9, & 11:00
Ø6.61
5.65
45°
45°
7.01
3.50
3.44
4 HOLES
.38-16 TAP ON
Ø5.88 B.C.
LEAD HOLE
.50 N.P.T.
2.44
2.44
4.56
3.25
6.50
INSTALL DUBO-LOK
WASHER UNDER RET.
RING SCREW HEAD
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOADING OF SWD DWG FOR 2D TO 3D CONVERSION - PKG12
REV: G
VERSION: 07
REVISED: 04:59:32 12/11/2018
TDR: 000001093440
MODEL NO. 35LYS630
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
STD HORZ 56C TENV 35M WD2 (PAINT FREE)
SH 1 of 1
35LYS630

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS