



Customer information packet

CWDL3504

.5HP, 1740RPM, 1PH, 60HZ, 56C, 3520L, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ 230.0 V @ 60 HZ
XP Class and Group	None
XP Division	Not Applicable
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.450 A @ 208.0 V 3.500 A @ 230.0 V 7.000 A @ 115.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	66.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	3.5 a

Part detail

Revision	-
Type	AC
Mech. spec.	35J306
Base	
Status	PRD/A
Elec. spec.	35WGG470
Layout	35LYJ306
Eff. date	10-10-2022
CD Diagram	CD0001
Poles	04
Leads	6#18
Proprietary	False
Created date	08-01-2022

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3520L
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.23 IN
Power Factor	70
Product Family	Wash Down
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1740 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1496L									
CAT.NO.	CWDL3504								
SPEC.	35J306G470								
HP	.5								
VOLTS	115/230								
AMP	7/3.5								
RPM	1740								
FRAME	56C		HZ	60		PH	1		
SER.F.	1.25	CODE	L	DES	N	CLASS	F		
NEMA-NOM-EFF	66	PF	70						
RATING	40C AMB-CONT								
CC			USABLE AT 208V	3.45					
DE	6205		ODE	6203					
ENCL	TEFC	SN							
	SFA 8.2/4.1								

AC Induction Motor Performance Data

Record # 94791

Typical performance - not guaranteed values

Winding: 35WGG470-R001		Type: 3520L		Enclosure: TEFC			
Nameplate Data			115 V, 60 Hz: Low Voltage Connection				
Rated Output (HP)	.5	Full Load Torque	1.511 LB-FT				
Volts	115/230	Start Configuration	direct on line				
Full Load Amps	7/3.5	Breakdown Torque	4.22 LB-FT				
R.P.M.	1740	Pull-up Torque	3.95 LB-FT				
Hz	60 Phase	1	Locked-rotor Torque	6.21 LB-FT			
NEMA Design Code	N	KVA Code	L	Starting Current	43.3 A		
Service Factor (S.F.)	1.25		No-load Current	5.29 A			
NEMA Nom. Eff.	66	Power Factor	70	Line-line Res. @ 25°C	1.3669 Ω A Ph		
					2.3003 Ω B Ph		
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load	62°C			
S.F. Amps	8/4		Temp. Rise @ S.F. Load	78°C			
			Locked-rotor Power Factor	98.3			

Load Characteristics 115 V, 60 Hz, 0.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	35	49	61	70	77	82	77
Efficiency	42.8	57.5	63.6	65.7	65.6	63.7	65.6
Speed	1781.1	1768.1	1752.9	1735.9	1715.7	1690.5	1716
Line amperes	5.38	5.7	6.26	7.01	8.01	9.26	8.01


ABB Motors and Mechanical Inc.

WINDING # 35WGG470


0.5 HP 1 PH 60 HZ 1740 RPM 115 V 3520L

Typical performance - not guaranteed values.


TORQUES (LB-FT): PO=4.22 PU=3.95 LR=6.21 LRA=43.3



3/28/2023 ACPERF, record # 94791



CD0001



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	-
LOW OPP	1,3,5	2,4,8	-

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0001

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:16	TDR: 0178636
100000		FILE: AAA00007405	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

TYPE L, DV, REV, 6 LEADS