

**BALDOR • RELIANCE**

---

# Customer information packet

## CXM050342

0.33//0.25HP, 1780//1480RPM, 3PH, 60//50HZ

Class - CLI GP D; CLII GP F,G

Division - Division I

## Specifications

Enclosure	XPFC
Frame	56C
Frame Material	Steel
Frequency	50.00 Hz 60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	.250 HP @ 50 HZ .330 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 190.0 V @ 50 HZ 460.0 V @ 60 HZ 380.0 V @ 50 HZ
Agency Approvals	UL CSA EEV
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	1.700 A @ 230.0 V 1.500 A @ 190.0 V .850 A @ 460.0 V .750 A @ 380.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT

## Part detail

Revision	C
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	35WGG155
Layout	35LYE2098
Eff. date	03-08-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	10-28-2021

Efficiency @ 100% Load	80.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	0.8 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	S
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3512M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.30 IN
Power Factor	49
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1780 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

**Nameplate**

NP0887XPSL									
<b>NO.</b>		<b>CC</b>							
<b>S/N</b>		<b>TEMP CODE</b>	T3C						
<b>SPEC.</b>	35-0000-1380	<b>INV.TYPE</b>	PWM						
<b>CAT.NO.</b>	CXM050342	<b>C HP FR</b>	60	<b>C HP TO</b>	90				
<b>HP</b>	.33//0.25	<b>CT HZ FROM</b>	6	<b>CT HZ TO</b>	60				
<b>VOLTS</b>	230/460//190/380	<b>VT HZ FROM</b>	6	<b>VT HZ TO</b>	60				
<b>AMPS</b>	1.7/0.85//1.5/0.75	<b>MAG CUR</b>	1.6/0.8						
<b>RPM</b>	1780//1480	<b>MX RPM</b>	2700						
<b>HZ</b>	60//50	<b>PH</b>	3	<b>CL</b>	F	<b>NOM.EFF.</b>	80		
<b>SER.F.</b>	1.15	<b>DES</b>	B	<b>SL HZ</b>	0.7	<b>WK2</b>	0.087		
<b>FRAME</b>	56C	<b>RATING</b>	40C AMB-CONT						
	NEMA MG-1 PART 5, IP54								
	1.15 SF ON SINE WAVE			SFA 1.8/0.9					

**AC Induction Motor Performance Data**

Record # 90037

Typical performance - not guaranteed values

Winding: 35WGG155-R048		Type: 3512M	Enclosure: TEFC
<b>Nameplate Data</b>			<b>460 V, 60 Hz: High Voltage Connection</b>
Rated Output (HP)	.33//.25	Full Load Torque	0.977 LB-FT
Volts	230/460//190/380	Start Configuration	direct on line
Full Load Amps	1.7/.85//1.5/.75	Breakdown Torque	6.28 LB-FT
R.P.M.	1780//1480	Pull-up Torque	3.26 LB-FT
Hz	60//50 Phase	Locked-rotor Torque	4.04 LB-FT
NEMA Design Code	B KVA Code	Starting Current	6.71 A
Service Factor (S.F.)	1.15	No-load Current	0.792 A
NEMA Nom. Eff.	75.5 Power Factor	Line-line Res. @ 25°C	43.2 Ω
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	17°C
S.F. Amps	1.8/.9//1.56/.78	Temp. Rise @ S.F. Load	19°C
		Locked-rotor Power Factor	70.7767
		Rotor inertia	0.0866 lb-ft <sup>2</sup>

**Load Characteristics 460 V, 60 Hz, 0.33 HP**

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	22	31	41	49	57	63	54
Efficiency	47.4	63.1	70.8	75.1	77.6	79.1	76.6
Speed	1794	1789	1785	1780	1774	1769	1776
Line amperes	0.786	0.791	0.814	0.839	0.878	0.933	0.862


ABB Motors and Mechanical Inc.

WINDING # 35WGG155

0.33 HP 3 PH 60 HZ 1780 RPM 460 V 3512M

Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=6.28 PU=3.26 LR=4.04 LRA=6.71



12/4/2024 ACPERF, record # 90037

**AC Induction Motor Performance Data**

Record # 90038

Typical performance - not guaranteed values

Winding: 35WGG155-R048		Type: 3512M	Enclosure: TEFC			
<b>Nameplate Data</b>			<b>380 V, 50 Hz: High Voltage Connection</b>			
Rated Output (HP)	.33//.25		Full Load Torque	0.892 LB-FT		
Volts	230/460//190/380		Start Configuration	direct on line		
Full Load Amps	1.7/.85//1.5/.75		Breakdown Torque	5.5 LB-FT		
R.P.M.	1780//1480		Pull-up Torque	2.98 LB-FT		
Hz	60//50	Phase	3	Locked-rotor Torque	3.69 LB-FT	
NEMA Design Code	B		KVA Code	S	Starting Current	6.08 A
Service Factor (S.F.)	1.15		No-load Current	0.775 A		
NEMA Nom. Eff.	75.5	Power Factor	49		Line-line Res. @ 25°C	43.2 Ω
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load	17°C		
S.F. Amps	1.8/.9//1.56/.78		Temp. Rise @ S.F. Load	18°C		
			Locked-rotor Power Factor	76.0359		
			Rotor inertia	0.0866 lb-ft <sup>2</sup>		

**Load Characteristics 380 V, 50 Hz, 0.25 HP**

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	23	32	40	49	56	63	53
Efficiency	42.4	58.8	67.4	72.1	75	76.1	73.8
Speed	1494	1490	1486	1481	1476	1471	1478
Line amperes	0.767	0.77	0.789	0.81	0.842	0.891	0.829


ABB Motors and Mechanical Inc.

WINDING # 35WGG155

0.25 HP 3 PH 50 HZ 1481 RPM 380 V 3512M


Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=5.5 PU=2.98 LR=3.69 LRA=6.08



12/4/2024 ACPERF, record # 90038





CD0005




LOW VOLTAGE  
(2Y)



LINE

HIGH VOLTAGE  
(1Y)



LINE

**NOTES:**

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

**BALDOR ELECTRIC Co.**

3PH, DV, 9 LEADS

CD0005