

ABB BALDOR RELIANCE III

Customer information packet

CXM18322T

3//2HP, 3450//2890RPM, 3PH, 60//50HZ, 182TC

Class - CLI GP D; CLII GP F,G

Division - Division I

Specifications

Enclosure	XPFC
Frame	182TC
Frame Material	Steel
Frequency	50.00 Hz 60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 50 HZ 3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	380.0 V @ 50 HZ 230.0 V @ 60 HZ 190.0 V @ 50 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA UR CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	7.400 A @ 230.0 V 6.000 A @ 190.0 V 3.700 A @ 460.0 V 3.000 A @ 380.0 V
Design Code	A
Drip Cover	No Drip Cover

Part Detail

Revision	A
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	36WGS041
Layout	36LYK919
Eff. date	10-04-2022
CD Diagram	CD0005
Poles	02
Leads	9#16
Proprietary	False
Created date	03-16-2021

Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	3.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3622M
Mounting Arrangement	F1
Number of Poles	2
Power Factor	91
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP0887XPSLEV													
NO.							CC	010A					
S/N							TEMP CODE		T3C				
SPEC.	36-0000-0483						INV.TYPE		PWM				
CAT.NO.	CXM18322T						C HP FR		60	C HP TO		90	
HP	3//2						CT HZ FROM		6	CT HZ TO		60	
VOLTS	230/460//190/380						VT HZ FROM		6	VT HZ TO		60	
AMPS	7.4/3.7//6/3				MAG CUR		2.4/1.2						
RPM	3450//2890				MX RPM		5400						
HZ	60//50	PH	3	CL	F	NOM.EFF.		86.5					
SER.F.	1.00	DES	A	SL HZ		2.5	WK2	0.1					
FRAME	182TC	RATING		40C AMB-CONT									
	NEMA MG-1 PART 5, IP54												
	1.15 SF ON SINE WAVE												

AC Induction Motor Performance Data

Record # 73670

Typical performance - not guaranteed values

Winding: 36WGS041-R041		Type: 3622M	Enclosure: XPFC
Nameplate Data		460 V, 60 Hz: High Voltage Connection	
Rated Output (HP)	3//2	Full Load Torque	4.7 LB-FT
Volts	230/460//190/380	Start Configuration	direct on line
Full Load Amps	7.4/3.7//6/3	Breakdown Torque	19.7 LB-FT
R.P.M.	3450//2890	Pull-up Torque	12 LB-FT
Hz	60//50 Phase	Locked-rotor Torque	14.1 LB-FT
NEMA Design Code	A KVA Code	Starting Current	33.3 A
Service Factor (S.F.)	1	No-load Current	1.17 A
NEMA Nom. Eff.	86.5 Power Factor	Line-line Res. @ 25°C	4.71 Ω
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	52°C
		Locked-rotor Power Factor	48.4
		Rotor inertia	0.0984 LB-FT2

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	66	82	88	91	92	93
Efficiency	80.3	86	87.3	86.9	86	84.5
Speed	3565	3535	3504	3472	3434	3394
Line amperes	1.56	2.17	2.93	3.67	4.57	5.5


ABB Motors and Mechanical Inc.


WINDING # 36WGS041

Typical performance - not guaranteed values.


3 HP 3 PH 60 HZ 3472 RPM 460 V 3622M

TORQUES (LB-FT): PO=19.7 PU=12 LR=14.1 LRA=33.3






CD0005




LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS

REV. LTR: E

BY: JLP

REVISED: 01/19/99 10:15

TDR: 0171435

900000

FILE: AAA00005140

MDL: -

MTL: -

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005