

**BALDOR • RELIANCE**

---

# Customer information packet

## CXM21122T

10//7.5HP, 3510//2915RPM, 3PH, 60//50HZ, 215

Class - CLI GP D; CLII GP F,G

Division - Division I

## Specifications

Enclosure	XPFC
Frame	215TC
Frame Material	Steel
Frequency	50.00 Hz 60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ 7.500 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	380.0 V @ 50 HZ 230.0 V @ 60 HZ 190.0 V @ 50 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA UR CSA EEV
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	22.400 A @ 230.0 V 20.800 A @ 190.0 V 11.200 A @ 460.0 V 10.400 A @ 380.0 V
Design Code	B
Drip Cover	No Drip Cover

## Part detail

Revision	F
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	37WGS627
Layout	37LYL772
Eff. date	07-02-2024
CD Diagram	CD0005
Poles	02
Leads	9#14
Proprietary	False
Created date	04-23-2021

Duty Rating	CONT
Efficiency @ 100% Load	90.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	10.4 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5200 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3750M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	21.81 IN
Power Factor	90
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3510 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

---

**Nameplate**

NP0887XPSLEV										
<b>NO.</b>		<b>CC</b>	010A							
<b>S/N</b>		<b>TEMP CODE</b>	T3C							
<b>SPEC.</b>	37-0000-0380		<b>INV.TYPE</b>	PWM						
<b>CAT.NO.</b>	CXM21122T		<b>C HP FR</b>	60	<b>C HP TO</b>	90				
<b>HP</b>	10//7.5		<b>CT HZ FROM</b>	6	<b>CT HZ TO</b>	60				
<b>VOLTS</b>	230/460//190/380		<b>VT HZ FROM</b>	6	<b>VT HZ TO</b>	60				
<b>AMPS</b>	22.4/11.2//20.8/10.4		<b>MAG CUR</b>	1.71/3.42						
<b>RPM</b>	3510//2915		<b>MX RPM</b>	5200						
<b>HZ</b>	60//50	<b>PH</b>	3	<b>CL</b>	F	<b>NOM.EFF.</b>	90.2			
<b>SER.F.</b>	1.15	<b>DES</b>	B	<b>SL HZ</b>	1.5	<b>WK2</b>	0.456			
<b>FRAME</b>	215TC	<b>RATING</b>	40C AMB-CONT							
	NEMA MG-1 PART 5, IP54									
	1.15 SF ON SINE WAVE									

**AC Induction Motor Performance Data**

Record # 87974

Typical performance - not guaranteed values

<b>Winding: 37WGS627-R002</b>		<b>Type: 3750M</b>		<b>Enclosure: TEFC</b>	
<b>Nameplate Data</b>			<b>460 V, 60 Hz: High Voltage Connection</b>		
<b>Rated Output (HP)</b>	10//7.5		<b>Full Load Torque</b>	14.93 LB-FT	
<b>Volts</b>	230/460//190/380		<b>Start Configuration</b>	direct on line	
<b>Full Load Amps</b>	22.4/11.2//20.8/10.4		<b>Breakdown Torque</b>	54 LB-FT	
<b>R.P.M.</b>	3510		<b>Pull-up Torque</b>	25.7 LB-FT	
<b>Hz</b>	60//50	<b>Phase</b>	3	<b>Locked-rotor Torque</b>	29.9 LB-FT
<b>NEMA Design Code</b>	<b>B KVA Code</b>		H	<b>Starting Current</b>	87.3 A
<b>Service Factor (S.F.)</b>			1	<b>No-load Current</b>	3.29 A
<b>NEMA Nom. Eff.</b>	90.2	<b>Power Factor</b>	90	<b>Line-line Res. @ 25°C</b>	0.73857 Ω
<b>Rating - Duty</b>	40C AMB-CONT			<b>Temp. Rise @ Rated Load</b>	52°C
				<b>Locked-rotor Power Factor</b>	29.7

**Load Characteristics 460 V, 60 Hz, 10 HP**

<b>% of Rated Load</b>	<b>25</b>	<b>50</b>	<b>75</b>	<b>100</b>	<b>125</b>	<b>150</b>
<b>Power Factor</b>	61	81	88	90	91	91
<b>Efficiency</b>	89	92.4	92.8	92.3	91.3	90.1
<b>Speed</b>	3578.8	3557.6	3534.8	3510.8	3483.4	3454.5
<b>Line amperes</b>	4.33	6.25	8.6	11.2	14.1	17.1


ABB Motors and Mechanical Inc.

WINDING # 37WGS627


Typical performance - not guaranteed values.

10 HP 3 PH 60 HZ 3510 RPM 460 V 3750M

TORQUES (LB-FT): PO=54 PU=25.7 LR=29.9 LRA=87.3



1/18/2025 ACPERF, record # 87974






CD0005



LOW VOLTAGE  
(2Y)



LINE

HIGH VOLTAGE  
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

**BALDOR ELECTRIC Co.**

3PH, DV, 9 LEADS