

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION





617436-590

ENCLOSURE: TOTALLY ENCLOSED

MOUNTING: FOOT, F-1

FRAME E365TSC
INCLUDES E364TSC FRAME FOOT HOLE
STEEL C/BOX

COOLING: FAN COOLED



WEIGHT = 950 LBS ±15% DEPENDING ON RATING.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF
STANDARD SHAFT EXTENSION IS .003 T.I.R.
FACE AND ECCENTRICITY RUNOUT=.007 T.I.R. MAX.

DIMENSIONS ARE IN INCHES.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: NEW	VERSION: 00	REVISED: 02:56:16 09/28/2020	TDR: 000001148970
MODEL NO. 617436-590			
BY: RAGHZT			

BALDOR

E365TSC TEFC F-1 FT - STEEL C/BOX