

ABB BALDOR RELIANCE III

Customer information packet

D1803R

3HP, 1750RPM, DC, 189ATY, DPG,

Specifications

Armature Voltage	180 V
Base Speed	1750 rpm
Enclosure	DP
Frame	DC0189ATY
Output Power	3.000 HP
Agency Approvals	CCSA US
Ambient Temperature	40 °C
Armature Current	14.8 a
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Field Winding Type	STR. SHUNT
Frame Prefix	DC
Heater Indicator	No Heater
Insulation Class	F
Lifting Lugs	Standard Lifting Lugs
Motor Standards	NEMA
Mounting Arrangement	F3
Overall Length	21.19 IN
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Slinger Indicator	No Slinger
Thermal Device - Bearing	None

Part Detail

Revision	-
Type	DC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	G4605A
Layout	609980-503
Eff. date	01-06-2020
CD Diagram	406770-007
Poles	00
Leads	
Proprietary	False
Created date	12-27-2019

Nameplate

000613006HP									
CAT.NO.			SPEC NO.	T18S1118					
FR	DC0189ATY	HP	3			DUTY	CONT		
ENCL.	DP	RPM	1750			S.F.	1.0		
ENCL MOD			VOLTS	180		INSUL		F	
MAX SAFE SPEED	04500	AMPS	14.80		AMB.		40		
FIELD DATA		SER.NO.							
WINDING	STR. SHUNT		POWER CODE		2/2-230-60-0				
VOLTS	200		D.E. BRG.		30BC02JPP30A				
MAX AMPS @ 25 C	1.90/.95		O.D.E. BRG.		30BC02JPG30A				
HOT AMPS	.73		MIN. AMB.		0		TYPE		TR
BRUSH:419904050A									
SPLASHPROOF									

ABB BALDOR RELIANCE III

CUSTOMER INFORMATION
DC189AT

MOTOR RATING
3.00HP

D1803R

BASE SPEED
1750

WINDING TYPE
STRAIGHT SHUNT

S.F.
1.0

ENCL.
DPG

AMB⁰C/INSUL
40/F

DUTY
CONT

POWER CODE/FORM FACTOR
2/2 230-60-0

TYPE
TR

WK²(LB-FT²)
.6247

COOLING AIR(CFM/IN H₂O)
-/-

θ (sec)
.394

R (hot)
.120

T_E
.00769

T_M
.0474


BASIC RPM
1950

MAX CONT RPM
2300

WINDER RPM
-

MAX. SAFE
4500

WINDING	VOLTS	RESISTANCE		CURRENT		INDUCTANCE	TURNS PER COIL
		25 ⁰ C	HOT	25 ⁰ C	HOT		
ARM CIRCUIT	180	.875	1.17	-	14.8	10.0 mH	-
SERIES S1-S2	-	-	-	-	-	-	-
SHUNT F1-F2	200	211	268	.946	.745	36.3 H	2000



REMARKS: TYPICAL DATA SPEED REGULATOR REQUIRED FOR STABILITY
CURVES VALID FOR NAMEPLATE SPEED RANGE ONLY



DR. BY J. MARTIN
CK. BY J. MARTIN
APP. BY T. EVON
DATE 7/11/88

D-C
APPLICATION
DATA

SG4605A

ISSUE DATE 7/11/88

REL S.O.	FRAME	RATING	RPM	ARM. VOLTS	ARM. AMPS
	DC189AT	3.00HP	1750	180	14.8
WINDING TYPE		S.F.	ENCL.	AMB °C/INSUL	DUTY
STRAIGHT SHUNT		1.0	DPG	40/F	CONT
POWER CODE	TYPE	WK ² (LB-FT ²)	HOT ARM.CIR.RES.	FLD. AMPS@25 °C	HOT FIELD RES
2/2 230-60-0	TR	.6247	1.17	.946	268
ARM. CIR. IND. (mh)	FIELD IND. (H)	COOLING AIR(CFM/IN H ² 0)		TURNS PER COIL SHUNT/SERIES	TEST DATE
10.0	36.3	-/-		2000/.00000	-
LOAD PERFORMANCE					
LOAD	AMPERES	TORQUE IN LB.-FT.	OUTPUT IN HP	RPM	% EFFICIENCY
NO LOAD	.60	0	0	1881	0
1/4	3.7	2.06	.722	1844	62.9
2/4	7.4	4.47	1.54	1810	72.5
3/4	11	6.81	2.31	1783	74.4
4/4	15	8.99	3.03	1770	74.1
O.L.	22	12.9	4.32	1763	71.7
RPM VS. FIELD AMPS					
FIELD AMPS	RPM N.L.	RPM F.L.	Eg N.L. @ BASE SPEED	Eg F.L. @ BASE SPEED	
.745	1881	1770	166	158	
.678	1932	1856	162	151	
.610	2002	1965	157	143	
.543	2114	2107	148	133	
.476	2282	2300	138	122	
MAXIMUM SAFE SPEED = 4500 RPM SPEED REGULATOR REQUIRED FOR STABILITY REMARKS: TYPICAL DATA					
		DR. BY J. MARTIN CK. BY J. MARTIN APP. BY T. EVON DATE 7/11/88		D-C MOTOR PERFORMANCE DATA DG4605A ISSUE DATE 7/11/88	

HP/KW 3.00HP

ENCL. DPG

WK2(LB-FT²) .6247

FLD.AMPS@25 °C .946

RPM 1750

AMB °C INSL. 40/F

HOT ARM. CIR. RES. 1.17

FIELD IND (H) 36.3

ARM. VOLTS 180

ARM. AMPS 14.8

ARM. CIRCUIT IND(mh) 10.0

CFM/IN. H₂O -/-

WDG. TYPE STRAIGHT SHUNT


FIELD VOLTS 200

HOT FIELD RES. 268

TEST S.O. -

POWER CODE 2/2 230-60-0

TEST DATE -



REMARKS: TYPICAL DATA SPEED REGULATOR REQUIRED FOR STABILITY



DR. BY J. MARTIN
CK. BY J. MARTIN
APP. BY T. EVON
DATE 7/11/88


**D-C
PERFORMANCE
CURVES**

PG4605A

ISSUE DATE 7/11/88

609980-503

INDUSTRIAL DIRECT CURRENT MOTORS AND GENERATORS - RPM III
ENCLOSURE: DRIP-PROOF FULLY-GUARDED MOUNTING: FOOT, "C" FACE COOLING: SELF-VENTILATED ACCESSORIES: PROVISIONS FOR
SPLASHPROOF, TOTALLY ENCLOSED METHOD OF DRIVE: COUPLED OR BELTED NON-VENTILATED TACHOMETER MOUNTING
ONLY WHEN SPECIFIED
DC180ATY-DC180ATCZ



DIMENSIONS ARE IN INCHES

FRAME	FLANGE	A	DC1	E	G	H	J	K	FK	BK	D	P	T	BA	BB(7)	BD	BF TAP	BF TAP DEPTH	AJ	AK(4)	A.C. SHAFT EXT. REF.
DC189ATY	ND. 2	9.00	4.50	3.75	.31	.44	1.50	3.56	3.56	.50	8.88	8.75	1.88	2.75	.12	8.75	3/8-13	.62	5.88	4.500	140TC EXT.
DC189ATCZ	ND. 1	9.00	4.50	3.75	.31	.44	1.50	3.56	3.56	.50	8.88	8.75	1.88	2.75	.12	8.75	3/8-13	.62	7.25	8.500	180TC EXT.
DC181DATY	ND. 2	9.00	4.50	3.75	.31	.44	1.50	3.56	3.56	.50	8.88	8.75	1.88	2.75	.12	8.75	3/8-16	.62	5.88	4.500	140TC EXT.
DC181DATCZ	ND. 1	9.00	4.50	3.75	.31	.44	1.50	3.56	3.56	.50	8.88	8.75	1.88	2.75	.12	8.75	3/8-16	.62	7.25	8.500	180TC EXT.
DC1811ATY	ND. 2	9.00	4.50	3.75	.31	.44	1.50	3.56	3.56	.50	8.88	8.75	1.88	2.75	.12	8.75	3/8-16	.62	5.88	4.500	140TC EXT.
DC1811ATCZ	ND. 1	9.00	4.50	3.75	.31	.44	1.50	3.56	3.56	.50	8.88	8.75	1.88	2.75	.12	8.75	3/8-16	.62	7.25	8.500	180TC EXT.

FRAME	FLANGE	C(5)	B	2F	DRIVE END SHAFT AND KEY								TERMINAL BOLT DIMENSIONS								WT. LBS.
					N	N-W (X/2)	V	AA	RA (3)	SO	LGTH	AA	AB	AC	AF	X	Y	YZ			
DC189ATY	ND. 2	18.81	11.62	10.00	2.44	2.25	.8750	2.00	2.12	.771	.188	1.38	1.00	7.30	6.11	2.19	4.38	3.75	3.25	130	
DC189ATCZ	ND. 1	19.44	11.62	10.00	3.06	2.88	1.250	2.62	2.62	.986	.250	1.81	1.00	7.30	6.11	2.19	4.38	3.75	3.25	130	
DC181DATY	ND. 2	19.56	12.38	11.00	2.44	2.25	.8750	2.00	2.12	.771	.188	1.38	1.00	7.30	6.11	2.19	4.38	3.75	3.25	155	
DC181DATCZ	ND. 1	20.19	12.38	11.00	3.06	2.88	1.250	2.62	2.62	.986	.250	1.81	1.00	7.30	6.11	2.19	4.38	3.75	3.25	155	
DC1811ATY	ND. 2	21.06	13.88	12.50	2.44	2.25	.8750	2.00	2.12	.771	.188	1.38	1.00	7.30	6.11	2.19	4.38	3.75	3.25	185	
DC1811ATCZ	ND. 1	21.69	13.88	12.50	3.06	2.88	1.250	2.62	2.62	.986	.250	1.81	1.00	7.30	6.11	2.19	4.38	3.75	3.25	185	

- (1) "D" DIMENSION WILL NOT BE EXCEEDED. SHIMS UP TO .06 INCHES IN THICKNESS ARE USUALLY REQUIRED FOR COUPLED OR GEARED MACHINES. TOLERANCE +.00/-.06.
(2) "U" VARIES +.0000, -.0005.
(3) "R" VARIES +.000, -.015.
(4) "AK" VARIES +.000, -.003.
FACE RUNDUT AND ECCENTRICITY .004 MAX. T. I. R.

- (5) WHEN THE MOTOR APPLICATION DOES NOT REQUIRE THE USE OF DPP, DRIVE END, ADD .25 TO "C" DIM. FOR BRACKET COVER.
(6) TERMINAL BOX CAN BE ROTATED TO REPOSITION CONDUIT CONNECTION.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED CONSULT FACTORY.
(7) "BB" OF .25 IS A MINIMUM VALUE.

MOTOR WEIGHT MAY VARY 15% FOR NON-STANDARD RATINGS AND/OR ACCESSORIES.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: REVISE "D" DIM TOLERANCE	VERSION: 04	TDR: 000001148815
REV. LTR: D	FILE: \RGG\00030\373	REVISED: 03:18:10 09/15/2020
MTL: -	BY: RGNAS	

BALDOR - RELIANCE®

DIMENSION DRAWING, DC180ATY - DC180ATCZ, DPP, TENV, FOOT MTG.

SH 1 of 1

609980-503

