ABB BALDOR RELIANCE

Customer information packet

CXT3202T

20HP, 3520RPM, 3PH, 60HZ, 256TC, 0936M, TEFC, F
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 2:12:15 AM

Specifications

Enclosure	TEFC
Frame	256TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CCSA US
	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	50.000 A @ 208.0 V
	46.000 A @ 230.0 V
	23.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated

Part Detail

Revision	F
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	09WGZ601
Layout	09LY-001-012
Eff. date	06-28-2024
CD Diagram	CD0005
Poles	02
Leads	9#12
Proprietary	False
Created date	12-17-2020

Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3
Heater Indicator	No Heater
High Voltage Full Load Amps	23.0 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0936M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	23.86 IN
Power Factor	89
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3520 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4163L									
CAT.NO.	CXT3202T					**I.P.**	54		
SPEC.	09-0000-2817					**ENCL**	TEFC		
FRAME	256TC		**H.P.**	20					
VOLTS	230/460		**P.F.**	89					
F.L. AMPS	46/23			**RATING**	40C AMB-CONT				
R.P.M.	3520								
HZ.	60	**PH.**	3	**CLASS**	F				
SER.F.	1.15	**DES.**	A	**SL HZ**	1.3				
NEMA NOM. EFF.	91	**WK2**	0.92						
DE	6309	**ODE**	6208						
MAG. CUR.	14.4/7.2								
INV TYPE	PWM	**CHP**	60	**TO**	90	**T. CODE**	T3		
CT	6	**TO**	60	**VT**	6	**TO**	60		
CC	010A	**SN**							
	USABLE AT 50 HZ 15HP 190/380V 42/21A								

AC Induction Motor Performance Data
Record # 32051
Typical performance - not guaranteed values

Winding: 09WGZ601-R006	**Type:** 0936M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			20	**Full Load Torque**	29.6 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			46/23	**Breakdown Torque**	111 LB-FT
R.P.M.			3520	**Pull-up Torque**	39.1 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	49.6 LB-FT
NEMA Design Code	B	**KVA Code**	H	**Starting Current**	161 A
Service Factor (S.F.)			1	**No-load Current**	7.17 A
NEMA Nom. Eff.	91	**Power Factor**	89	**Line-line Res. @ 25ºC**	0.47592 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	76°C
				Locked-rotor Power Factor	29
				Rotor inertia	0.92 LB-FT2

Load Characteristics 460 V, 60 Hz, 20 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	58	78	86	89	90	90
Efficiency	88.9	92.2	92.4	91.7	90.7	89.2
Speed	3579.6	3561.5	3541.3	3519.5	3495.4	3467.8
Line amperes	9	13	17.7	22.9	28.6	35


ABB Motors and Mechanical Inc.


WINDING # 09WGZ601

20 HP 3 PH 60 HZ 3520 RPM 460 V 0936M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=111 PU=39.1 LR=49.6 LRA=161




09LY-001-012
(920-960) = 23.92
10.17
APPROXIMATE
CENTER OF GRAVITY
+/- .50"
3.75
.25
.38 KEY
2.88 LONG
Ø9.09
.33
1.625
1.624
Ø8.500
8.497
SLINGER
(EA END
WHEN REQ'D)
DRAIN FITTING
(EA. END)
8 HOLES
Ø.53
8.25
.75
8.25
4.75
10.00
11.50
12.94
10.18
6.63
2.50
45°
45°
4 HOLES
.50-13 TAP
Ø7.25 B.C.
.07
13.08
.00
6.25 +.00 -.06
APPROXIMATE
CENTER OF
GRAVITY +/- .50"
3.50
.79
LEAD HOLE
Ø1.75
5.00
5.00
8.18
5.75
11.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD LEADER "SLINGER WHEN REQ'D*
REV: D
VERSION: 04
REVISED: 07:29:05 09/08/2026
TDR: 000001283352
MODEL NO. 09LY-001-012
REF: -
BY: ENNIND0
B
BALDOR - RELIANCE®
HOR TEFC 254-6TC GP W/SLD BRGS
09LY-001-012

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS