



---

# Customer information packet

## CXT3304T

30HP, 1760RPM, 3PH, 60HZ, 286TC, 1056M, TEFC, F

Class - CLI GP A,B,C,D

Division - Division II

## Specifications

Enclosure	TEFC
Frame	286TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CCSA US CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	3
Current @ Voltage	78.000 A @ 208.0 V 76.000 A @ 230.0 V 38.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.6 %
Electrically Isolated Bearing	Not Electrically Isolated

## Part detail

Revision	E
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	10WGY538
Layout	10LYC152
Eff. date	06-28-2024
CD Diagram	CD0180
Poles	04
Leads	9#8
Proprietary	False
Created date	11-16-2020

Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3
Heater Indicator	No Heater
High Voltage Full Load Amps	38.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1056M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	27.76 IN
Power Factor	80
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

**Nameplate**

<b>NP4163L</b>										
<b>CAT.NO.</b>	CXT3304T					<b>I.P.</b>	54			
<b>SPEC.</b>	10-0000-1822					<b>ENCL</b>	TEFC			
<b>FRAME</b>	286TC		<b>H.P.</b>	30						
<b>VOLTS</b>	230/460		<b>P.F.</b>	80						
<b>F.L. AMPS</b>	76/38		<b>RATING</b>	40C AMB-CONT						
<b>R.P.M.</b>	1760									
<b>HZ.</b>	60		<b>PH.</b>	3		<b>CLASS</b>	F			
<b>SER.F.</b>	1.15		<b>DES.</b>	A		<b>SL HZ</b>	1.33			
<b>NEMA NOM. EFF.</b>	93.6		<b>WK2</b>	4.46						
<b>DE</b>	6311		<b>ODE</b>	6309						
<b>MAG. CUR.</b>	36/18									
<b>INV TYPE</b>	PWM	<b>CHP</b>	60		<b>TO</b>	90		<b>T. CODE</b>	T3	
<b>CT</b>	3	<b>TO</b>	60		<b>VT</b>	3		<b>TO</b>	60	
<b>CC</b>	010A		<b>SN</b>							
USABLE AT 50 HZ 25HP 190/380V										
76/38A										

**AC Induction Motor Performance Data**

Record # 57562

Typical performance - not guaranteed values

<b>Winding: 10WGY538-R039</b>		<b>Type: 1056M</b>		<b>Enclosure: TEFC</b>	
<b>Nameplate Data</b>			<b>460 V, 60 Hz: High Voltage Connection</b>		
<b>Rated Output (HP)</b>		30	<b>Full Load Torque</b>		88.7 LB-FT
<b>Volts</b>		208-230/460	<b>Start Configuration</b>		direct on line
<b>Full Load Amps</b>		78-76/38	<b>Breakdown Torque</b>		330 LB-FT
<b>R.P.M.</b>		1760	<b>Pull-up Torque</b>		142 LB-FT
<b>Hz</b>	60 Phase	3	<b>Locked-rotor Torque</b>		178 LB-FT
<b>NEMA Design Code</b>	A KVA Code	J	<b>Starting Current</b>		270 A
<b>Service Factor (S.F.)</b>		1	<b>No-load Current</b>		17.9 A
<b>NEMA Nom. Eff.</b>	93.6 Power Factor	80	<b>Line-line Res. @ 25°C</b>		0.19377 Ω
<b>Rating - Duty</b>		40C AMB-CONT	<b>Temp. Rise @ Rated Load</b>		64°C
			<b>Locked-rotor Power Factor</b>		30.9
			<b>Rotor inertia</b>		4.47 LB-FT <sup>2</sup>

**Load Characteristics 460 V, 60 Hz, 30 HP**

<b>% of Rated Load</b>	<b>25</b>	<b>50</b>	<b>75</b>	<b>100</b>	<b>125</b>	<b>150</b>
<b>Power Factor</b>	41	63	73	80	82	85
<b>Efficiency</b>	87.6	92.3	93.5	93.7	93.4	92.9
<b>Speed</b>	1792.2	1787.6	1782.4	1776.5	1770.3	1762.1
<b>Line amperes</b>	19.8	24.3	30.7	37.6	45.6	55.2


ABB Motors and Mechanical Inc.

WINDING # 10WGY538


Typical performance - not guaranteed values.

30 HP 3 PH 60 HZ 1760 RPM 460 V 1056M

TORQUES (LB-FT): PO=330 PU=142 LR=178 LRA=270




5/12/2025 ACPERF, record # 57562




CD0180



LOW VOLTAGE  
(2D)



HIGH VOLTAGE  
(1D)



**NOTES:**

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIRO
MTL: -	© □	

**BALDOR - RELIANCE®**

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1