

ABB BALDOR RELIANCE III

Customer information packet

D1152

.5HP, 1750RPM, DC, 56, 3420D, TEFC, F1

Class - None

Division -

Specifications

Armature Voltage	115 V
Base Speed	1750 rpm
Enclosure	TEFC
Frame	56
Frame Material	Steel
Haz Area Class and Group	None
Output Power	0.500 HP
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Armature Current	4.8 a
Armature Inertia	4.680 lb-ft ²
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Field Winding Type	COMPOUND
Heater Indicator	No Heater
Insulation Class	F
Lifting Lugs	No Lifting Lugs
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 14 AWG 2 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Mounting Arrangement	F1
Overall Length	13.54 IN
Product Family	WP Below Decks Marine Duty
Pulley End Bearing Type	Sealed Bearing
RoHS Status	ROHS COMPLIANT
Service Factor	1.00

Part Detail

Revision	AA
Type	DC
Mech. spec.	34-6121
Base	
Status	PRD/A
Elec. spec.	34WG3116
Layout	34LY6121
Eff. date	10-25-2024
CD Diagram	CD0862B01
Poles	00
Leads	
Proprietary	False
Created date	01-01-0001

Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger

Nameplate

NP2801L			
CAT.NO.	D1152		
SPEC.	34-6121-3116		
HP	.5	ENCL	TEFC
RPM	1750		
FRAME	56	TYPE	3420D
ARM V	115	ARM A	4.6
FLD V	115	FLD A	.37
INSUL	F	AMB.	40
DUTY	CONT	SUPPLY	A
BRG/DE	6203	BRG/ODE	6203
BRUSHES	2/BP5000H03		
	IEEE 45	BLANK	
SER.			
BLANK	--		
APRV-CSA	APRV-UL		

DC Motor Performance Data

Record # 1419

Typical performance - not guaranteed values

Winding: 34WG3116-R001		Type: 3420D	Enclosure: TEFC
Nameplate Data		General Characteristics	
Rated Output (HP)	0.5	Armature Resistance @ 25°C	2.6 Ω
R.P.M.	1750		
Armature Volts	115	Series Winding Resistance @ 25°C	0.493 Ω
Armature Amps	4.8	Shunt Winding Resistance @ 25°C	247 Ω
Field Volts			
Field Amps			
Rating - Duty	40C AMB-CONT		
Power Supply Code	K		

Load Characteristics at 115 Armature Volts

Load Point	1	2	3	4	5	6
Armature Amps	0.34	2.04	3.05	3.84	4.74	5.64
R.P.M.	1982	1854	1781	1733	1671	1602
Torque (LB-FT)	0	0.75	1.125	1.5	1.875	2.25


ABB Motors and Mechanical Inc.

WINDING # 34WG3116


Typical performance - not guaranteed values.

0.5 HP DC 1750 RPM 115 V 3420D

ENCL: TEFC DUTY: CONT CL: F



34LY6121



CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: LOAD TO SOLIDWORKS - REV D

REV: E

VERSION: 01

REVISED: 08:22:18 12/22/2022

TDR: 000001201165

BALDOR - RELIANCE®

34LY6121

MODEL NO. 34LY6121

BY: ENFRAJ0

REF: -

STD. HORZ 34DC NEMA 56 TEFC S/P 14-2 WEATHERPROOF

34LY6121

