

ABB BALDOR RELIANCE III

Customer information packet D2510R

10HP, 1750RPM, DC, 2113ATY, TEFC,

Specifications

Enclosure	TEFC
Frame	MC2113ATZ
Frame Material	Exposed Laminations
Output Power	10.000 HP
Agency Approvals	CCSA US
Ambient Temperature	40 °C
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Feedback Device	NO FEEDBACK
Field Winding Type	STAB SHUNT
Frame Prefix	MC
Heater Indicator	No Heater
Lifting Lugs	Standard Lifting Lugs
Motor Standards	NEMA
Mounting Arrangement	F1
Overall Length	33.44 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Slinger Indicator	No Slinger

Part Detail

Revision	-
Type	DC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	G6241C A
Layout	609951-013
Eff. date	04-13-2015
CD Diagram	406770-001
Poles	00
Leads	
Proprietary	False
Created date	04-10-2015

Nameplate


000613006HP									
CAT.NO.		SPEC NO.	T21S0303						
FR	MC 2113ATZ	HP	10	DUTY	CONT				
ENCL.	TEFC	RPM	1750/ 2300		S.F.	1.0			
ENCL MOD		VOLTS	240		INSUL	F			
MAX SAFE SPEED	4500	AMPS	35.50		AMB.	40			
FIELD DATA		SER.NO.							
WINDING	STAB SHUNT	POWER CODE	C						
VOLTS	150	D.E. BRG.	50BC03J30X						
MAX AMPS @ 25 C	3.13	O.D.E. BRG.	45BC02J30X						
HOT AMPS	2.19/ 1.58	MIN. AMB.	0			TYPE	TR		
	BRUSH:419904051AB								

609951-013

**INDUSTRIAL DIRECT CURRENT MOTORS
AND GENERATORS - RPM III**

ENCLOSURE: TOTALLY ENCLOSED COOLING: FAN COOLED
MOUNTING: FOOT ACCESSORIES: PROVISION FOR
METHOD OF DRIVE: COUPLED OR BELTED TACHOMETER MOUNTING
ONLY WHEN SPECIFIED

FRAMES SC2113ATZ THRU LC2812ATZ



DIMENSIONS ARE IN INCHES																
FRAME	A	BC (1)	E	G	H	HG	J	D	P	T	BA	K	FK	BK	FAK (6)	FZK (7)
SC2113ATZ-LC2113ATZ	10.25	5.25	4.25	.44	.44	1.38	1.75	11.62	12.75	1.38	3.50	5.19	6.81	2.38	9.750	N/A
SC2512ATZ-LC2512ATZ	12.31	6.25	5.00	.50	.56	1.62	2.00	13.62	14.75	1.94	4.25	6.06	8.00	3.00	11.250	N/A
MC2812ATZ-LC2812ATZ	13.78	7.00	5.50	.62	.56	1.88	2.75	15.06	16.12	2.31	4.75	6.75	9.19	3.50	N/A	12.500

FRAME	C	B	BS	2F	DRIVE END SHAFT AND KEY					WT. LBS.
					N	N-V	U(2)	V	R(3)	
SC2113ATZ	32.19	22.50	11.38	18.00	4.00	3.75	1.875	3.50	1.591	500 2.50 355
MC2113ATZ	33.44	23.75	12.62	18.00	4.00	3.75	1.875	3.50	1.591	500 2.50 380
LC2113ATZ	35.06	25.38	14.25	18.00	4.00	3.75	1.875	3.50	1.591	500 2.50 410
SC2512ATZ	35.94	25.06	12.06	20.00	4.50	4.25	2.125	4.00	1.845	500 3.00 555
MC2512ATZ	37.44	26.56	13.56	20.00	4.50	4.25	2.125	4.00	1.845	500 3.00 590
LC2512ATZ	38.94	28.06	15.06	20.00	4.50	4.25	2.125	4.00	1.845	500 3.00 630
MC2812ATZ	41.62	29.94	14.25	22.00	5.00	4.75	2.375	4.50	2.021	625 3.50 835
LC2812ATZ	43.88	32.19	16.50	22.00	5.00	4.75	2.375	4.50	2.021	625 3.50 900

- (1) "B" DIMENSION WILL NOT BE EXCEEDED. SHIMS UP TO .03 INCHES IN THICKNESS ARE USUALLY REQUIRED FOR COUPLED OR GEARED MACHINES.
(2) "U" VARIES-----+.000 -.001
(3) "2F" VARIES-----+.000 -.015
(4) TERMINAL BOX VARIES WITH H.P. FOR DIMENSIONS "AA", "AB", "AC", "AF", "X" AND "Y". SEE DRAWING NUMBER 609959-1.
(5) WALLS OR OBSTRUCTIONS MUST NOT ENCRDACH ON AIR INLET SPACE "XC".
(6) "FAK" VARIES +.005 -.000-----FACE RUNOUT AND ECCENTRICITY .007 MAX. T.I.R.
(7) "FZK" VARIES +.000 -.005-----FACE RUNOUT AND ECCENTRICITY .007 MAX. T.I.R.
(8) STUB SHAFT SUPPLIED ONLY WHEN SPECIFIED. KEY SIZE .188 X .188 X 1.00
(9) FOR RE-045 OR SPY PROVISIONS ON "C2812" ADD 1.00 TO "LL" DIMENSION.
TERMINAL BOX CAN BE ROTATED FOR LEAD OUTLET AT TOP, SIDES OR BOTTOM.
TERMINAL BOX LOCATED ON OPPOSITE SIDE WHEN F-2, W-1, W-4, W-5, W-7, OR C-1 MOUNTING IS SPECIFIED. BOX LOCATED ON TOP WHEN SPECIFIED.
MOTOR WEIGHT MAY VARY 15% FOR NON-STANDARD RATINGS AND/OR ACCESSORIES.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.

TACHOMETER	LL
BC-42	4.25
BC-46	
RD-11	
RD-12	
RD-51	
RD-61	3.80 1.12
RE-62	
M627, M628	
M727, M737	SEE NOTE (9)
M738	
DYNAPAR 74S	SEE NOTE (9)
RE-045	
SPY	


CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: LOADED TO BUS	VERSION: 00	TDR: 000000577407
REV. LTR: -	REVISED: 11:02:01 01/26/2011	BY: CONNAS
FILE: \RGG\00015\557		
MTL: -		

BALDOR
DIMENSION DRAWING, SC2113ATZ - LC2812ATZ, TEFC, FOOT MTG
SH 1 of 1

609951-013

609959-001

INDUSTRIAL DIRECT CURRENT MOTORS
AND GENERATORS - RPM III
TERMINAL BOX DIMENSIONS
STANDARD SIZE AND ONE SIZE LARGER
FRAMES C2113ATZ THRU C2815ATZ

DIMENSIONS ARE IN INCHES

FRAME SIZE	MAX. AMPS	STANDARD SIZE						STEEL TERMINAL BOX DIMENSIONS						ONE SIZE LARGER					
		AK(1)	AB	AC	AF	X	Y	NUMBER	AK(1)	AB	AC	AF	X	Y	NUMBER	AK(1)	AB	AC	AF
C2113ATZ	40	3/4 & 1"	8.97	7.47	1.94	4.38	5.00	705028-1-R	1-1/4 & 1-1/2	10.03	8.03	2.50	5.50	6.12	705029-1-R	1-1/4 & 1-1/2	10.03	8.03	2.50
C2115ATZ	96	1-1/4 & 1-1/2	10.03	8.03	2.50	5.50	6.12	705029-1-R	2" & 2-1/2	11.16	8.41	3.19	7.00	7.62	705030-1-R	2" & 2-1/2	11.16	8.41	3.19
(2)	208	2" & 2-1/2	11.16	8.41	3.19	7.00	7.62	705030-1-R	2" & 2-1/2	11.16	8.41	3.19	7.00	7.62	705030-1-R	2" & 2-1/2	11.16	8.41	3.19
C2516ATZ	40	3/4 & 1"	10.03	8.53	1.94	4.38	5.00	705028-1-R	1-1/4 & 1-1/2	11.09	9.09	2.50	5.50	6.12	705029-1-R	1-1/4 & 1-1/2	11.09	9.09	2.50
C2514ATZ	96	1-1/4 & 1-1/2	11.09	9.09	2.50	5.50	6.12	705029-1-R	2" & 2-1/2	12.22	9.47	3.19	7.00	7.62	705030-1-R	2" & 2-1/2	12.22	9.47	3.19
C2115ATZ	208	2" & 2-1/2	12.22	9.47	3.19	7.00	7.62	705030-1-R	2" & 2-1/2	12.22	9.47	3.19	7.00	7.62	705030-1-R	2" & 2-1/2	12.22	9.47	3.19
(2)	128	2"	14.03	10.53	4.25	8.44	7.25	74874-R	3"	14.47	11.22	4.25	8.44	7.25	74874-R	3"	14.47	11.22	4.25
C2816ATZ	185	3"	14.47	11.22	4.25	8.44	7.25	74874-R	3"	15.91	11.84	5.38	10.56	9.00	706308-3-R	3"	15.91	11.84	5.38
C2815ATZ	269	4"	15.91	11.84	5.38	10.56	9.00	706308-3-R	5" (4)	18.72	13.47	7.00	12.75	15.00	706589-1-C	5" (4)	18.72	13.47	7.00

FRAME SIZE	MAX. AMPS	STANDARD SIZE						CAST IRON TERMINAL BOX DIMENSIONS						ONE SIZE LARGER					
		AK(3)	AB	AC	AF	X	Y	NUMBER	AK(3)	AB	AC	AF	X	Y	NUMBER	AK(3)	AB	AC	AF
C2113ATZ	18	3/4	10.03	8.03	2.50	5.00	5.75	705028-2-S	1"	10.03	8.03	2.50	5.00	5.75	705028-2-T	1"	10.03	8.03	2.50
C2115ATZ	40	1"	10.03	8.03	2.50	5.00	5.75	705028-2-T	1-1/2	10.97	8.53	3.00	6.00	7.00	705029-2-R	1-1/2	10.97	8.53	3.00
C2115ATZ	96	1-1/2	10.97	8.53	3.00	6.00	7.00	705029-2-R	2"	12.66	8.91	3.62	7.88	9.25	705030-2-R	2"	12.66	8.91	3.62
(2)	208	2"	10.97	8.53	3.00	6.00	7.00	705029-2-S	2-1/2	11.09	9.09	2.50	5.00	5.75	705028-2-T	2-1/2	11.09	9.09	2.50
C2516ATZ	40	3/4	11.09	9.09	2.50	5.00	5.75	705028-2-S	1"	12.03	9.59	3.00	6.00	7.00	705029-2-R	1-1/2	12.03	9.59	3.00
C2514ATZ	96	1-1/2	12.03	9.59	3.00	6.00	7.00	705029-2-R	2"	12.03	9.59	3.00	6.00	7.00	705029-2-S	2"	12.03	9.59	3.00
C2113ATZ	208	2"	12.78	10.34	3.00	6.00	7.00	75460-T	2-1/2	13.72	9.97	3.62	7.88	9.25	705030-2-R	2-1/2	13.72	9.97	3.62
C2816ATZ	185	3"	14.47	10.72	3.62	7.88	9.25	76700-R	4"	14.47	10.72	3.62	7.88	9.25	76700-R	4"	14.47	10.72	3.62
C2815ATZ	269	4"	15.78	11.59	4.12	9.50	10.50	76700-R	5" (4)	18.59	13.34	7.00	12.75	15.00	76700-S	5" (4)	18.59	13.34	7.00

CONDUIT BOX DIMENSIONS WITH TERMINAL BOARDS (IEC TYPE BOX)

FRAME SIZE	AMPS	STANDARD SIZE						OPTIONAL AUXILIARY CONDUIT BOX DIMENSIONS (MAXIMUM)					
		AB	AC	AF	X	AA	Y	FRAME SIZE	XAB	XY	XY	XY	PART NUMBER
C210	100	10.71	8.98	2.72	7.48	---	7.48	C210	10.86	8.00	8.00	8.00	706310-225-R
	200	11.66	9.25	3.35	8.82	---	8.82	C250	11.88	8.00	8.00	8.00	706310-3-B
	100	11.30	9.57	2.72	7.48	---	7.48	C280	12.62	8.00	8.00	8.00	706310-3-B
C250	200	11.85	9.84	3.35	8.82	---	8.82						
	400	17.48	12.75	6.20	14.39	---	14.39						
	800	17.48	12.75	6.20	14.39	---	14.39						
	200	12.60	10.59	3.76	8.82	---	8.82						
	400	18.27	13.54	6.20	14.39	---	14.39						
	800	18.27	13.54	6.20	14.39	---	14.39						
C280	1600	18.27	13.54	7.68	15.35	---	15.35						

- (1) MAX CONDUIT
(2) RATES PROVIDED WITH DOUBLE KNUCKLE
(3) MAX PIPE LAP

- (4) TERMINAL BOX 76870-S AND 76870-98 EXTENDS BELOW MOTOR FEET
TERMINAL BOX 76870-S AND 76870-98 EXTENDS BELOW MOTOR FEET
DR C-1 MOUNTING IS SPECIFIED. BOX LOCATED IN TOP WHEN SPECIFIED.
FOR "X"/TERMINAL BOX DIMENSIONS SEE 609959-2
FOR MILL TYPE TERMINAL BOX DIMENSIONS SEE 609959-3

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: ADD 706310-63G C/BOX TO C250 AND C280 FRAMES	VERSION: 01	TDR: 000000816512
REV. LTR: A		
FILE: \RGG\00021\153		REVISED: 03: 09: 09 09/06/2013
MTL: -		BY: RGGWT

BALDOR

DIMENSION SHEET

SH 1 of 1

609959-001

