


INDUSTRIAL DIRECT CURRENT MOTORS AND GENERATORS – RPM III

ENCLOSURE: DRIP-PROOF FULLY-GUARDED,
SPLASHPROOF
MOUNTING: FOOT

COOLING: FORCE VENTILATED WITH
INTEGRAL BLOWER AND
MOTOR AIR FILTERED-
SPECIAL BAFFLE

ACCESSORIES: PROVISION FOR
TACHOMETER MOUNTING
ONLY WHEN SPECIFIED

FRAME MC3212ATZ



- 1) SHAFT RUNDUT .003 MAX. T.I.R..
- 2) WHEN THE MOTOR APPLICATION DOES NOT REQUIRE THE USE OF OPPOSITE DRIVE END, ADD .25 TO THIS DIMENSION.
- 3) MOTOR TAPPED FOR SCREW-IN STUB SHAFT AT ODE END.
- 4) TERMINAL BOX CAN BE ROTATED WITH LEAD OUTLET AT TOP, SIDES OR BOTTOM. BOX IS RATED 128 A.
- 5) MOTOR WEIGHT APPROX. 1150 LBS.
- 6) HORIZONTAL APPLICATIONS ONLY.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.

REF. 5075RS-1BV (SPEC. D32-A000-0075)

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: REVISE DRAWING		
REV. LTR: A	VERSION: 01	TDR: 000001241447
FILE: \RGG\00033\332	REVISED: 03:42:52 09/23/2024	BY: USNISC2
MTL: -		

BALDOR - RELIANCE®

DIM DRAWING, MC3212ATZ, DPP, FOOT MTG, BAFFLED, AIR FILTER

SH 1 of 1