

INDUSTRIAL DIRECT CURRENT MOTORS AND GENERATORS - RPM III


ENCLOSURE: DRIP-PROOF FULLY-GUARDED
SPLASHPROOF

COOLING: FORCE VENTILATED
WITH INTEGRAL
BLOWER AND MOTOR

MOUNTING: FOOT

ACCESSORIES: PROVISION FOR
TACHOMETER MOUNTING
ONLY WHEN SPECIFIED

FRAMES SC3210ATZ THRU ULC3214ATZ



DIMENSIONS ARE IN INCHES

FRAME	XAC	XC	XE	XF	XO
SC3210ATZ-ULC3214ATZ	6.75	3.25	8.50	19.25	28.00

FRAME	A	D(1)	E	G	H	HG	J	O	P	T	BA	K	STD.	LG.(8)	BK
SC3210ATZ-ULC3214ATZ	15.50	8.00	6.25	.75	.69	2.25	3.00	15.81	15.62	3.54	5.25	6.75	7.94	10.44	4.00

													(5)										
FRAME		METHOD OF DRIVE	C(7)		B		BS	2F	DRIVE END SHAFT AND KEY					OPPOSITE DRIVE END SHAFT AND KEY					WT. LBS.				
			STD.	LG.(8)	STD.	LG.(8)			N	N-W	U(2)	V	R(3)	SO.	LGTH.	FN	FN-FW	FU(2)	FV	FR(3)	SO.	LGTH.	
SC3210ATZ	-LSC3210ATZ	COUPLED	36.25	38.75	28.31	30.81	13.38	20.00	5.50	5.25	2.625	5.00	2.275	.625	4.00	4.75	4.50	2.250	4.25	1.972	.500	3.25	1115
USC3210ATZ	-ULSC3210ATZ	BELTED	36.75	39.25	28.31	30.81	13.38	20.00	6.00	5.75	2.875	5.50	2.450	.750	4.25	4.75	4.50	2.250	4.25	1.972	.500	3.25	1120
UMC3212ATZ	-LMC3212ATZ	COUPLED	39.25	41.75	31.31	33.81	16.38	25.00	5.50	5.25	2.625	5.00	2.275	.625	4.00	4.75	4.50	2.250	4.25	1.972	.500	3.25	1210
UMC3212ATZ	-ULMC3212ATZ	BELTED	39.75	42.25	31.31	33.81	16.38	25.00	6.00	5.75	2.875	5.50	2.450	.750	4.25	4.75	4.50	2.250	4.25	1.972	.500	3.25	1215
LC3212ATZ	-LC3212ATZ	COUPLED	41.25	43.75	33.31	35.81	18.38	25.00	5.50	5.25	2.625	5.00	2.275	.625	4.00	4.75	4.50	2.250	4.25	1.972	.500	3.25	1290
ULC3212ATZ	-ULC3212ATZ	BELTED	41.75	44.25	33.31	35.81	18.38	25.00	6.00	5.75	2.875	5.50	2.450	.750	4.25	4.75	4.50	2.250	4.25	1.972	.500	3.25	1295
LC3214ATZ	-LC3214ATZ	COUPLED	46.25	48.75	38.31	40.81	23.38	32.00	5.50	5.25	2.625	5.00	2.275	.625	4.00	4.75	4.50	2.250	4.25	1.972	.500	3.25	1470
UC3214ATZ	-ULC3214ATZ	BELTED	46.75	49.25	38.31	40.81	23.38	32.00	6.00	5.75	2.875	5.50	2.450	.750	4.25	4.75	4.50	2.250	4.25	1.972	.500	3.25	1475

- (1) "D" DIMENSION WILL NOT BE EXCEEDED. SHIMS UP TO .06 INCHES IN THICKNESS ARE USUALLY REQUIRED FOR COUPLED OR GEARED MACHINES.
- (2) "U" AND "FU" VARY-----+.000 -.001
- (3) "R" AND "FR" VARY-----+.000 -.015
- (4) TERMINAL BOX VARIES WITH H.P. FOR DIMENSIONS "AA", "AB", "AC", "AF", "X" AND "Y". REFER TO BOX D/S. (STD. 609979-1, "X/P" 609979-2, MILL 609979-3)
- (5) OPPOSITE DRIVE END SHAFT SUPPLIED ONLY WHEN SPECIFIED.
- (6) MOTOR SHAFT TAPPED FOR SCREW IN STUB SHAFT.
- (7) WHEN THE MOTOR APPLICATION DOES NOT REQUIRE THE USE OF DPP, DRIVE END, ADD .25 TO "C" DIM. FOR BRACKET COVER.
- (8) DIMENSION FOR FRAMES WITH PREFIX LSC, LMC, LLC, LC, ULSC, ULMC, ULLC OR ULC.
- (9) "XG" DIMENSION IS NOT APPLICABLE TO "C3214ATZ" FRAMES (BLOWER MOTOR IS CENTERED ON SHAFT C/L).

TERMINAL BOX CAN BE ROTATED FOR LEAD OUTLET AT TOP, SIDES OR BOTTOM.
TERMINAL BOX LOCATED ON OPPOSITE SIDE WHEN F-2, W-1, W-4, W-5, W-7, OR C-1 MOUNTING IS SPECIFIED.
BOX LOCATED ON TOP WHEN SPECIFIED.
BLOWER ASSEMBLY CAN BE LOCATED AT POSITIONS 1, 2, OR 4, EXCEPT BLOWER ASSEMBLY AND TERMINAL BOX CAN NOT BE LOCATED AT THE SAME POSITION.
MOTOR WEIGHT MAY VARY 15% FOR NON-STANDARD RATINGS AND/OR ACCESSORIES.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: LOADED TO BUS		
REV. LTR: -	VERSION: 00	TDR: 000000578087
FILE: \RGG\00016\040	REVISED: 03:36:51 01/28/2011	BY: CONNAS
MTL: -		

BALDOR

DIMENSION DRAWING, SC3210ATZ - ULC3214ATZ, DPP, FOOT MTG

SH 1 of 1