

ABB BALDOR RELIANCE III

Customer information packet

D50400RS-BV

400HP, 1750RPM, DC, 4013ATZ, DPG-FV,

Specifications

Enclosure	DP
Frame	LC4013ATZ
Frame Material	Exposed Laminations
Output Power	400.000 HP
Agency Approvals	CCSA US
Ambient Temperature	40 °C
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Feedback Device	NO FEEDBACK
Field Winding Type	STAB SHUNT
Frame Prefix	LC
Heater Indicator	No Heater
Lifting Lugs	Standard Lifting Lugs
Motor Standards	NEMA
Mounting Arrangement	F2
Overall Length	60.19 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Slinger Indicator	No Slinger

Part Detail

Revision	B
Type	DC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	G7668A A
Layout	609962-025
Eff. date	07-19-2024
CD Diagram	406770-001
Poles	00
Leads	
Proprietary	False
Created date	04-09-2015

Nameplate

000613006LP									
CAT.NO.		SPEC NO.	T40S1311						
FR	LC 4013ATZ	HP	400	DUTY	CONT				
ENCL.	DP	RPM	1750/2000	S.F.	1.0				
ENCL MOD	FORCE VENT	VOLTS	500	INSUL		F			
MAX SAFE SPEED	03000	AMPS	635.00	AMB.	40				
	FIELD DATA	SER.NO.							
WINDING	STAB SHUNT	POWER CODE	C						
VOLTS	300	D.E. BRG.	95BC02J30X						
MAX AMPS @ 25 C	7.97	O.D.E. BRG.	95BC02J30X						
HOT AMPS	5.68/4.89	MIN. AMB.	0	TYPE	TR				
	BRUSH:419904052AB								
	AIR BAFFLED								


609962-025

INDUSTRIAL DIRECT CURRENT MOTORS
AND GENERATORS - RPM III

ENCLOSURE: DRIP-PROOF FULLY-GUARDED,
SPLASHPROOF
MOUNTING: FOOT

COOLING: FORCE VENTILATED WITH
INTEGRAL BLOWER AND
MOTOR AIR FILTERED-
SPECIAL BAFFLE
ACCESSORIES: PROVISION FOR
TACHOMETER MOUNTING
ONLY WHEN SPECIFIED


FRAMES C4011ATZ THRU ULC4013ATZ



DIMENSIONS ARE IN INCHES

FRAME	A	B (1)	E	G	H	HG	J	D	P	T	BA	K	FK	BK	AB	AF	RH (6)
C4011ATZ-ULC4013ATZ	19.38	10.00	8.00	1.06	1.06	2.82	3.50	19.81	19.56	4.31	6.62	8.75	12.12	5.25	16.12	8.00	6240

FRAME	METHOD OF DRIVE	C (7)	B	BS	2F	N	DRIVE END SHAFT AND KEY	(5) OPPOSITE DRIVE END SHAFT AND KEY	WT. LBS.
							N-W UK (2) V RC (3) SQ LGTH FN FN-FW FUK (2) FV FRC (3) SQ LGTH		
C4011ATZ	COUPLED	52.19	42.06	16.00	28.00	7.62	7.25 3.625 7.00 3.134 .875 5.75 7.62 7.25 3.625 7.00 3.134 .875 5.75	7.62 7.25 3.625 7.00 3.134 .875 5.75	2500
UC4011ATZ	BELTED	53.19	42.06	16.00	28.00	8.62	8.25 4.125 8.00 3.563 1.000 6.50 7.62 7.25 3.625 7.00 3.134 .875 5.75	7.62 7.25 3.625 7.00 3.134 .875 5.75	2505
MC4013ATZ	COUPLED	56.94	46.81	20.75	36.00	7.62	7.25 3.625 7.00 3.134 .875 5.75 7.62 7.25 3.625 7.00 3.134 .875 5.75	7.62 7.25 3.625 7.00 3.134 .875 5.75	2800
UMC4013ATZ	BELTED	57.94	46.81	20.75	36.00	8.62	8.25 4.125 8.00 3.563 1.000 6.50 7.62 7.25 3.625 7.00 3.134 .875 5.75	7.62 7.25 3.625 7.00 3.134 .875 5.75	2805
LC4013ATZ	COUPLED	60.19	50.06	24.00	36.00	7.62	7.25 3.625 7.00 3.134 .875 5.75 7.62 7.25 3.625 7.00 3.134 .875 5.75	7.62 7.25 3.625 7.00 3.134 .875 5.75	3100
ULC4013ATZ	BELTED	61.19	50.06	24.00	36.00	8.62	8.25 4.125 8.00 3.563 1.000 6.50 7.62 7.25 3.625 7.00 3.134 .875 5.75	7.62 7.25 3.625 7.00 3.134 .875 5.75	3105



FRAME	XA	XB	XC	XD	XE	XF	XD	XP
C4011ATZ-ULC4013ATZ	16.00	6.00	1.25	26.00	9.84	18.75	42.94	22.50

- (1) "D" DIMENSION WILL NOT BE EXCEEDED. SHIMS UP TO .06 INCHES IN THICKNESS ARE USUALLY REQUIRED FOR COUPLED OR GEARED MACHINES.
- (2) "F" AND "FV" VARY -----.000 - .001
- (3) "R" AND "FR" VARY -----.000 - .015
- (4) CUSTOMER TO PROVIDE HOLE IN TERMINAL BOX FOR CONDUIT.
- (5) OPPOSITE DRIVE END SHAFT SUPPLIED ONLY WHEN SPECIFIED.
- (6) MOTOR SHAFT TAPPED FOR SCREW-IN STUB SHAFT
- (7) WHEN THE MOTOR APPLICATION DOES NOT REQUIRE THE USE OF OPP. DRIVE END, ADD .25 TO "C" DIM. FOR BRACKET COVER.
- (8) FOR HORIZONTAL APPLICATIONS ONLY.

TERMINAL BOX LOCATED ON OPPOSITE SIDE WHEN F-2, W-1, W-4, W-5, W-7, OR C-1 MOUNTING IS SPECIFIED. BOX LOCATED ON TOP WHEN SPECIFIED.
BLOWER ASSEMBLY CAN BE LOCATED AT POSITIONS 1, 2, OR 4.
MOTOR WEIGHT MAY VARY 15% FOR NON-STANDARD RATINGS AND/OR ACCESSORIES.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.


CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: LOADED TO BUS	VERSION: 00	TDR: 000000577407
REV. LTR: -	REVISED: 12:40:55 01/26/2011	BY: CONNAS
FILE: \RGG\00015\603		
MTL: -		

BALDOR
DIMENSION DRAWING, C4011ATZ - ULC4013ATZ, DPP, FOOT MTG.
SH 1 OF 1

609962-025

065564-004



SYM	MAKE FROM	a	b	c	REMARKS
	065564-004				
A	X	1/8	5/8	24*	TERMBX & CVR 180AT-250AT
B	X	1/8	5/8	37 1/2*	TERMBX & CVR 280AT-320AT
C	Y	1/4	5/8	44 1/2Δ	FILTER TO HOUSING GASKET
D	X	1/8	5/8	170"	TEAO HEAT EXCH.
E	Y	1/4	5/8	72"Δ	TERMBX & CVR

SYM	MAT'L SPEC	a	b	c
X	46024-XV	1/8	5/8	* 50' ROLL; WET ADHESIVE ON ONE SIDE
Y	46024-XV	1/4	5/8	* 50' ROLL; WET ADHESIVE ON ONE SIDE

Δ RELIANCE WILL CUT AND MOUNT ON FILTER HOUSING PER
ASSEMBLY DRAWING 603989-2.

* PROD. NOTE: WHEN ORDERING THRU PURCHASING
ORDER AS 50 FT. ROLLS, WET ADHESIVE ON ONE
SIDE. RELIANCE WILL CUT AND MOUNT ON COVER.
PER INSTRUCTIONS ON COVER DRAWINGS.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: CHANGE DESCRIPTION ON TITLE BLOCK		
REV. LTR: C	VERSION: 03	TDR: 000000571980
FILE: \RGG\00000\220	REVISED: 10:54:04 12/16/2010	BY: RGGWT
MTL: -		

BALDOR
GASKET,STRIP,CLOSED CELL NEOPRENE
SH 1 of 1

065564-004

