

ABB BALDOR RELIANCE III

Customer information packet

D5075RS-1BV

MC3212ATZ, 75HP, 1750RPM, 500, 300, , F2

Specifications

Armature Voltage	500 V
Base Speed	1750 rpm
Enclosure	DPG-FV
Field Voltage	300 V
Frame	MC3212ATZ
Output Power	75.000 HP
Ambient Temperature	40 °C
Armature Current	122.0 a
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Field Winding Type	STAB SHUNT
Frame Prefix	MC
Heater Indicator	No Heater
Insulation Class	F
IP Rating	IP23
Lifting Lugs	Standard Lifting Lugs
Motor Standards	NEMA
Mounting Arrangement	F1
Overall Length	39.25 IN
Service Factor	1.00
Shaft Diameter	2.624 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Slinger Indicator	No Slinger

Part Detail

Revision	C
Type	DC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	G6295A A
Layout	609972-368
Eff. date	09-25-2024
CD Diagram	406770-001
Poles	00
Leads	
Proprietary	False
Created date	01-24-2019

Nameplate

000613006LP									
CAT.NO.	D5075RS-1BV	SPEC NO.		D32-A000-0075					
FR	MC3212ATZ	HP	75		DUTY		CONT		
ENCL.	DPG-FV	RPM	1750/2100			S.F.	1.00		
ENCL MOD		VOLTS	500			INSUL		F	
MAX SAFE SPEED	3600	AMPS	122.00			AMB.	40		
FIELD DATA		SER.NO.							
WINDING	STAB SHUNT	POWER CODE		C					
VOLTS	300	D.E. BRG.		70BC03J30X					
MAX AMPS @ 25 C	3.56	O.D.E. BRG.		60BC02J30X					
HOT AMPS	2.50/1.84	MIN. AMB.		0		TYPE		TR	
	BRUSH:419904052AJ								
	AIR BAFFLED								

609972-368


INDUSTRIAL DIRECT CURRENT MOTORS AND GENERATORS – RPM III

ENCLOSURE: DRIP-PROOF FULLY-GUARDED,
SPLASHPROOF
MOUNTING: FOOT

COOLING: FORCE VENTILATED WITH
INTEGRAL BLOWER AND
MOTOR AIR FILTERED-
SPECIAL BAFFLE

ACCESSORIES: PROVISION FOR
TACHOMETER MOUNTING
ONLY WHEN SPECIFIED

FRAME MC3212ATZ



- 1) SHAFT ROUNDT .003 MAX. T.I.R.
- 2) WHEN THE MOTOR APPLICATION DOES NOT REQUIRE THE USE OF OPPOSITE DRIVE END, ADD .25 TO THIS DIMENSION.
- 3) MOTOR TAPPED FOR SCREW-IN STUB SHAFT AT ODE END.
- 4) TERMINAL BOX CAN BE ROTATED WITH LEAD OUTLET AT TOP, SIDES OR BOTTOM. BOX IS RATED 128 A.
- 5) MOTOR WEIGHT APPROX. 1150 LBS.
- 6) HORIZONTAL APPLICATIONS ONLY.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.

REF. 5075RS-1BV (SPEC. D32-A000-0075)

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: REVISE DRAWING	VERSION: 01	TDR: 00001241447
REV. LTR: A	FILE: \RGG\00033\332	BY: USN/SCH2
MTL: -	REVISED: 03:42:52 09/23/2024	


BALDOR - RELIANCE®

DIM DRAWING, MC3212ATZ, DPP. FOOT MTG, BAFFLED, AIR FILTER
SH 1 of 1

609972-368

INDUSTRIAL DIRECT CURRENT MOTORS
AND GENERATORS – RPM III

STEEL AND CAST IRON TERMINAL BOX DIMENSIONS
STANDARD SIZE AND ONE SIZE LARGER
FRAMES C3210ATZ THRU C3613ATZ



STEEL TERMINAL BOX DIMENSIONS

FRAME SIZE	MAX AMPS	AA(1)	AB	AC	AF	X	Y	PART NUMBER	AA(1)	AB	AC	AF	X	Y	PART NUMBER
C3210ATZ	185	2	14.88	11.38	4.25	8.44	7.25	74874-R	3	15.31	12.06	4.25	8.44	7.25	74874-24-R
C3212ATZ	269	3	15.31	12.06	4.25	8.44	7.25	74874-24-R	4	16.75	12.69	5.38	10.56	9.00	700308-3-R
C3214ATZ	500	5	16.75	12.69	5.38	10.56	9.00	700308-3-R	5	21.00	15.88	6.50	12.10	14.62	702658-1-C
C3612ATZ	185	2	15.88	12.38	4.25	8.44	7.25	74874-R	3	16.31	13.06	4.25	8.44	7.25	74874-24-R
C3613ATZ	269	3	16.31	13.06	4.25	8.44	7.25	74874-24-R	4	17.75	13.69	5.38	10.56	9.00	700308-3-R
	500	5	22.00	15.88	6.50	12.10	14.62	702658-1-C	5	22.00	15.88	6.50	12.10	14.62	702658-1-C

CAST IRON TERMINAL BOX DIMENSIONS

FRAME SIZE	MAX AMPS	AA(2)	AB	AC	AF	X	Y	PART NUMBER	AA(2)	AB	AC	AF	X	Y	PART NUMBER
C3210ATZ	185	1-1/2	13.62	11.19	3.00	6.00	7.00	75460-R	3	15.31	11.56	3.62	7.88	9.25	76700-RB
C3212ATZ	269	4	15.31	11.56	3.62	7.88	9.25	76700-RB	4	16.62	12.44	4.12	9.50	10.50	76708-RR
C3214ATZ	500	5	16.62	12.44	4.12	9.50	10.50	76708-RR	5	19.44	14.19	7.00	12.75	15.00	76870-S
C3612ATZ	185	1-1/2	14.62	12.19	3.00	6.00	7.00	75460-R	3	16.31	12.56	3.62	7.88	9.25	76700-RB
C3613ATZ	269	4	16.31	12.56	3.62	7.88	9.25	76700-RB	4	17.62	13.44	4.12	9.50	10.50	76708-RR
	500	5	20.44	15.19	7.00	12.75	15.00	76870-S	6	20.44	15.19	7.00	12.75	15.00	76870-R

CONDUIT BOX DIMENSIONS WITH TERMINAL BOARDS (IEC TYPE BOX)

FRAME SIZE	MAX AMPS	AB	AC	AF	X	AA (3)	Y	PART NUMBER
C320	400	19.02	15.28	6.20	14.39	---	14.39	706310-63-B
	800	19.02	15.28	6.20	14.39	---	14.39	706310-63-B
	1600	19.02	15.28	7.68	15.35	---	15.35	706310-63-C
C360	400	20.00	15.28	6.20	14.39	---	14.39	706310-63-B
	800	20.00	15.28	6.20	14.39	---	14.39	706310-63-B
	1600	20.00	15.28	7.68	15.35	---	15.35	706310-63-C

OPTIONAL AUXILIARY CONDUIT BOX DIMENSIONS (MAXIMUM)

FRAME SIZE	XAB	XX	XY	PART NUMBER	FRAME SIZE	XAB	XX	XY	PART NUMBER
C320	10.00	4.25	4.25	602007-26-A	C320	13.50	8.00	8.00	706310-3-B
C360	11.00	4.25	4.25	602007-26-A	C360	14.50	8.00	8.00	706310-3-B

- (1) 'AA' CONDUIT.
- (2) 'AA' PIPE TAP.
- (3) CUSTOMER TO PROVIDE HOLE FOR CONDUIT.
- (4) TERMINAL BOX LOCATED OPPOSITE SIDE WHEN F-2, V-1, V-4, V-5, W-7, OR C-1 MOUNTING IS SPECIFIED. BOX LOCATED ON TOP WHEN SPECIFIED.
- (5) 'X/P' TERMINAL BOX DIMENSIONS SEE 609979-2.
- (6) FOR MILL TYPE TERMINAL BOX DIMENSIONS SEE 609979-3.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.


REV. DESC: LOAD TO BUS	VERSION: 00	TDR: 000000958110
REV. LTR: -	REVISED: 08:37:45 12/17/2015	BY: RGGWT
FILE: \RGG\00026\318		
MTL: -		



DIM SHT,C3210ATZ THRU C3613ATZ,W/AUX C/BOX

SH 1 of 1

065564-004



SYM	MAKE FROM 065564-004	a	b	c	REMARKS
A	X	1/8	5/8	24*	TERMBX & CVR 180AT-250AT
B	X	1/8	5/8	37 1/2*	TERMBX & CVR 280AT-320AT
C	Y	1/4	5/8	44 1/2 Δ	FILTER TO HOUSING GASKET
D	X	1/8	5/8	170"	TEAO HEAT EXCH.
E	Y	1/4	5/8	72" Δ	TERMBX & CVR

SYM	MAT'L SPEC	a	b	c
X	46024-XV	1/8	5/8	* 50' ROLL; WET ADHESIVE ON ONE SIDE
Y	46024-XV	1/4	5/8	* 50' ROLL; WET ADHESIVE ON ONE SIDE

Δ RELIANCE WILL CUT AND MOUNT ON FILTER HOUSING PER ASSEMBLY DRAWING 603989-2.

* PROD. NOTE: WHEN ORDERING THRU PURCHASING ORDER AS 50 FT. ROLLS, WET ADHESIVE ON ONE SIDE. RELIANCE WILL CUT AND MOUNT ON COVER. PER INSTRUCTIONS ON COVER DRAWINGS.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: CHANGE DESCRIPTION ON TITLE BLOCK		
REV. LTR: C	VERSION: 03	TDR: 000000571980
FILE: \RGG\00000\220	REVISED: 10:54:04 12/16/2010	BY: RGGWT
MTL: -		

BALDOR
GASKET,STRIP,CLOSED CELL NEOPRENE
SH 1 of 1

065564-004

