ABB BALDOR RELIANCE

Customer information packet

DM3542

.75HP, 1725RPM, 3PH, 60HZ, 56, 3428M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/13/2026 12:00:01 PM

Specifications

Enclosure	TEFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	UR
	CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	1.400 A @ 460.0 V
	2.800 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	74.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	P
Type	AC
Mech. spec.	34M812
Base	
Status	PRD/A
Elec. spec.	34WGR422
Layout	34LYM812
Eff. date	05-21-2025
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	07-25-2016

High Voltage Full Load Amps	1.4 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Max Speed	2700 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3428M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.85 IN
Power Factor	68
Product Family	Dirty Duty Plus
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3659							
CAT.NO.	DM3542						
SPEC.	34M812R422G1			**ENCL**	TEFC		
FRAME	56	**H.P.**	.75				
VOLTS	230/460						
AMPS	2.8/1.4			**IP**	56		
R.P.M.	1725						
HZ.	60	**PH.**	3	**CLASS**	F		
SER.F.	1.25	**DES.**	B	**CC**			
NEMA NOM. EFF.	74						
RATING	40C AMB-CONT						
DE	6203	**ODE**	6203				
GREASE	POLYREX EM						
SN							
	50C AT 1.0 SF						
	SFA 3.2/1.6						

AC Induction Motor Performance Data
Record # 58333
Typical performance - not guaranteed values

Winding: 34WGR422-R001	**Type:** 3428M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			.75	**Full Load Torque**	2.28 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			2.8/1.4	**Breakdown Torque**	10 LB-FT
R.P.M.			1725	**Pull-up Torque**	7.67 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	11.8 LB-FT
NEMA Design Code	B	**KVA Code**	N	**Starting Current**	11.1 A
Service Factor (S.F.)			1.25	**No-load Current**	1.04 A
NEMA Nom. Eff.	74	**Power Factor**	68	**Line-line Res. @ 25ºC**	17.999 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	60°C
S.F. Amps			3.2/1.6	**Temp. Rise @ S.F. Load**	70°C
				Locked-rotor Power Factor	55.7

Load Characteristics 460 V, 60 Hz, 0.75 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	33	48	60	68	75	79	75
Efficiency	50.2	65.5	71.3	74.1	75.2	75	75.2
Speed	1783.6	1770.3	1757	1742.7	1726.6	1709.9	1727
Line amperes	1.07	1.15	1.25	1.39	1.57	1.76	1.57


ABB Motors and Mechanical Inc.

WINDING # 34WGR422

0.75 HP 3 PH 60 HZ 1725 RPM 460 V 3428M


Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=10 PU=7.67 LR=11.8 LRA=11.1



11/13/2026 ACPERF, record # 58333

34LYM812



CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION


REV. DESC: UPDATE STACK RANGES			
REV: F	VERSION: 06	REVISED: 01:35:47 02/04/2026	TDR: 000001271334
34LYM812	MODEL NO. 34LYM812		REF: -
	BY: ENJEFD0		


BALDOR - RELIANCE®

STD HORZ 34M NEMA 56 TEFC DDP (S/P032-002-002)

34LYM812

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS