

BALDOR® • RELIANCE™

Customer information packet

DRX18324T

3HP, 3470//2890RPM, 3PH, 60/50HZ, 182T, XPFC,
Class - CLI GP C,D
Division - Division I

Specifications

Enclosure	XPFC
Frame	182T
Frame Material	Iron
Frequency	50.00 Hz 60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ 2.000 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 190.0 V @ 50 HZ 230.0 V @ 60 HZ 380.0 V @ 50 HZ
XP Class and Group	CLI GP C,D
XP Division	Division I
Agency Approvals	UL CSA EEV
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	3.200 A @ 380.0 V 3.800 A @ 460.0 V 6.400 A @ 190.0 V 7.600 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT

Part detail

Revision	A
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	06WGY471
Layout	06LY-000-044
Eff. date	09-09-2022
CD Diagram	CD0005
Poles	02
Leads	9#16
Proprietary	False
Created date	08-05-2019

Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	3.2 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0618M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	17.56 IN
Power Factor	89
Product Family	General Purpose
Pulley Face Code	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3470 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

XP Temp Code

T3C

Nameplate

NP1401XPSLEV										
NO.		CC	010A							
S/N		TEMP CODE	T3C							
SPEC.	06-0000-0200		INV.TYPE	PWM						
CAT.NO.	DRX18324T		C HP FR	60	C HP TO	90				
HP	3//2		CT HZ FROM	6	CT HZ TO	60				
VOLTS	230/460//190/380		VT HZ FROM	6	VT HZ TO	60				
AMPS	7.6/3.8//6.4/3.2		MAG CUR	3.2/1.6						
RPM	3470//2890		MX RPM	5400						
HZ	60//50	PH	3	CL	F	NOM.EFF.	86.5			
SER.F.	1.00	DES	B	SL HZ	2.2	WK2	0.079			
FRAME	182T	RATING	40C AMB-CONT							
	55C AMB @1.0SF									
	1.15SF SINEWAVE				NEMA MG-1 PT 5,IP55					

AC Induction Motor Performance Data

Record # 77882

Typical performance - not guaranteed values

Winding: 06WGY471-R020		Type: 0618M		Enclosure: XPFC	
Nameplate Data			460 V, 60 Hz: High Voltage Connection		
Rated Output (HP)		3	Full Load Torque		4.51 LB-FT
Volts		230/460//190/380	Start Configuration		direct on line
Full Load Amps		7.6/3.8//6.4/3.2	Breakdown Torque		25.5 LB-FT
R.P.M.		3470//2890	Pull-up Torque		9.08 LB-FT
Hz	60//50	Phase	3	Locked-rotor Torque	11.9 LB-FT
NEMA Design Code		B KVA Code	K	Starting Current	29.3 A
Service Factor (S.F.)			1	No-load Current	1.64 A
NEMA Nom. Eff.	86.5	Power Factor	89	Line-line Res. @ 25°C	6.24 Ω
Rating - Duty			40C AMB-CONT	Temp. Rise @ Rated Load	45°C
				Locked-rotor Power Factor	59.2
				Rotor inertia	0.0795 LB-FT ²

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	47	70	81	87	90	91
Efficiency	81.1	86.6	87.4	86.6	85.2	83.1
Speed	3568	3538	3505	3468	3430	3382
Line amperes	1.82	2.29	2.94	3.71	4.53	5.5


ABB Motors and Mechanical Inc.

WINDING # 06WGY471

3 HP 3 PH 60 HZ 3468 RPM 460 V 0618M

Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=25.5 PU=9.08 LR=11.9 LRA=29.3



11/28/2023 ACPERF, record # 77882

AC Induction Motor Performance Data

Record # 77883

Typical performance - not guaranteed values

Winding: 06WGY471-R020		Type: 0618M		Enclosure: XPFC	
Nameplate Data			380 V, 50 Hz: High Voltage Connection		
Rated Output (HP)		3	Full Load Torque		3.61 LB-FT
Volts		230/460//190/380	Start Configuration		direct on line
Full Load Amps		7.6/3.8//6.4/3.2	Breakdown Torque		23.13 LB-FT
R.P.M.		3470//2890	Pull-up Torque		9.15 LB-FT
Hz	60//50	Phase	3	Locked-rotor Torque	11.99 LB-FT
NEMA Design Code		B KVA Code	K	Starting Current	27.03 A
Service Factor (S.F.)			1	No-load Current	1.6 A
NEMA Nom. Eff.	86.5	Power Factor	89	Line-line Res. @ 25°C	6.24 Ω
Rating - Duty			40C AMB-CONT	Temp. Rise @ Rated Load	36°C
				Locked-rotor Power Factor	65.7
				Rotor inertia	0.0795 LB-FT ²

Load Characteristics 380 V, 50 Hz, 2 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	44	65	78	84	88	90
Efficiency	73.4	81.5	84.1	84.1	83.2	81.7
Speed	2972	2947	2921	2890	2860	2821
Line amperes	1.73	2.09	2.58	3.18	3.82	4.57


ABB Motors and Mechanical Inc.

WINDING # 06WGY471


Typical performance - not guaranteed values.

2 HP 3 PH 50 HZ 2890 RPM 380 V 0618M


TORQUES (LB-FT): PO=23.13 PU=9.15 LR=11.99 LRA=27.03




11/28/2023 ACPERF, record # 77883



CD0005




LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005