ABB BALDOR RELIANCE

Customer information packet

DRX251544T

15HP, 1765//1470RPM, 3PH, 60HZ, 254T, XPFC, F1
Class - CLI GP C,D
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 9:36:50 PM

Specifications

Enclosure	XPFC
Frame	254T
Frame Material	Iron
Frequency	50.00 Hz
	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 50 HZ
	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	190.0 V @ 50 HZ
	460.0 V @ 60 HZ
	380.0 V @ 50 HZ
Agency Approvals	UL
	CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	36.200 A @ 230.0 V
	30.400 A @ 190.0 V
	18.100 A @ 460.0 V
	15.200 A @ 380.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT

Part Detail

Revision	M
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	09WGZ910
Layout	09LYJ480
Eff. date	04-09-2025
CD Diagram	CD0005
Poles	04
Leads	9#12
Proprietary	False
Created date	03-08-2019

Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	15.2 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	IP55
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0944M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	25.50 IN
Power Factor	83
Product Family	Chemical Process Features
Pulley Face Code	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1401XPSLEV											
NO.				**CC**	010A						
S/N				**TEMP CODE**	T3C						
SPEC.	09-0000-1187			**INV.TYPE**	PWM						
CAT.NO.	DRX251544T			**C HP FR**	60	**C HP TO**	90				
HP	15//10			**CT HZ FROM**	6			**CT HZ TO**	60		
VOLTS	230/460//190/380			**VT HZ FROM**	6			**VT HZ TO**	60		
AMPS	36.2/18.1//30.4/15.2		**MAG CUR**	16/8//15/7.5							
RPM	1765//1470		**MX RPM**	2700							
HZ	60//50	**PH**	3	**CL**	F	**NOM.EFF.**	92.4				
SER.F.	1.00	**DES**	A	**SL HZ**	1.2	**WK2**	1.93				
FRAME	254T	**RATING**	40C AMB-CONT								
	55C AMB @ 1.00 SF, 60C RISE										
	1.15SF ON SINEWAVE			NEMA MG-1 PT.5,IP55							

AC Induction Motor Performance Data
Record # 51149
Typical performance - not guaranteed values

Winding: 09WGZ910-R044	**Type:** 0944M	**Enclosure:** XPFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			15	**Full Load Torque**	44.5 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			36.2/18.1	**Breakdown Torque**	153 LB-FT
R.P.M.			1765	**Pull-up Torque**	69.5 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	86.5 LB-FT
NEMA Design Code	A	**KVA Code**	H	**Starting Current**	127 A
Service Factor (S.F.)			1	**No-load Current**	7.56 A
NEMA Nom. Eff.	92.4	**Power Factor**	83	**Line-line Res. @ 25ºC**	0.59555 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	54°C
				Locked-rotor Power Factor	33
				Rotor inertia	1.92 LB-FT2

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	45	69	79	83	85	87
Efficiency	88.2	92.2	92.7	92.4	91.5	90.4
Speed	1791.3	1783.1	1774	1765.2	1754.6	1743.1
Line amperes	8.62	11	14.5	18.1	22.6	26.9


ABB Motors and Mechanical Inc.

WINDING # 09WGZ910

15 HP 3 PH 60 HZ 1765 RPM 460 V 0944M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=153 PU=69.5 LR=86.5 LRA=127




AC Induction Motor Performance Data
Record # 75708
Typical performance - not guaranteed values


Winding: 09WGZ910-R063	**Type:** 0944M	**Enclosure:** XPFC

Nameplate Data				**380 V, 50 Hz: High Voltage Connection**	
Rated Output (HP)			15//10	**Full Load Torque**	35.63 LB-FT
Volts			230/460//190/380	**Start Configuration**	direct on line
Full Load Amps			36.2/18.1//30.4/15.2	**Breakdown Torque**	147 LB-FT
R.P.M.			1765//1470	**Pull-up Torque**	71.45 LB-FT
Hz	60//50	**Phase**	3	**Locked-rotor Torque**	88.92 LB-FT
NEMA Design Code	A	**KVA Code**	H	**Starting Current**	123 A
Service Factor (S.F.)			1	**No-load Current**	7.42 A
NEMA Nom. Eff.	92.4	**Power Factor**	83	**Line-line Res. @ 25ºC**	0.553 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	41°C
				Locked-rotor Power Factor	36.5
				Rotor inertia	1.92 lb-ft²


Load Characteristics 380 V, 50 Hz, 10 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	40	63	74	81	83	86
Efficiency	86.7	91.4	92.1	92	91.2	90.3
Speed	1493	1486	1479	1472	1463	1454
Line amperes	8.14	9.82	12.46	15.18	18.67	21.93


ABB Motors and Mechanical Inc.
WINDING # 09WGZ910
10 HP 3 PH 50 HZ 1472 RPM 380 V 0944M
Typical performance - not guaranteed values.
TORQUES(LB-FT): PO=147 PU=71.45 LR=88.92 LRA=123
TORQUE
RPM
KW
AMPS
EFF
PF
%EFF
%PF
TORQUE (LB-FT)
RPM
KW
AMPS
PERCENT OF RATED OUTPUT (10 HP)
11/15/2026 ACPERF, record # 75708


09LYJ480
(922-964) = 25.54
12.29
4.20
4.00
.38 KEY
2.88 LONG
Ø13.50
Ø1.625
1.624
ALUM.
SLINGER
(EA. END)
DRAIN FITTING
HW4505A02
(EA. END)
.38-16 TAP
8 HOLES
Ø.53
8.25
8.25
.75
10.00
4.25
11.50
13.44
12.82
6.75
2.70
12.96
6.25 +.00 -.06
3.25
.87
LEAD HOLE
1.25 NPT
5.00
5.00
9.49
5.75
5.75
1 PIN
HW3202E06
(EA END)
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CORRECT DIMS
REV: H
VERSION: 08
REVISED: 10:06:51 05/13/2024
TDR: 000001229321
MODEL NO. 09LYJ480
REF: -
BY: ENCARC0
B
BALDOR - RELIANCE®
HORZ XPFC 254-6T CL.I GP.C&D ONLY W/CP FEAT
09LYJ480

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS