

BALDOR® • RELIANCE™

Customer information packet

D5540R

40 1750/2300 MC3212ATZ TEFC 500V

Specifications

Enclosure	TEFC
Frame	MC3212ATZ
Frame Material	Exposed Laminations
Output Power	40.000 HP
Agency Approvals	CCSA US
Ambient Temperature	40 °C
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Feedback Device	CUST SUPPLIED/PROVISIONS
Field Winding Type	STAB SHUNT
Frame Prefix	MC
Heater Indicator	No Heater
Lifting Lugs	Standard Lifting Lugs
Motor Standards	NEMA
Mounting Arrangement	F2
Overall Length	43.56 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Slinger Indicator	No Slinger

Part detail

Revision	-
Type	DC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	G6318A B
Layout	609971-013
Eff. date	04-13-2015
CD Diagram	406770-002
Poles	00
Leads	
Proprietary	False
Created date	04-10-2015

Nameplate

000613006HP					
CAT.NO.	D5540R	SPEC NO.	T32S0301		
FR	MC 3212ATZ	HP	40	DUTY	CONT
ENCL.	TEFC	RPM	1750/ 2300	S.F.	1.0
ENCL MOD		VOLTS	500	INSUL	F
MAX SAFE SPEED	3600	AMPS	65.00	AMB.	40
	FIELD DATA	SER.NO.			
WINDING	STAB SHUNT	POWER CODE	C		
VOLTS	300	D.E. BRG.	70BC03J30X		
MAX AMPS @ 25 C	1.82	O.D.E. BRG.	60BC02J30X		
HOT AMPS	1.31/ .92	MIN. AMB.	0	TYPE	TR
	BRUSH:419904052AJ; FLD. DATA				
	FOR HIGH VOLTS; FIELD VOLTS				



609971-013

INDUSTRIAL DIRECT CURRENT MOTORS AND GENERATORS - RPM III

ENCLOSURE: TOTALLY ENCLOSED
MOUNTING: FOOT

FRAMES SC3210ATZ THRU ULLC3612ATZ

COOLING: FAN COOLED
ACCESSORIES: PROVISION FOR
TACHOMETER MOUNTING
ONLY WHEN SPECIFIED



TACHOMETER	LL
BC-42	4.25
BC-46	
RD-11	
RD-12	
RD-51	
RD-61	
RD-62	
RE-210	
M627, M628	
M727, M737	
M738	2.12
DYNAPAR 74S	
RE-045G WITH K45M1000	
5PY	

- (1) "D" DIMENSION WILL NOT BE EXCEEDED. SHIMS UP TO .06 INCHES IN THICKNESS ARE USUALLY REQUIRED FOR COUPLED OR GEARED MACHINES.
- (2) "U" VARIES----+.000 -.001
- (3) "R" VARIES----+.000 -.015
- (4) TERMINAL BOX VARIES WITH H.P. FOR DIMENSIONS "AA", "AB", "AC", "AF", "X" AND "Y". SEE DRAWING NUMBER 609979-1.
- (5) DIMENSION FOR FRAMES WITH PREFIX LSC, LMC, LLC, ULMC, OR ULLC.
- (6) METHOD OF DRIVE: COUPLED OR BELTED.
- (7) WALLS OR OBSTRUCTIONS MUST NOT ENCRDACH ON AIR INLET SPACE "XC".
- (8) "FAK" VARIES +.000 - .005----FACE RUNDUT AND ECCENTRICITY .007 MAX. T. I. R.
- (9) STUB SHAFT SUPPLIED ONLY WHEN SPECIFIED. KEY SIZE .188 X .188 X 1.00. TERMINAL BOX CAN BE ROTATED FOR LEAD OUTLET AT TOP, SIDES OR BOTTOM. TERMINAL BOX LOCATED ON OPPOSITE SIDE WHEN F-2, W-1, W-4, V-5, W-7, OR C-1 MOUNTING IS SPECIFIED. BOX LOCATED ON TOP WHEN SPECIFIED. MOTOR WEIGHT MAY VARY 15% FOR NON-STANDARD RATINGS AND/OR ACCESSORIES. IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.

DIMENSIONS ARE IN INCHES

FRAME	A	D(1)	E	G	H	HG	J	D	P	T	BA	K	FK		BK	FAJ	FAK(8)	XC(7)
													STD.	LG. (5)				
SC3210ATZ-LLC3212ATZ	15.50	8.00	6.25	.75	.69	2.25	3.00	17.00	18.00	3.12	5.25	6.75	7.94	10.44	4.00	13.00	14.500	1.25
SC3612ATZ-ULLC3612ATZ	17.50	9.00	7.00	.88	.81	2.62	3.50	19.00	20.00	3.12	5.88	7.25	8.56	10.31	4.62	15.25	16.750	1.25

FRAME	METHOD OF DRIVE	C		B		BS	2F	DRIVE END SHAFT AND KEY										WT. LBS.
		STD.	LG. (5)	STD.	LG. (5)			N	N-W	U(2)	V	R(3)	SQ.	LGTH.				
SC3210ATZ-LSC3210ATZ	(6)	40.36	43.06	28.31	30.81	13.38	20.00	5.50	5.25	2.625	5.00	2.275	6.25	4.00	1150			
MC3212ATZ-LMC3212ATZ	(6)	43.56	46.06	31.31	33.81	16.38	25.00	5.50	5.25	2.625	5.00	2.275	6.25	4.00	1245			
LC3212ATZ-LLC3212ATZ	(6)	45.56	48.06	33.31	35.81	18.38	25.00	5.50	5.25	2.625	5.00	2.275	6.25	4.00	1325			
MC3612ATZ-LMC3612ATZ	COUPLED	47.69	49.44	34.44	36.19	18.12	28.00	6.00	5.75	2.875	5.50	2.450	7.50	4.25	1740			
UMC3612ATZ-ULMC3612ATZ	BELTED	48.44	50.19	34.44	36.19	18.12	28.00	6.75	6.50	3.250	6.25	2.831	7.50	5.00	1750			
LC3612ATZ-LLC3612ATZ	COUPLED	51.44	53.19	38.19	39.94	21.88	28.00	6.00	5.75	2.875	5.50	2.450	7.50	4.25	1905			
ULC3612ATZ-ULLC3612ATZ	BELTED	52.19	53.94	38.10	39.94	21.88	28.00	6.75	6.50	3.250	6.25	2.831	7.50	5.00	1915			

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.


REV. DESC: CHANGE LAYOUT OF DRAWING		
REV. LTR: A	VERSION: 01	TDR: 0000007673
FILE: \RGG\00015\623	REVISED: 07:49:39 10/03/2012	BY: RCGWT
MTL: -		

BALDOR
DIMENSION DRAWING, SC3210ATZ - ULLC3612ATZ, TEFC, FOOT MTG
SH 1 of 1

609971-013

INDUSTRIAL DIRECT CURRENT MOTORS AND GENERATORS – RPM III

STEEL AND CAST IRON TERMINAL BOX DIMENSIONS
STANDARD SIZE AND ONE SIZE LARGER
FRAMES C3210ATZ THRU C3613ATZ



FRAME SIZE	MAX AMPS	STANDARD SIZE					STEEL TERMINAL BOX DIMENSIONS					ONE SIZE LARGER					PART NUMBER					
		AA(2)	AB	AC	AF	X	Y	AA(1)	AB	AC	AF	X	Y	AA(2)	AB	AC		AF	X	Y		
C3210ATZ	185	2	14.88	11.38	4.25	8.44	7.25	74874-R	3	15.31	12.06	4.25	8.44	7.25	74874-24-R	3	15.31	12.06	4.25	8.44	7.25	74874-24-R
C3212ATZ	269	3	15.31	12.06	4.25	8.44	7.25	74874-24-R	4	16.75	12.69	5.38	10.56	9.00	700308-3-R	4	16.75	12.69	5.38	10.56	9.00	700308-3-R
C3214ATZ	500	4	16.75	12.69	5.38	10.56	9.00	700308-3-R	5	21.00	15.88	6.50	12.10	14.62	702658-1-C	5	21.00	15.88	6.50	12.10	14.62	702658-1-C
C3612ATZ	185	2	15.88	12.38	4.25	8.44	7.25	74874-R	3	16.31	13.06	4.25	8.44	7.25	74874-24-R	3	16.31	13.06	4.25	8.44	7.25	74874-24-R
C3613ATZ	269	3	16.31	13.06	4.25	8.44	7.25	74874-24-R	4	17.75	13.69	5.38	10.56	9.00	700308-3-R	4	17.75	13.69	5.38	10.56	9.00	700308-3-R
C3613ATZ	500	5	22.00	15.88	6.50	12.10	14.62	702658-1-C	5	22.00	15.88	6.50	12.10	14.62	702658-1-C	5	22.00	15.88	6.50	12.10	14.62	702658-1-C

FRAME SIZE	MAX AMPS	STANDARD SIZE					CAST IRON TERMINAL BOX DIMENSIONS					ONE SIZE LARGER					PART NUMBER					
		AA(2)	AB	AC	AF	X	Y	AA(1)	AB	AC	AF	X	Y	AA(2)	AB	AC		AF	X	Y		
C3210ATZ	185	3	15.31	11.19	3.00	6.00	7.00	75460-R	3	15.31	11.56	3.62	7.88	9.25	76700-RB	3	15.31	11.56	3.62	7.88	9.25	76700-RB
C3212ATZ	269	4	16.62	12.44	4.12	9.50	10.50	76708-RR	5	19.44	14.19	7.00	12.75	15.00	76870-S	5	19.44	14.19	7.00	12.75	15.00	76870-S
C3214ATZ	500	5	19.44	14.19	7.00	12.75	15.00	76870-S	6	19.44	14.19	7.00	12.75	15.00	76870-R	6	19.44	14.19	7.00	12.75	15.00	76870-R
C3612ATZ	185	3	16.31	12.56	3.62	7.88	9.25	75460-R	3	16.31	12.56	3.62	7.88	9.25	76700-RB	3	16.31	12.56	3.62	7.88	9.25	76700-RB
C3613ATZ	269	4	17.62	13.44	4.12	9.50	10.50	76708-RR	5	17.62	13.44	4.12	9.50	10.50	76708-RR	5	17.62	13.44	4.12	9.50	10.50	76708-RR
C3613ATZ	500	5	20.44	15.19	7.00	12.75	15.00	76870-S	6	20.44	15.19	7.00	12.75	15.00	76870-S	6	20.44	15.19	7.00	12.75	15.00	76870-S

FRAME SIZE	MAX AMPS	STANDARD SIZE					OPTIONAL AUXILIARY CONDUIT BOX DIMENSIONS (MAXIMUM)					PART NUMBER
		AA	AB	AC	AF	X	AA (3)	Y	XX	XY	YY	
C320	400	19.02	15.28	6.20	14.39	---	14.39	706310-63-B				
	800	19.02	15.28	6.20	14.39	---	14.39	706310-63-B				
	1600	19.02	15.28	7.68	15.35	---	15.35	706310-63-C				
C360	400	20.00	15.28	6.20	14.39	---	14.39	706310-63-B				
	800	20.00	15.28	6.20	14.39	---	14.39	706310-63-B				
	1600	20.00	15.28	7.68	15.35	---	15.35	706310-63-C				

FRAME SIZE	XAB	XX	XY	XY	FRAME SIZE	XAB	XX	XY	XY	FRAME SIZE	XAB	XX	XY	XY	FRAME SIZE	XAB	XX	XY	XY
C320	10.00	4.25	4.25	602007-26-A	C320	13.50	8.00	8.00	706310-3-B	C360	14.50	8.00	8.00	706310-3-B					
C360	11.00	4.25	4.25	602007-26-A	C360	14.50	8.00	8.00	706310-3-B										

- (1) *AA* CONDUIT.
- (2) *AA* PIPE TAP.
- (3) CUSTOMER TO PROVIDE HOLE FOR CONDUIT.
- (4) TERMINAL BOX LOCATED ON OPPOSITE SIDE WHEN F-2, V-1, V-4, W-5, W-7.
- (5) TERMINAL BOX LOCATED ON TOP WHEN SPECIFIED.
- (6) TERMINAL BOX DIMENSIONS SEE 609979-2.
- (7) FOR *X/P* TERMINAL BOX DIMENSIONS SEE 609979-3.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: LOAD TO BUS	VERSION: 00	TDR: 000000958110
REV. LTR: -	REVISED: 08: 37: 45 12/17/2015	BY: RCGWT
FILE: \RGG\00026\318		
MTL: -		


BALDOR

DIM SHT,C3210ATZ THRU C3613ATZ,W/AUX C/BOX
SH 1 of 1

406770-002

406770-002

CONNECTION DIAGRAM
D-C MOTOR - STAB. SHUNT
DUAL VOLTAGE FIELD



1. CAUTION — ARMATURE AND SERIES FIELD MAY HAVE MULTIPLE LEADS. CONNECT ALL LUGS WITH THE SAME MARKING TOGETHER.
 2. OPTIONAL SERIES FIELD IS MARKED S3 AND S4. FOR CUMULATIVE SERIES FIELD, CONNECT S3 TO S2 AND CONNECT S4 TO NEGATIVE. FOR DIFFERENTIAL SERIES FIELD CONNECT S4 TO S2 AND S3 TO NEGATIVE.
 3. OPTIONAL CONTROL SIGNAL LEAD IS MARKED AX2. ALWAYS TAKE INTERPOLE DROP BETWEEN A2 AND AX2. NOTE: NEMA DESIGNATION FOR AX2 IS LETTER C.
 4. SPACE HEATERS, WHEN PROVIDED, WILL HAVE LEADS MARKED H1 AND H2, H3, H4, ETC.
 5. THERMAL PROTECTOR, WHEN PROVIDED, WILL HAVE LEADS MARKED P1 AND P2, P3, P4, ETC.
 6. WINDING RTD'S, WHEN PROVIDED, WILL HAVE LEAD MARKED W1.
 7. BRUSH WEAR SENSOR, WHEN PROVIDED, WILL HAVE LEAD MARKED W1.
 8. WARNING — MOTOR MUST BE GROUNDED TO PREVENT SERIOUS INJURIES TO PERSONNEL. GROUND THE MOTOR PER IEC, NATIONAL ELECTRICAL CODE AND ANY APPLICABLE LOCAL ELECTRICAL CODES. A TAPPED HOLE IS PROVIDED IN THE CONDUIT BOX, ON THE FOOT. FRAME BRACE OR OPPOSITE OPPOSITE DRIVE END BRACKET, ADJACENT TO THE TERMINAL BOX FOR MOTOR GROUNDING. GROUND LEAD, WHEN PROVIDED, WILL BE GREEN.
- CUSTOMER _____ S.O. NO. _____
RELIANCE
CUSTOMER ORDER NO. _____

REV. DESC: UPDATE LOGO AND TITLEBLOCK: LOADED TO BUS		
REV. LTR: -	VERSION: 00	TDR: 000000781086
FILE: \RSN\00026\434	REVISED: 02:35:07 02/01/2013	BY: MGHPC
MTL: -		



D-C MOTOR CONNECTION DIAGRAM STAB. SHUNT, DUAL VOLTAGE FIELD
SH 1 of 1