

ABB BALDOR RELIANCE III

Customer information packet

DM3542

.75HP, 1725RPM, 3PH, 60HZ, 56, 3428M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	1.400 A @ 460.0 V 2.800 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	74.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	P
Type	AC
Mech. spec.	34M812
Base	
Status	PRD/A
Elec. spec.	34WGR422
Layout	34LYM812
Eff. date	05-21-2025
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	07-25-2016

High Voltage Full Load Amps	1.4 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Max Speed	2700 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3428M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.85 IN
Power Factor	68
Product Family	Dirty Duty Plus
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3659									
CAT.NO.	DM3542								
SPEC.	34M812R422G1				ENCL		TEFC		
FRAME	56	H.P.		.75					
VOLTS	230/460								
AMPS	2.8/1.4				IP		56		
R.P.M.	1725								
HZ.	60	PH.		3	CLASS		F		
SER.F.	1.25	DES.		B	CC				
NEMA NOM. EFF.	74								
RATING	40C AMB-CONT								
DE	6203	ODE		6203					
GREASE	POLYREX EM								
SN									
	50C AT 1.0 SF								
	SFA 3.2/1.6								

AC Induction Motor Performance Data

Record # 58333

Typical performance - not guaranteed values

Winding: 34WGR422-R001			Type: 3428M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		.75	Full Load Torque		2.28 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		2.8/1.4	Breakdown Torque		10 LB-FT		
R.P.M.		1725	Pull-up Torque		7.67 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		11.8 LB-FT	
NEMA Design Code		B	KVA Code	N	Starting Current		11.1 A
Service Factor (S.F.)		1.25	No-load Current		1.04 A		
NEMA Nom. Eff.		74	Power Factor	68	Line-line Res. @ 25°C		17.999 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		60°C
S.F. Amps		3.2/1.6	Temp. Rise @ S.F. Load		70°C		
			Locked-rotor Power Factor		55.7		

Load Characteristics 460 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	33	48	60	68	75	79	75
Efficiency	50.2	65.5	71.3	74.1	75.2	75	75.2
Speed	1783.6	1770.3	1757	1742.7	1726.6	1709.9	1727
Line amperes	1.07	1.15	1.25	1.39	1.57	1.76	1.57

ABB Motors and Mechanical Inc.

WINDING # 34WGR422

Typical performance - not guaranteed values.

0.75 HP 3 PH 60 HZ 1725 RPM 460 V 3428M

TORQUES (LB-FT): PO=10 PU=7.67 LR=11.8 LRA=11.1





