

ABB BALDOR RELIANCE III

Customer information packet

DMG2315

0259AT, 15KW, 1750RPM, 230, 230, DPFG, F2

Specifications

Armature Voltage	230 V
Base Speed	1750 rpm
Enclosure	DPFG
Field Voltage	230 V
Output Power	15.000 KW
Agency Approvals	CSA
Ambient Temperature	40 °C
Armature Current	65.0 a
Base Indicator	Rigid
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Field Winding Type	COMPOUND
Heater Indicator	No Heater
Insulation Class	F
Lifting Lugs	Standard Lifting Lugs
Motor Standards	NEMA
Mounting Arrangement	F2
Overall Length	28.00 IN
Service Factor	1.00
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Slinger Indicator	No Slinger
Thermal Device - Bearing	None

Part Detail

Revision	E
Type	DC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	K0041A
Layout	1486
Eff. date	12-04-2025
CD Diagram	
Poles	00
Leads	
Proprietary	False
Created date	11-12-2019

Nameplate

15405									
CAT.NO.			MODEL NO.		T25S8009				
KW	15KW	RPM	1750		FRAME		0259AT		
ARM VOLTS	230		ARM AMPS	65.00		WOUND		STD COMPOUND	
FIELD VOLTS	230		FIELD AMPS	1.33					
FIELD CONN.			OHMS	115.0		INSUL. CLASS			F
ENCL	DPFG	DUTY	CONT		MAX AMBIENT			40	
SERVICE FACTOR	1.0								
S/N			E/S	K0041A					
	BRUSH:150986-25-1								
	IP23								
O.D.E. BRG.	6207	D.E. BRG.	6209	BRUSH		150986-25-1			QTY



000613006SC

KG

Accessories

Part number	Description	Multiplier
92EP5000A01	C-FACE CONVERSION KIT FOR STOCK MTR,FR 2	

REL S.O.	FRAME	RATING	RPM	ARM. VOLTS	ARM. AMPS
	259	15.0HP	1750	230	65.0
WINDING TYPE		S.F.	ENCL.	AMB °C/INSUL	DUTY
STAB. SHUNT		1.0	DPG	40/F	CONT
POWER CODE		TYPE	WK ² (LB-FT ²)	HOT ARM.CIR.RES.	FLD. AMPS@25 °C
D		T	2.686	.401	2.00
ARM. CIR. IND. (mh)		FIELD IND. (H)	COOLING AIR (CFM/IN H ² O)		TEST DATE
5.12		91.9	-/-		-
LOAD PERFORMANCE					
LOAD	AMPERES	TORQUE IN OZ.-FT.	OUTPUT IN HP	RPM	% EFFICIENCY
NO LOAD	552	0	0	1533	0
1/4	16	0	0	1452	0
2/4	33	0	0	1378	0
3/4	49	0	0	1322	0
4/4	65	0	0	1261	0
O.L.	98	0	0	1171	0
RPM VS. FIELD AMPS					
FIELD AMPS	RPM N.L.	RPM F.L.	Eg N.L. @ BASE SPEED	Eg F.L. @ BASE SPEED	
1.33	1532	1261	259	248	
1.09	1681	1699	238	225	
.858	1944	1811	207	195	
.620	2481	1990	162	156	
.382	3824	2300	105	108	
REMARKS: TYPICAL DATA					
		DR. BY E.H.GILLOT CK. BY B. GRANT APP. BY R.ERLACHER DATE 01-23-2009		D-C MOTOR PERFORMANCE DATA DK0041A ISSUE DATE 01-23-2009	



1486

FOOT MOUNTING							D.E. SHAFT EXTENSION					DRIVE KEY		FRAME					
FRAME	BA	E	2F	G	H	J	N	N-W	U	V	W	KEY-SQ.	KEY-LONG	A	B	C	D	O	P
1810AT	2.75	3.75	11.00	.38	.406	1.50	2.90	2.77	1.125 ¹	2.50 ³	.13	.250	1.38	8.75	12.25	21.46	4.50 ²	9.00	9.00
219AT	3.50	4.25	11.00	.50	.406	2.00	3.00	2.75	1.375 ¹	2.50 ³	.25	.312	1.75	10.38	12.00	24.50	5.25 ²	10.47	10.44
258AT	4.25	5.00	12.50	.69	.531	2.25	3.44	3.25	1.625 ¹	3.00 ³	.19	.375	2.31	12.38	14.00	26.50	6.25 ²	12.47	12.44
259AT	4.25	5.00	14.00	.69	.531	2.25	3.44	3.25	1.625 ¹	3.00 ³	.19	.375	2.31	12.38	15.50	28.00	6.25 ²	12.47	12.44
288AT	4.75	5.50	14.00	.69	.531	2.50	3.91	3.75	1.875 ¹	3.50 ³	.16	.500	2.50	13.81	15.62	32.00	7.00 ²	13.88	13.75
328AT	5.25	6.25	16.00	.81	.656	3.00	4.40	4.25	2.125 ¹	4.00 ³	.15	.500	3.12	15.88	17.75	34.63	8.00 ²	15.94	15.88
329AT	5.25	6.25	18.00	.81	.656	3.00	4.40	4.25	2.125 ¹	4.00 ³	.15	.500	3.12	15.88	19.75	36.63	8.00 ²	15.94	15.88

CONDUIT BOX							APPROXIMATE WEIGHT
FRAME	AA	AB	AC	AF	BS	XL	
1810AT	3/4NPT	INTEGRAL WITH ENDPLATE					195
219AT	3/4-1	7.91	6.44	2.44	9.38	3.81	260
258AT	1-1/4	9.35	7.72	2.94	9.75	4.94	366
259AT	1-1/4	9.35	7.72	2.94	11.25	4.94	411
288AT	1-1/4	11.88	9.25	5.00	12.64	7.88	566
328AT	2	12.94	10.32	5.00	13.68	7.88	775
329AT	2	12.94	10.32	5.00	15.68	7.88	884

- 1) SHAFT DIAMETERS TO 1.500 TOLERANCE +.0000 - .0005
SHAFT DIAMETERS ABOVE 1.500 TOLERANCE +.0000 - .0010
SHAFT DIAMETERS TO 1.625 RUNOUT .002 T.I.R. MAX.
SHAFT DIAMETERS ABOVE 1.625 RUNOUT .003 T.I.R. MAX.
- 2) 'D' DIMENSION TOLERANCE +.000 - .030
- 3) 'V' DIMENSION IS MAX. HUB LENGTH ON SHAFT
- 4) CONDUIT BOX CAN BE ROTATED IN 90° STEPS ON ITS OWN AXIS.
- 5) ALL DIMENSIONS NOT NOTED ARE NOMINAL DIMENSIONS CONSULT FACTORY FOR TOLERANCES.

 FOR F1 OR F2 CONDUIT BOX
LOCATION SEE SALES ORDER

1486

MATL: -			
REV:	C	CORRECTED "A" DIMENSIONS	
9871		SCALE: 0.08	BY: TBM
		FILE: CHB00003091	REVISED: 09/10/96
		TDR: 0104915	

BALDOR ELECTRIC Co.

DIM SHEET, 1810AT THRU 329AT GENERATORS