ABB BALDOR RELIANCE

Customer information packet

DRX14244T

2/1.5HP, 1765//1455RPM, 3PH, 60//50HZ, 145T
Class - CLI GP C,D
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 12:07:58 PM

Specifications

Enclosure	XPFC
Frame	145T
Frame Material	Steel
Frequency	50.00 Hz
	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	190.0 V @ 50 HZ
	460.0 V @ 60 HZ
	380.0 V @ 50 HZ
Agency Approvals	CSA EEV
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	5.600 A @ 230.0 V
	5.800 A @ 208.0 V
	5.200 A @ 190.0 V
	2.800 A @ 460.0 V
	2.600 A @ 380.0 V
Design Code	B
Drip Cover	No Drip Cover

Part Detail

Revision	E
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	35WGG073
Layout	35LYX081
Eff. date	08-17-2023
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	10-28-2021

Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	2.6 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3528M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	15.09 IN
Power Factor	77
Product Family	General Purpose
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP1401XPSLEV											
NO.				**CC**	010A						
S/N				**TEMP CODE**	T3C						
SPEC.	35-0000-1353			**INV.TYPE**	PWM						
CAT.NO.	DRX14244T			**C HP FR**	60	**C HP TO**	90				
HP	2/1.5			**CT HZ FROM**	6			**CT HZ TO**	60		
VOLTS	230/460//190/380			**VT HZ FROM**	6			**VT HZ TO**	60		
AMPS	5.6/2.8//5.2/2.6			**MAG CUR**	3.2/1.6						
RPM	1760//1465			**MX RPM**	2700						
HZ	60//50	**PH**	3	**CL**	F	**NOM.EFF.**	86.5				
SER.F.	1.00	**DES**	B	**SL HZ**	1.3	**WK2**	0.202				
FRAME	145T	**RATING**	40C AMB-CONT								
	55C AMB @ 1.0 SF										
	1.15 SF SINEWAVE				NEMA MG-1 PT 5, IP55						

AC Induction Motor Performance Data
Record # 87414
Typical performance - not guaranteed values


Winding: 35WGG073-R008	**Type:** 3528M	**Enclosure:** XPFC

Nameplate Data			
Rated Output (HP)			2//1.5
Volts			230/460//190/380
Full Load Amps			5.6/2.8//5/2.5
R.P.M.			1760//1456
Hz	60//50	**Phase**	3
NEMA Design Code	B	**KVA Code**	L
Service Factor (S.F.)			1
NEMA Nom. Eff.	86.5	**Power Factor**	74
Rating - Duty			40C AMB-CONT

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	5.99 LB-FT
Start Configuration	direct on line
Breakdown Torque	20.5 LB-FT
Pull-up Torque	13.8 LB-FT
Locked-rotor Torque	15 LB-FT
Starting Current	22.5 A
No-load Current	1.62 A
Line-line Res. @ 25ºC	9.54 Ω
Temp. Rise @ Rated Load	64°C
Locked-rotor Power Factor	57.9
Rotor inertia	0.202 lb-ft²

Load Characteristics 460 V, 60 Hz, 2 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	35	55	68	76	81	84
Efficiency	78.2	85.3	86.8	86.5	85.4	83.6
Speed	1791	1782	1771	1760	1748	1734
Line amperes	1.71	1.97	2.34	2.82	3.36	3.97


ABB Motors and Mechanical Inc.
WINDING # 35WGG073
Typical performance - not guaranteed values.
2 HP 3 PH 60 HZ 1760 RPM 460 V 3528M
TORQUES(LB-FT): PO=20.5 PU=13.8 LR=15 LRA=22.5
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (2 HP)
11/16/2026 ACPERF, record # 87414

AC Induction Motor Performance Data
Record # 87415
Typical performance - not guaranteed values


Winding: 35WGG073-R008	**Type:** 3528M	**Enclosure:** XPFC


Nameplate Data			
Rated Output (HP)			2//1.5
Volts			230/460//190/380
Full Load Amps			5.6/2.8//5/2.5
R.P.M.			1760//1456
Hz	60//50	**Phase**	3
NEMA Design Code	B	**KVA Code**	L
Service Factor (S.F.)			1
NEMA Nom. Eff.	86.5	**Power Factor**	74
Rating - Duty			40C AMB-CONT

380 V, 50 Hz: High Voltage Connection	
Full Load Torque	5.4 LB-FT
Start Configuration	direct on line
Breakdown Torque	18.6 LB-FT
Pull-up Torque	13.3 LB-FT
Locked-rotor Torque	14.4 LB-FT
Starting Current	21 A
No-load Current	1.58 A
Line-line Res. @ 25ºC	9.54 Ω
Temp. Rise @ Rated Load	58°C
Locked-rotor Power Factor	63.3
Rotor inertia	0.202 lb-ft²


Load Characteristics 380 V, 50 Hz, 1.5 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	33	53	67	75	81	84
Efficiency	75.7	83.6	85.4	85.3	84.1	82.2
Speed	1492	1484	1474	1464	1453	1440
Line amperes	1.66	1.88	2.2	2.63	3.12	3.68


ABB Motors and Mechanical Inc.
WINDING # 35WGG073
Typical performance - not guaranteed values.
1.5 HP 3 PH 50 HZ 1464 RPM 380 V 3528M
TORQUES(LB-FT): PO=18.6 PU=13.3 LR=14.4 LRA=21
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (1.5 HP)
11/16/2026 ACPERF, record # 87415


35LYX081
510-520 = 14.22
521-528 = 15.09
529-535 = 15.97
536 - 546 = 17.34
2.60
2.25
.19 KEY
1.38 LONG
Ø7.19
X-PROOF NAMEPLATE
FOR HAZARDOUS LOCATIONS
Ø .8750
.8745
DRAINS
(EACH END)
4.60
4.00
2.25
5.00
.50
5.94
6 HOLES
.38 WIDE
6.67
7.21
7.08
3.50
3.44
LEAD HOLE
.75 N.P.T.
2.75
2.75
4.82
3.25
6.50
.0015 MAX
CLEARANCE
(EACH END)
.09
.38
.019 MAX
DIAMETRICAL
CLEARANCE
.006
.004
.37
1.00
(MIN)
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD TO SOLIDWORKS
REV: D
VERSION: 04
REVISED: 01:07:11 08/30/2019
TDR: 000001117187
MODEL NO. 35LYX081
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
HORZ 143-5T XPFC 35M CL-I GP-C&D, DRILL RIG W/FACE DRAINS
35LYX081

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS