ABB BALDOR RELIANCE

Customer information packet

DRX32524T

50HP, 3560//2960RPM, 3PH, 60HZ, 326TS, XPFC, F
Class - CLI GP C,D
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 9:24:12 AM

Specifications

Enclosure	XPFC
Frame	326TS
Frame Material	Iron
Frequency	50.00 Hz
	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	40.000 HP @ 50 HZ
	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	380.0 V @ 50 HZ
	230.0 V @ 60 HZ
	190.0 V @ 50 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	56.000 A @ 460.0 V
	54.000 A @ 380.0 V
	122.000 A @ 208.0 V
	112.000 A @ 230.0 V
	108.000 A @ 190.0 V
Design Code	A
Drip Cover	No Drip Cover

Part Detail

Revision	F
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	12WGY587
Layout	12LY-000-232
Eff. date	11-22-2024
CD Diagram	CD0180
Poles	02
Leads	9#8
Proprietary	False
Created date	05-30-2019

Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	54.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1264M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	30.50 IN
Power Factor	89
Product Family	Hazardous Location Motor
Pulley Face Code	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3560 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1401XPSLEV											
NO.				**CC**	010A						
S/N				**TEMP CODE**	T3C						
SPEC.	12-0000-0682			**INV.TYPE**	PWM						
CAT.NO.	DRX32524T			**C HP FR**	60	**C HP TO**	90				
HP	50//40			**CT HZ FROM**	6			**CT HZ TO**	60		
VOLTS	230/460//190/380			**VT HZ FROM**	6			**VT HZ TO**	60		
AMPS	112/56//108/54		**MAG CUR**	36/18							
RPM	3560//2960		**MX RPM**	5400							
HZ	60//50	**PH**	3	**CL**	F	**NOM.EFF.**	93				
SER.F.	1.00	**DES**	A	**SL HZ**	0.7	**WK2**	5.01				
FRAME	326TS	**RATING**	40C AMB-CONT								
	55C AMB @ 1.0 SF, 60C RISE										
	1.15SF ON SINEWAVE			NEMA MG-1 PT.5,IP55							

AC Induction Motor Performance Data
Record # 66213
Typical performance - not guaranteed values

Winding: 12WGY587-R004	**Type:** 1264M	**Enclosure:** XPFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			50	**Full Load Torque**	74.1 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			112/56	**Breakdown Torque**	287 LB-FT
R.P.M.			3560	**Pull-up Torque**	107 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	137 LB-FT
NEMA Design Code	A	**KVA Code**	K	**Starting Current**	505 A
Service Factor (S.F.)			1	**No-load Current**	17.6 A
NEMA Nom. Eff.	93	**Power Factor**	89	**Line-line Res. @ 25ºC**	0.08644 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	53°C
				Locked-rotor Power Factor	21.5
				Rotor inertia	4.98 LB-FT2

Load Characteristics 460 V, 60 Hz, 50 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	58	79	86	90	90	91
Efficiency	91.5	94.3	94.8	94.6	94.1	93.5
Speed	3590	3580.8	3570.3	3560.2	3549.3	3538.6
Line amperes	22.4	31.8	43.5	55.6	69	82.4


ABB Motors and Mechanical Inc.

WINDING # 12WGY587

50 HP 3 PH 60 HZ 3560 RPM 460 V 1264M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=287 PU=107 LR=137 LRA=505



AC Induction Motor Performance Data
Record # 75687
Typical performance - not guaranteed values

Winding: 12WGY587-R003	**Type:** 1264M	**Enclosure:** XPFC

Nameplate Data			
Rated Output (HP)			50//40
Volts			230/460//190/380
Full Load Amps			112/56//108/54
R.P.M.			3560//2960
Hz	60//50	**Phase**	3
NEMA Design Code	A	**KVA Code**	K
Service Factor (S.F.)			1
NEMA Nom. Eff.	93	**Power Factor**	89
Rating - Duty			40C AMB-CONT
S.F. Amps			

380 V, 50 Hz: High Voltage Connection	
Full Load Torque	71.22 LB-FT
Start Configuration	direct on line
Breakdown Torque	278 LB-FT
Pull-up Torque	113 LB-FT
Locked-rotor Torque	145 LB-FT
Starting Current	495 A
No-load Current	17.33 A
Line-line Res. @ 25ºC	0.0846 Ω
Temp. Rise @ Rated Load	49°C
Temp. Rise @ S.F. Load	60°C
Locked-rotor Power Factor	24.1
Rotor inertia	4.98 LB-FT2

Load Characteristics 380 V, 50 Hz, 40 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	57	78	86	89	90	91
Efficiency	92.7	94.9	95	94.6	94	93.3
Speed	2991	2982	2972	2962	2952	2942
Line amperes	21.78	30.84	42.08	53.81	66.82	79.96


ABB Motors and Mechanical Inc.


WINDING # 12WGY587

40 HP 3 PH 50 HZ 2962 RPM 380 V 1264M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=278 PU=113 LR=145 LRA=495




12LY-000-232
(1232-1272) = 30.56
15.56
4.02
3.75
Ø16.94
.50 KEY
2.00 LONG
Ø1.875
1.874
METAL
SLINGER
(EA. END)
.38-16 TAP
8 HOLES
Ø.66
10.50
10.50
12.00
14.00
1.00
5.25
17.42
17.42
8.70
3.00
16.92
8.00 +.00 -.06
3.62
1.00
6.25
6.25
12.48
7.25
14.50
LEAD HOLE
2.00 NPT
DRAIN FITTING
HW50A02 W/
HW302306 (PIN)
(EA END)
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD TO SWD DRAWING
REV: C
VERSION: 03
REVISED: 02:59:10 04/01/2024
TDR: 000001227248
MODEL NO. 12LY-000-232
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
HORZ XPFC 324-6TS CL.I GP.C&D W/GRSR & DRILL RIG FEATURES
12LY-000-232

CD0180





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1