ABB BALDOR RELIANCE

Customer information packet

DRX40144T

100HP, 1785RPM, 3PH, 60HZ, 405T, TEFC, F1
Class - CLI GP C,D
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/18/2026 12:20:53 PM

Specifications

Enclosure	TEFC
Frame	405T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	100.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	UL
	CSA
	CCSAUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	6-60
Current @ Voltage	112.000 A @ 460.0 V
	224.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.4 %
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	112.0 a
Insulation Class	F
Inverter Code	Inverter Ready

Part Detail

Revision	A
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A40WG0692
Layout	617433-608
Eff. date	05-06-2024
CD Diagram	416820-002
Poles	04
Leads	3#2,6#4
Proprietary	False
Created date	03-08-2019

IP Rating	NONE
KVA Code	G
Max Speed	3600 rpm
Motor Lead Quantity/Wire Size	3 @ 2 AWG
Motor Standards	NEMA
Motor Type	A40064M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	38.22 IN
Power Factor	87
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	2.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1785 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat

Nameplate

NP2496L
MOBIL POLYREX EM

000613006PC			
CLASS I GROUP	C D X	**NO.**	
CLASS II GROUP	X X X		
OPERATING TEMP CODE	T3C		

NP3140L											
SPEC NO.	A40-7255-0692			**CAT.NO.**	DRX40144T				**FRAME**	405T	
HP	100	**VOLTS**	230/460		**PHASE**	3	**DESIGN**	B	**TYPE**	P	
RPM	1785	**AMPS**	224/112		**HZ**	60	**AMB**	40	**SF**	1.00	
DRIVE END BEARING	80BC03J30X			**DUTY**	CONT		**INSUL.CLASS**	F			
OPP D.E. BEARING	80BC03J30X			**ENCL**	TEFC	**CODE**	G				
SF	1.15	**WK2**	26.346	**MAG CUR**	28.6		**RPM MAX**	3600			
CT HZ	6-60	**VT HZ**	0-60	**CHP HZ**	60-90		**NEMA-NOM-EFF**	95.4			
	SUIT FOR 55C AMB AT 1.00 SF				IP55						
SER.NO.				**MOTOR WEIGHT**							

REL. S.O.	FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS
	405HP	100	P	3/60	1785	230/460

AMPS	DUTY	AMB °C/ INSUL.	S.F.	NEMA DESIGN	CODE LETTER	ENCL.
224/112	CONT	40/F	1.15	B	G	TEFC

E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES.@25 °C OHMS (BETWEEN LINES)
596956	418142-33-RE	---	---	.0123/.0492

PERFORMANCE

LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY
NO LOAD	0	28.6	1800	5.49	0
1/4	25.0	39.2	1796	64.3	93.0
2/4	50.0	59.5	1792	82.5	95.4
3/4	75.0	84.6	1788	86.7	95.7
4/4	100	112	1783	87.4	95.4
5/4	125	141	1778	87.3	94.9

SPEED TORQUE

	RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES
LOCKED ROTOR	0	151	445	725
PULL UP	360	136	400	706
BREAKDOWN	1721	250	735	382
FULL LOAD	1783	100	295	112

AMPERES SHOWN FOR 460. VOLT CONNECTION. IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE

REMARKS: TYPICAL DATA
XE MOTOR-DATA-NEMA NOM. EFF. 95.4 PCT
GUARANTEED MIN EFF. 94.5 PCT


BALDOR
A MEMBER OF THE ABB GROUP

DR. BY G. R. WEBB
CK. BY W. L. SMITH
APP. BY W. L. SMITH
DATE 01/19/12

A-C MOTOR PERFORMANCE DATA

A40WG0692-R004
ISSUE DATE 08/06/20

REL S.O.		RPM	1785	S.F.	1.15	ROTOR	418142-33-RE
FRAME	405HP	VOLTS	230/460	NEMA DESIGN	B	TEST S.O.	TYPICAL DATA
HP	100	AMPS	224/112	CODE LETTER	G	TEST DATE	---
TYPE	P	DUTY	CONT	ENCLOSURE	TEFC	STATOR RES.@ 25 °C	.0123/.0492
PHASE/HERTZ	3/60	AMB °C/INSUL	40/F	E/S	596956		OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.


BALDOR
A MEMBER OF THE ABB GROUP

DR. BY	G. R. WEBB
CK. BY	W. L. SMITH
APP. BY	W. L. SMITH
DATE	01/19/12

A-C MOTOR PERFORMANCE CURVES A40WG0692-R004

ISSUE DATE 08/06/20

REL. S.O.		RPM	1785	S.F.	1.15	ROTOR	418142-33-RE
FRAME	405HP	VOLTS	230/460	NEMA DESIGN	B	TEST S.O.	TYPICAL DATA
HP	100	AMPS	224/112	CODE LETTER	G	TEST DATE	---
TYPE	P	DUTY	CONT	ENCLOSURE	TEFC	STATOR RES.@ 25 °C.	.0123/.0492
PHASE/HERTZ	3/60	AMB °C/INSUL	40/F	E/S	596956		OHMS (BETWEEN LINES)



REMARKS:

THERMAL LIMIT CURVE

XE MOTOR-DATA-NEMA NOM. EFF. 95.4 PCT

GUARANTEED MIN EFF. 94.5 PCT

AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

BALDOR
A MEMBER OF THE ABB GROUP

DR. BY	G. R. WEBB
CK. BY	W. L. SMITH
APP. BY	W. L. SMITH
DATE	01/19/12

A-C MOTOR PERFORMANCE CURVES

A40WG0692-R004

ISSUE DATE 08/06/20

DUTY MASTER ALTERNATING CURRENT MOTORS

617433-608

ENCLOSURE: X/P, UNDERWRITERS LISTED


SQUIRREL-CAGE INDUCTION


MOUNTING: FOOT, F-1 MOUNT


G405T/G404T FRAME MOUNTING HOLES


CL. 1, GRP. C & D

COOLING: FAN COOLED









DIMENSIONS ARE IN INCHES.
WEIGHT: 1400 LBS ± 15% DEPENDING ON RATING.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: NEW DRAWING			
REV: -	VERSION: 00	REVISED: 02:53:03 03/08/2019	TDR: 000001101608
MODEL NO. 617433-608			REF:
BY: USJEDIL	Material:		C

BALDOR


G405/404T TEFC XP F1 FOOT/CAST IRON BOX/CL.1 GRP C & D

617433-608

SHEET NUMBER 1 OF 1


617433-608


1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.


CONNECTION DIAGRAM
ACCESSORIES
MOTOR WINDING THERMOSTATS
CONTACTS @ °C
FIGURE NUMBER
CONTACT RATING
VOLTS
CONTINUOUS AMPERES
INRUSH AMPERES
110-120 3.0 30
220-240 1.5 15
440-480 0.75 7.5
550-600 0.60 6.0
418174-006
THERMOSTATS
NORMALLY CLOSED
NORMALLY OPEN
FIGURE 1
FIGURE 2
FIGURE 3
FIGURE 4
FIGURE 5
FIGURE 6
FIGURE 7
FIGURE 8
P1
P2
CUSTOMER
CUSTOMER ORDER NO.
S.O. NO.
418174-006
REV. DESC: LOADED TO BUS
REV. LTR: A
VERSION: 01
TDR: 000000570390
FILE: \RAG\00013\849
REVISED: 10:16:21 12/07/2010
BY: RAGDRF
MTL: -
BALDOR
A-C MOTOR CONNECTION ACCESSORIES
SH 1 of 1

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED





(N. P. 1575-B)

REV. DESC: ADJUST TEXT DARKNESS		
REV. LTR: B	VERSION: 02	TDR: 000001285318
FILE: \RAG\00022\453	REVISED: 09:36:26 09/24/2026	BY: USJOSUL
MTL: –		

ABB

CONN DIAG – STANDARD 9 LEAD, DELTA-CONNECTED

SH1 of 1

416820-002