

ABB BALDOR RELIANCE III

Customer information packet

DRX441264T

125HP, 1190RPM, 3PH, 60HZ, 445T, TEFC, F1

Class - CLI GP C,D

Division - Division I

Specifications

Enclosure	TEFC
Frame	445T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	125.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	UL CSA CCSAUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	10-60
Current @ Voltage	144.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.0 %
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	144.0 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	G

Part Detail

Revision	A
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A44WG2120
Layout	617426-001
Eff. date	05-06-2024
CD Diagram	416820-036
Poles	06
Leads	3#1
Proprietary	False
Created date	03-11-2019

Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	3 @ 1 AWG
Motor Standards	NEMA
Motor Type	A44076M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	44.97 IN
Power Factor	86
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	3.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1190 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat

Nameplate

NP2496L
MOBIL POLYREX EM

000613006PC

CLASS I GROUP	C D X	NO.	
----------------------	-------	------------	--

CLASS II GROUP	X X X		
-----------------------	-------	--	--

OPERATING TEMP CODE	T3C		
----------------------------	-----	--	--

NP3140L

SPEC NO.	A44-9130-2120			CAT.NO.	DRX441264T			FRAME	445T
HP	125	VOLTS	460	PHASE	3	DESIGN	B	TYPE	P
RPM	1190	AMPS	144	HZ	60	AMB	40	SF	1.00
DRIVE END BEARING	90BC03J30X		DUTY	CONT	INSUL.CLASS		F		
OPP D.E. BEARING	90BC03J30X		ENCL	TEFC	CODE	G			
SF	1.15	WK2	59.4	MAG CUR	51.4	RPM MAX	2700		
CT HZ	10-60	VT HZ	0-60	CHP HZ	60-90	NEMA-NOM-EFF	95		
	SUIT FOR 55C AMB AT 1.00 SF					IP55			
SER.NO.				MOTOR WEIGHT					

REL. S.O.	FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS
	445T	125	P	3/60	1190	460
AMPS	DUTY	AMB °C/ INSUL.	S.F.	NEMA DESIGN	CODE LETTER	ENCL.
144	CONT	40/F	1.15	B	G	TEFC
E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES. @25 °C OHMS (BETWEEN LINES)		
599769	418143-080-GE	---	---	.0408		

PERFORMANCE

LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY
NO LOAD	0	51.4	1200	4.76	0
1/4	31.3	61.8	1197	51.7	91.6
2/4	62.5	84.2	1195	73.5	94.6
3/4	93.7	112	1192	82.2	95.1
4/4	125	144	1189	85.8	95.0
5/4	156	178	1185	87.1	94.5

SPEED TORQUE

	RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES
LOCKED ROTOR	0	141	777	911
PULL UP	180	127	701	893
BREAKDOWN	1143	277	1528	513
FULL LOAD	1189	100	552	144

AMPERES SHOWN FOR 460. VOLT CONNECTION. IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE


REMARKS: TYPICAL DATA
XE - MOTOR; NEMA NOM. EFF.= 95.0 PCT.; GUAR MIN .
EFF.= 94.1 PCT.



DR. BY M.C. BENTON
CK. BY S.E. WALLACE
APP. BY E.J. CHRISTIAN
DATE 04/09/90

**A-C MOTOR
PERFORMANCE A44WG2120-R032
DATA** ISSUE DATE 04/30/21

REL S.O.	RPM 1190	S.F. 1.15	ROTOR 418143-080-GE
FRAME 445T	VOLTS 460	NEMA DESIGN B	TEST S.O. TYPICAL DATA
HP 125	AMPS 144	CODE LETTER G	TEST DATE ---
TYPE P	DUTY CONT	ENCLOSURE TEFC	STATOR RES. @ 25 °C .0408
PHASE/HERTZ 3/60	AMB °C/INSUL 40/F	E/S 599769	OHMS (BETWEEN LINES)




AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.



DR. BY M.C. BENTON
 CK. BY S.E. WALLACE
 APP. BY E.J. CHRISTIAN
 DATE 04/09/90

**A-C MOTOR
 PERFORMANCE CURVES**
 A44WG2120-R032
 ISSUE DATE 04/30/21

REL. S.O.	RPM 1190	S.F. 1.15	ROTOR 418143-080-GE
FRAME 445T	VOLTS 460	NEMA DESIGN B	TEST S.O. TYPICAL DATA
HP 125	AMPS 144	CODE LETTER G	TEST DATE ---
TYPE P	DUTY CONT	ENCLOSURE TEFC	STATOR RES. @ 25 °C .0408
PHASE/HERTZ 3/60	AMB °C/INSUL 40/F	E/S 599769	OHMS (BETWEEN LINES)



THERMAL LIMIT CURVE


REMARKS: EFF. = 94.1 PCT. T CURVE


AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.



DR. BY M.C. BENTON
 CK. BY S.E. WALLACE
 APP. BY E.J. CHRISTIAN
 DATE 04/09/90


**A-C MOTOR
PERFORMANCE
CURVES** **A44WG2120-R032**
 ISSUE DATE 04/30/21 Page 9 of 13





416820-036

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575-BA)

416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682	REVISED: 11: 54: 06 04/30/2010	
MTL: -	BY: RAGRA	

BALDOR
CONN DIAG - STANDARD 3 LEAD
SH 1 of 1

CONNECTION DIAGRAM ACCESSORIES

MOTOR WINDING THERMOSTATS	
CONTACTS _____ @ _____ °C	
FIGURE NUMBER _____	
CONTACT RATING	
VOLTS	CONTINUOUS AMPERES
110-120	3.0
220-240	1.5
440-480	0.75
550-600	0.60
	INRUSH AMPERES
	30
	15
	7.5
	6.0

NORMALLY CLOSED	THERMOSTATS	NORMALLY OPEN
 FIGURE 1		 FIGURE 4
 FIGURE 2		 FIGURE 5
 FIGURE 3		 FIGURE 6
 FIGURE 7		 FIGURE 8

CUSTOMER _____ CUSTOMER ORDER NO. _____ S.O. NO. _____

418174-006

418174-006

REV. DESC: LOADED TO BUS		
REV. LTR: A	VERSION: 01	TDR: 000000570390
FILE: \RAG\00013\849	REVISED: 10:16:21 12/07/2010	BY: RAGDRF
MTL: -		

BALDOR

A-C MOTOR CONNECTION ACCESSORIES

SH 1 of 1