

ABB BALDOR RELIANCE III

Customer information packet

ECP2276T-5

7.5HP, 1180RPM, 3PH, 60HZ, 254T, 0954M, TEFC, F

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	254T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1.0
Current @ Voltage	8.700 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part Detail

Revision	AY
Type	AC
Mech. spec.	09J371
Base	
Status	PRD/A
Elec. spec.	09WGY264
Layout	09LYJ371
Eff. date	09-16-2025
CD Diagram	CD0006
Poles	06
Leads	3#12
Proprietary	False
Created date	08-29-2010

Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	8.7 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0954M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	24.78 IN
Power Factor	71
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3995ABBL													
CAT #		ECP2276T-5				SER				CC		010A	
SPEC		09J371Y264				RATING		40C AMB-CONT					
HZ	VOLTS		AMPS		RPM	HP	CODE	SF	DES	PF	NEMA NOM. EFF		
60	575		8.7		1180	7.5	J	1.15	A	71	%	91.7	%
											%		%
PH	3	CL	F	MAX RPM	1800	MAX CORR KVAR		4	USABLE AT 208V		N/A		
IP55		FR	254T	ENCL	TEFC	DE BRG		6309	ODE BRG		6309		
GREASE		POLYREX EM				MTR WT		333	LBS				
USABLE AT		N/A											
CL I DIV 2 GRPS A,B,C,D				CL I ZONE 2 GRPS				IIA,IIB,IIC		TEMP T	160	C	
1.0 SF ON PWM INVERTER				POWER		INV TEMP CL		180	C				
CHP	60-90	HZ	1.5:1	CT	1.0-60	HZ	60:1	VT	0-60	HZ	1000:1		
SPACE HEATER LEADS H1-H2:				TIE LIKE NUMBERS				TOGETHER					
V		A		W		MAX SPACE HEATER TEMP							

Accessories

Part number	Description	Multiplier
09-1309	C FACE KIT	A8

AC Induction Motor Performance Data

Record # 1931

Typical performance - not guaranteed values

Winding: 09WGY264-R001				Type: 0954M		Enclosure: TEFC	
Nameplate Data				575 V, 60 Hz: Single Voltage Motor			
Rated Output (HP)		7.5		Full Load Torque		33.3 LB-FT	
Volts		575		Start Configuration		direct on line	
Full Load Amps		8.7		Breakdown Torque		102 LB-FT	
R.P.M.		1180		Pull-up Torque		41 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		60 LB-FT	
NEMA Design Code		A		KVA Code		J	
Service Factor (S.F.)		1.15		Starting Current		58 A	
NEMA Nom. Eff.		91.7		Power Factor		71	
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load	
S.F. Amps						Temp. Rise @ S.F. Load	
						Locked-rotor Power Factor	
						Rotor inertia	

Load Characteristics 575 V, 60 Hz, 7.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	33	53	61	71	78	80	75
Efficiency	84.9	90.6	91.8	91.9	91.4	90.5	91.6
Speed	1196	1192	1188	1183	1178	1173	1180
Line amperes	5.1	5.9	7.5	8.7	9.8	11.5	9.36


ABB Motors and Mechanical Inc.


WINDING # 09WGY264

Typical performance - not guaranteed values.




7.5 HP 3 PH 60 HZ 1180 RPM 575 V 0954M

TORQUES (LB-FT) : PO=102 PU=41 LR=60 LRA=58





CD0006



- NOTES:
1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
 2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
 5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10: 24: 49 02/19/2019	BY: ENBRIRO
MTL: —		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1