ABB BALDOR RELIANCE

Customer information packet

ECP2276T

7.5HP, 1180RPM, 3PH, 60HZ, 254T, 0954M, TEFC, F
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/14/2026 11:44:02 AM

Specifications

Enclosure	TEFC
Frame	254T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CCSA US
	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1.0
Current @ Voltage	25.000 A @ 208.0 V
	21.400 A @ 230.0 V
	10.700 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated

Part Detail

Revision	AZ
Type	AC
Mech. spec.	09J371
Base	
Status	PRD/A
Elec. spec.	09WGX827
Layout	09LYJ371
Eff. date	09-16-2025
CD Diagram	CD0005
Poles	06
Leads	9#12
Proprietary	False
Created date	08-29-2010

Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	10.7 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0954M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	24.78 IN
Power Factor	71
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1180 rpm

Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3995ABAL

CAT #	ECP2276T			**SER**				**CC**	010A									
SPEC	09J371X827			**RATING**	40C AMB-CONT													
HZ	**VOLTS**		**AMPS**		**RPM**	**HP**	**CODE**	**SF**	**DES**	**PF**		**NEMA NOM. EFF**						
60	230/460		21.4/10.7		1180	7.5	J	1.15	A	71	%	91	%					
											%		%					
PH	3	**CL**	F	**MAX RPM**	1800		**MAX CORR KVAR**	4.15		**USABLE AT 208V**	N/A							
IP55		**FR**	254T	**ENCL**	TEFC		**DE BRG**	6309		**ODE BRG**	6309							
GREASE	POLYREX EM									**MTR WT**	337	**LBS**						
USABLE AT	50HZ 5HP 190/380V 18.6/9.3A							SF1.0										
CL I DIV 2 GRPS A,B,C,D				**CL I ZONE 2 GRPS**					**IIA,IIB,IIC**		**TEMP T**	160	C					
1.0 SF ON PWM INVERTER				**POWER**			**INV TEMP CL**	180	C									
CHP	60-90	**HZ**	1.5:1	**CT**	1.0-60	**HZ**	60:1	**VT**	0-60	**HZ**	1000:1							
SPACE HEATER LEADS H1-H2:				**TIE LIKE NUMBERS**			**TOGETHER**											
V		**A**		**W**			**MAX SPACE HEATER TEMP**											

AC Induction Motor Performance Data
Record # 47260
Typical performance - not guaranteed values

Winding: 09WGX827-R040	**Type:** 0954M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			7.5	**Full Load Torque**	32.4 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			21.4/10.7	**Breakdown Torque**	99.2 LB-FT
R.P.M.			1180	**Pull-up Torque**	39.4 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	57.8 LB-FT
NEMA Design Code	A	**KVA Code**	J	**Starting Current**	69.7 A
Service Factor (S.F.)			1.15	**No-load Current**	5.84 A
NEMA Nom. Eff.	91	**Power Factor**	71	**Line-line Res. @ 25ºC**	0.89 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	31°C
S.F. Amps				**Temp. Rise @ S.F. Load**	36°C
				Rotor inertia	4.34 LB-FT2

Load Characteristics 460 V, 60 Hz, 7.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	32	52	63	71	73	75	72
Efficiency	83	89.7	91.5	91.5	91.8	91.2	91.9
Speed	1196	1192	1189	1184	1179	1173	1181
Line amperes	6.34	7.49	8.87	10.7	12.9	15.7	12


ABB Motors and Mechanical Inc.


WINDING # 09WGX827

7.5 HP 3 PH 60 HZ 1180 RPM 460 V 0954M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=99.2 PU=39.4 LR=57.8 LRA=69.7




09LYJ371
(920 - 964) = 24.78
[629]
[293]
11.53
[109]
4.31
[102]
4.00
.38 KEY
2.88 LONG
Ø 1.625
1.624 [41]
SLINGER
(EA. END)
DRAIN FITTING
(EA. END)
25-20 TAP
GND LOC.
8 HOLES
Ø.53
[210]
8.25
[210]
8.25
[19]
.75
[254]
10.00
[108]
4.25
[292]
11.50
[329]
12.94
[262]
10.33
[168]
6.63
[69]
2.70
PLUG
(EA. END)
[327]
12.88
6.25
6.19
[159]
3.27
.79
LEAD
HOLE
1.25 NPT
[127]
5.00
[127]
5.00
[210]
8.27
[146]
5.75
[292]
11.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: REMOVE WHEN REQ'D FROM SLINGER AND DRAIN CALL OUT
REV: N
VERSION: 13
REVISED: 09:42:54 05/29/2025
TDR: 000001256996
MODEL NO. 09LYJ371
REF: -
BY: ENSHAB0
B
BALDOR - RELIANCE®
HOR TEFC 254-6T ECP W/309 BRGS
09LYJ371

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS