



---

# Customer information packet

## ECP2333T-5

15HP, 1765RPM, 3PH, 60HZ, 254T, 0944M, TEFC, F1

Class - CLI GP A,B,C,D

Division - Division II

## Specifications

Enclosure	TEFC
Frame	254T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR CCSA US
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1.2
Current @ Voltage	14.600 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Front Face Code	Standard

## Part detail

Revision	V
Type	AC
Mech. spec.	09J371
Base	
Status	PRD/A
Elec. spec.	09WGT124
Layout	09LYJ371
Eff. date	09-12-2024
CD Diagram	CD0006
Poles	04
Leads	3#12
Proprietary	False
Created date	01-29-2016

Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	14.6 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0944M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	24.78 IN
Power Factor	83
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

<b>Thermal Device - Winding</b>	None
<b>Vibration Sensor Indicator</b>	No Vibration Sensor
<b>Winding Thermal 1</b>	None
<b>Winding Thermal 2</b>	None

**Nameplate**

**NP3995ABBL**

<b>CAT #</b>	ECP2333T-5			<b>SER</b>				<b>CC</b>	010A		
<b>SPEC</b>	09J371T124G1			<b>RATING</b>	40C AMB-CONT						
<b>HZ</b>	<b>VOLTS</b>		<b>AMPS</b>	<b>RPM</b>	<b>HP</b>	<b>CODE</b>	<b>SF</b>	<b>DES</b>	<b>PF</b>	<b>NEMA NOM. EFF</b>	
60	575		14.6	1765	15	H	1.15	A	83 %	92.4 %	
									%	%	
<b>PH</b>	3	<b>CL</b>	F	<b>MAX RPM</b>	2700	<b>MAX CORR KVAR</b>	4.12	<b>USABLE AT 208V</b>		N/A	
IP55	<b>FR</b>	254T	<b>ENCL</b>	TEFC	<b>DE BRG</b>	6309	<b>ODE BRG</b>	6309			
<b>GREASE</b>	POLYREX EM			<b>MTR WT</b>	297	<b>LBS</b>					
<b>USABLE AT</b>	N/A										
<b>CL I DIV 2 GRPS A,B,C,D</b>				<b>CL I ZONE 2 GRPS</b>			<b>IIA,IIB,IIC</b>		<b>TEMP T</b>	160	<b>C</b>
<b>1.0 SF ON PWM INVERTER</b>			<b>POWER</b>	<b>INV TEMP CL</b>	180	<b>C</b>					
<b>CHP</b>	60-90	<b>HZ</b>	1.5:1	<b>CT</b>	1.2-60	<b>HZ</b>	50:1	<b>VT</b>	0-60	<b>HZ</b>	1000:1
<b>SPACE HEATER LEADS H1-H2:</b>				<b>TIE LIKE NUMBERS</b>			<b>TOGETHER</b>				
<b>V</b>		<b>A</b>		<b>W</b>		<b>MAX SPACE HEATER TEMP</b>					

**AC Induction Motor Performance Data**

Record # 61321

Typical performance - not guaranteed values

<b>Winding:</b> 09WGT124-R008		<b>Type:</b> 0944M		<b>Enclosure:</b> TEFC	
<b>Nameplate Data</b>			<b>575 V, 60 Hz: Single Voltage Motor</b>		
<b>Rated Output (HP)</b>	15	<b>Full Load Torque</b>	44.5 LB-FT		
<b>Volts</b>	575	<b>Start Configuration</b>	direct on line		
<b>Full Load Amps</b>	14.6	<b>Breakdown Torque</b>	153 LB-FT		
<b>R.P.M.</b>	1765	<b>Pull-up Torque</b>	69.5 LB-FT		
<b>Hz</b>	60	<b>Locked-rotor Torque</b>	86.5 LB-FT		
<b>NEMA Design Code</b>	A	<b>Starting Current</b>	102 A		
<b>Service Factor (S.F.)</b>	1.15	<b>No-load Current</b>	6.05 A		
<b>NEMA Nom. Eff.</b>	92.4	<b>Line-line Res. @ 25°C</b>	0.874 Ω		
<b>Rating - Duty</b>	40C	<b>Temp. Rise @ Rated Load</b>	54°C		
<b>S.F. Amps</b>	AMB-CONT	<b>Temp. Rise @ S.F. Load</b>	66°C		
		<b>Locked-rotor Power Factor</b>	33		
		<b>Rotor inertia</b>	1.92 LB-FT <sup>2</sup>		

**Load Characteristics 575 V, 60 Hz, 15 HP**

<b>% of Rated Load</b>	<b>25</b>	<b>50</b>	<b>75</b>	<b>100</b>	<b>125</b>	<b>150</b>	<b>S.F.</b>
<b>Power Factor</b>	45	69	78	83	85	87	86
<b>Efficiency</b>	88.1	92.3	92.6	92.4	91.5	90.5	92.2
<b>Speed</b>	1791	1783	1774	1765	1755	1743	1769
<b>Line amperes</b>	6.9	8.8	11.6	14.6	18.1	21.5	16.3


ABB Motors and Mechanical Inc.

WINDING # 09WGT124


Typical performance - not guaranteed values.

15 HP 3 PH 60 HZ 1765 RPM 575 V 0944M

TORQUES (LB-FT): PO=153 PU=69.5 LR=86.5 LRA=102





12/4/2024 ACPERF, record # 61321





CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIRO
MTL: -	© □	

**BALDOR - RELIANCE®**

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1