ABB BALDOR RELIANCE

Customer information packet

EBM3313T

10HP, 1770RPM, 3PH, 60HZ, 215T, 3742M, OPEN, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/22/2026 4:16:56 AM

Specifications

Enclosure	OPEN
Frame	215T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Brake Torque	50.0 lb-ft
Current @ Voltage	25.000 A @ 230.0 V
	26.000 A @ 208.0 V
	12.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Brake Mounting

Part Detail

Revision	R
Type	AC
Mech. spec.	37B021
Base	
Status	PRD/A
Elec. spec.	37WGT853
Layout	37LYB021
Eff. date	09-05-2025
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	04-09-2010

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	12.5 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3742M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	26.08 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1259L									
CAT.NO.	EBM3313T								
SPEC.	37B021T853G1								
HP	10								
VOLTS	230/460								
AMP	25/12.5								
RPM	1770								
FRAME	215T	**HZ**	60	**PH**	3				
SER.F.	1.15	**CODE**	H	**DES**	B	**CL**	F		
NEMA-NOM-EFF	91.7	**PF**	82						
RATING	40C AMB-CONT								
CC	010A								
DE	6307	**ODE**	6306						
ENCL	OPEN	**SN**							
	SFA 27.72/13.86								

AC Induction Motor Performance Data
Record # 53404
Typical performance - not guaranteed values

Winding: 37WGT853-R026	**Type:** 3742M	**Enclosure:** OPSB

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			10	**Full Load Torque**	29.7 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			25/12.5	**Breakdown Torque**	87.58 LB-FT
R.P.M.			1770	**Pull-up Torque**	44.18 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	51.57 LB-FT
NEMA Design Code	B	**KVA Code**	H	**Starting Current**	86.72 A
Service Factor (S.F.)			1.15	**No-load Current**	4.91 A
NEMA Nom. Eff.	91.7	**Power Factor**	82	**Line-line Res. @ 25ºC**	1.18 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	34°C
S.F. Amps				**Temp. Rise @ S.F. Load**	43°C
				Locked-rotor Power Factor	37.9
				Rotor inertia	1.03 LB-FT2

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	48	70	80	84	86	86	83
Efficiency	87.7	91.8	92.2	91.7	90.8	89.5	91.4
Speed	1793	1785	1777	1769	1759	1749	1763
Line amperes	5.6	7.31	9.53	12.15	15	18.24	14.2


ABB Motors and Mechanical Inc.

WINDING # 37WGT853


10 HP 3 PH 60 HZ 1770 RPM 460 V 3742M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=87.58 PU=44.18 LR=51.57 LRA=86.72




11/22/2026 ACPERF, record # 53404


37LYB021
10-35 FT/LB = 7.97
50-75 FT/LB = 8.13
105 FT/LB = 8.63
(717-735) = 16.82
(738-744) = 17.95
(745-750) = 18.70
(751-756) = 19.45
3.94
3.88
3.38
GREASE FITTING
(EA. END)
.31 KEY
2.38 LONG
NAMEPLATE
Ø 1.3750
1.3745
6 HOLES
Ø .41
5.50
3.50
7.00
.50
8.00
Ø9.52
7.87
2.27
10.02
5.25 +.00 -.06
LEAD HOLE
Ø 1.38
4.25
4.25
6.69
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: FIX STACK LENGTHS
REV: H
VERSION: 03
REVISED: 01:18:25 04/30/2024
TDR: 000001230132
MODEL NO. 37LYB021
REF: -
BY: USALMAZ
B
BALDOR
STD HORZ 213-5T OPEN 37M W/ 87BK BRAKE
37LYB021

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS