

ABB BALDOR RELIANCE III

Customer information packet

ECP4312T-4

50HP, 1185RPM, 3PH, 60HZ, 365T, A36062M, TEFC

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	365T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	6-60
Current @ Voltage	61.700 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3A
Heater Indicator	No Heater
High Voltage Full Load Amps	61.7 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	F

Part Detail

Revision	X
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG0777
Layout	617428-034
Eff. date	08-26-2024
CD Diagram	416820-036
Poles	06
Leads	3#4
Proprietary	False
Created date	10-19-2010

Lifting Lugs	No Lifting Lugs
Max Speed	1800 rpm
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A36062M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	33.49 IN
Power Factor	81
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	2.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1185 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate
NP4033LUA

CAT #		ECP4312T-4					SER				CC		010A													
SPEC		P36G467					RATING		40C AMB-CONT																	
HZ		VOLTS			AMPS			RPM		HP		CODE		-	SF	DES		PF		NEMA NOM. EFF						
60		460			61.7			1185		50		F			1.15	B		81		%						
																				%						
PH		3	CL		F	MAX RPM		1800	MAX CORR KVAR			14														
BRG		DE		6313		ODE		6313	ENCL		TEFC		FR		365T		IP		55							
GREASE		POLYREX EM									MTR WT			879		LBS										
					CL I DIV 2 GRPS A,B,C,D					CL I ZONE 2 GRPS					IIA,IIB,IIC					TEMP T		200	C			
INV READY			CT		15-60		HZ		4:1		VT		3-60		HZ		20:1		CHP		60-75		HZ		1.25:1	
INV TEMP CL			200		C		USABLE AT		50HZ 40HP 380V 60A										SF1.0							

Accessories

Part number	Description	Multiplier
K36G2	C-FACE KIT	A8

ABB BALDOR RELIANCE III							CUSTOMER INFORMATION PACKET							ECP4312T-4 - 50HP, 1185RPM, 3PH, 60HZ, 365T, A36062M, TEFC																																		
S/O			FRAME			HP			TYPE			PHASE/ HERTZ			RPM			VOLTS																														
			365T			50			P			3/60			1185			460																														
AMPS							DUTY							AMB °C/ INSUL							S.F.							NEMA DESIGN							CODE LETTER							ENCLOSURE						
61.7							CONT							40/F							1.0							B							F							TEFC						
E/S							ROTOR							TEST S.O.							TEST DATE							STATOR RES. @25 °C OHMS (BETWEEN LINES)																				
892103							418141-71JE							---							---							.130																				
PERFORMANCE																																																
LOAD							HP							AMPERES							RPM							% POWER FACTOR							% EFFICIENCY													
NO LOAD							0							21.3							1200							5.08							0													
1/4							12.5							26.2							1197							49.4							90.8													
2/4							25.0							35.6							1193							70.0							93.9													
3/4							37.5							47.8							1190							77.8							94.4													
4/4							50.0							61.7							1186							80.6							94.2													
5/4							62.5							76.7							1182							81.5							93.6													
SPEED TORQUE																																																
										RPM							TORQUE % FULL LOAD							TORQUE LB.-FT.							AMPERES																	
LOCKED ROTOR										0							154							340							345																	
PULL UP										650							133							295							305																	
BREAKDOWN										1133							230							510							191																	
FULL LOAD										1186							100							221							61.7																	
AMPERES SHOWN FOR 460 VOLT CONNECTION. IF OTHER CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.																																																
TYPICAL DATA XE MOTOR-TYPICAL DATA-NEMA NOM. EFF. 94.1 PCT. GUARANTEED MIN. EFF. 93.6 PCT.																																																
										DRAWN BY: <u>W. L. SMITH</u> CHECKED BY: <u>J.J.HARRISON</u> APPROVED BY: <u>W. L. SMITH</u> DATE: <u>12/07/05</u>										AC MOTOR PERFORMANCE DATA							A36WG0777-R004 DATE ISSUED 03/04/20																					

FRAME 365T

RPM 1185

S.F. 1.0

ROTOR 418141-71JE

HP 50

VOLTS 460

NEMA DESIGN B

TEST S.O. TYPICAL DATA

TYPE P

AMPS 61.7

CODE LETTER F

TEST DATE ---

PHASE / HERTZ 3/60

DUTY CONT


ENCLOSURE TEFC

STATOR RES. @ 25°C .130

AMB °C / INSUL 40/F

E/S 892103

OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.




DRAWN BY: W. L. SMITH
CHECKED BY: J.J.HARRISON
APPROVED BY: W. L. SMITH
DATE: 12/07/05

AC MOTOR
PERFORMANCE
DATA


A36WG0777-R004

ISSUE DATE 03/04/2014



416820-036

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575-BA)

416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682		REVISED: 11: 54: 06 04/30/2010
MTL: -		BY: RAGRA

BALDOR

CONN DIAG - STANDARD 3 LEAD
SH 1 of 1