ABB BALDOR RELIANCE

Customer information packet

ECP3764T-4

3HP, 1165RPM, 3PH, 60HZ, 213T, 0736M, TEFC, F1
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/18/2026 12:09:37 AM

Specifications

Enclosure	TEFC
Frame	213T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
	CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1.7
Current @ Voltage	4.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part Detail

Revision	Z
Type	AC
Mech. spec.	07K374
Base	
Status	PRD/A
Elec. spec.	07WGX816
Layout	07LYK374
Eff. date	10-01-2025
CD Diagram	CD0006
Poles	06
Leads	3#14
Proprietary	False
Created date	07-13-2007

Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	4.5 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Max Speed	1800 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0736M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	19.50 IN
Power Factor	70
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1165 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3257								
CAT.NO.	ECP3764T-4							
SPEC.	07K374X816G1							
HP	3 TE							
VOLTS	460							
AMP	4.5							
RPM	1165							
FRAME	213T	**HZ**	60			**PH**	3	
SER.F.	1.15	**CODE**	K	**DES**	B	**CL**	F	
RATING	40C AMB-CONT							
SN								
DE	6307	**ODE**	6307					
NEMA-NOM-EFF	89.5	**PF**	70					
G.MIN.EFF	87.5	**CC**	010A					
T. CODE	T3C	**T=**	160					

NP3260					
SPEC.	07K374X816G1				
D.E. BRG.	35BC03XP30X				
O.D.E. BRG.	35BC03XP30X				
GREASE	POLYREX EM				
RPM MAX	1800	**MAX. KVAR**	1.34		
BLANK					
INV.TYPE	PWM				
T=	160				
C HP FR	60	**C HP TO**	90		
CT HZ FROM	1.7	**CT HZ TO**	60		
VT HZ FROM	0-	**VT HZ TO**	60		
HTR-VOLTS		**HTR-AMPS**			
HTR-WATTS		**MAX. SPACE HEATER TEMP.**			


AC Induction Motor Performance Data
Record # 92665
Typical performance - not guaranteed values


Winding: 07WGX816-R019	**Type:** 0736M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			3	**Full Load Torque**	13.5 LB-FT
Volts			460	**Start Configuration**	direct on line
Full Load Amps			4.5	**Breakdown Torque**	48.9 LB-FT
R.P.M.			1165	**Pull-up Torque**	23 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	30 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	31.5 A
Service Factor (S.F.)			1.15	**No-load Current**	2.39 A
NEMA Nom. Eff.	89.5	**Power Factor**	70	**Line-line Res. @ 25ºC**	2.67 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	30°C
S.F. Amps				**Temp. Rise @ S.F. Load**	36°C
				Locked-rotor Power Factor	22.6
				Rotor inertia	0.895 lb-ft²

Load Characteristics 460 V, 60 Hz, 3 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	34	53	64	70	74	75	72
Efficiency	82.2	88.3	89.3	89.8	88.7	87.5	89.3
Speed	1193	1186	1178	1170	1159	1148	1163
Line amperes	2.58	3.07	3.72	4.46	5.35	6.37	4.99



ABB Motors and Mechanical Inc.
WINDING # 07WGX816
Typical performance - not guaranteed values.
3 HP 3 PH 60 HZ 1165 RPM 460 V 0736M
TORQUES(LB-FT): PO=48.9 PU=23 LR=30 LRA=31.5
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (3 HP)
11/18/2026 ACPERF, record # 92665


07LYK374
717-750 = 19.49
9.11
3.88
3.38
AUXILIARY NP
(WHEN REQ'D)
PLUG
Ø12.19
.31 KEY
2.38 LONG
Ø 1.3750
1.3745
FORSHEDA
SLINGER
SLINGER
GROUND
LUG
8 HOLES
Ø.41
DRAIN
FITTING
(EA. END)
5.50
5.50
.57
7.00
3.51
8.13
14.62
8.87
5.75
2.04
5.74
5.25
5.19
LEAD
HOLE
1.00 N.P.T.
4.25
4.25
7.25
4.82
9.63
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRAWING TO SWD
REV: G
VERSION: 07
REVISED: 11:34:04 11/21/2022
TDR: 000001199231
MODEL NO. 07LYK374
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
STD HORZ 213-5T TEFC M CP W/6307 BRGS, LIPPED KOBX LID
07LYK374


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007			BALDOR - RELIANCE®
REV. LTR: E	VERSION: 01	TDR: 000001099922	
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0	3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED
MTL: –			SH 1 of 1