ABB BALDOR RELIANCE

Customer information packet

ECP4402T

100HP, 3565RPM, 3PH, 60HZ, 405TS, A40060M, TEF
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/21/2026 7:49:36 PM

Specifications

Enclosure	TEFC
Frame	405TS
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	100.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	6-60
Current @ Voltage	110.000 A @ 460.0 V
	220.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3
Heater Indicator	No Heater
High Voltage Full Load Amps	110.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	F
Lifting Lugs	Standard Lifting Lugs

Part Detail


Revision	N
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A40WG0022
Layout	617429-502
Eff. date	10-24-2024
CD Diagram	416820-002
Poles	02
Leads	3#2,6#4
Proprietary	False
Created date	07-15-2013

Motor Lead Quantity/Wire Size	3 @ 2 AWG
Motor Standards	NEMA
Motor Type	A40060M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	35.04 IN
Power Factor	90
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	2.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3565 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP3238												
CAT NO	ECP4402T	**SPEC NO.**	P40G3905									
HP	100	**AMPS**	220/110	**VOLTS**	230/460	**DESIGN**	B					
FRAME	405TS	**RPM**	3565	**HZ**	60	**AMB**	40	**SF**	1.15			
D.E. BRG.DATA	6313	**O.D.E. BRG.DATA**	6313	**PH**	3	**DUTY**	CONT	**INSUL.CLASS**	F			
D.E. BRG.	65BC03J30X	**TYPE**	P	**ENCL**	TEFC	**CODE**	F					
O.D.E. BRG.	65BC03J30X	**POWER FACTOR**	90	**NEMA NOM EFFICIENCY**	94.1							
3/4 LOAD EFF.	94.2	**MAX CORR KVAR**	10.0	**GUARANTEED EFFICIENCY**	93							
TEMP CODE	T3	**TEMP =**	200									
CHP HZ	60-75	**CT HZ**	6-60	**VT HZ**	0-60							
INVERTER-TEMP-CODE	T3											
SER.NO.		**MOTOR WEIGHT**										

REL. S.O.	RPM 3565	S.F. 1.15	ROTOR 418142005PE
FRAME 405TS	VOLTS 230/460	NEMA DESIGN B	TEST S.O. TYPICAL DATA
HP 100	AMPS 220/110	CODE LETTER F	TEST DATE ---
TYPE P	DUTY CONT	ENCLOSURE TEFC	STATOR RES.@ 25 ℃.0131/.0526
PHASE/HERTZ 3/60	AMB ℃/INSUL 40/F	E/S 596932	OHMS (BETWEEN LINES)



THERMAL LIMIT CURVE

REMARKS: XE MOTOR-NEMA NOM. EFF. 94.1 %

GUARANTEED MIN. EFF. 93.0%

AMPERES SHOWN FOR 460 **VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.**

BALDOR A MEMBER OF THE ABB GROUP

DR. BY	J.J.HARRISON
CK. BY	W.L.SMITH
APP. BY	E.J.CHRISTIAN
DATE	12/09/03

A-C MOTOR PERFORMANCE CURVES **A40WG0022-R003**

ISSUE DATE 03/03/17

Printed on 3/7/17 7:26 @ bengap01.balc

REL. S.O.	FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS
	405TS	100	P	3/60	3565	230/460

AMPS	DUTY	AMB °C/ INSUL.	S.F.	NEMA DESIGN	CODE LETTER	ENCL.
220/110	CONT	40/F	1.15	B	F	TEFC

E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES.@25 °C OHMS (BETWEEN LINES)
596932	418142005PE	---	---	.0131/.0526

PERFORMANCE

LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY
NO LOAD	0	25.6	3600	8.43	0
1/4	25.0	36.8	3591	70.0	90.9
2/4	50.0	57.9	3582	85.9	94.2
3/4	75.1	82.9	3572	89.4	94.8
4/4	100	110	3563	89.9	94.8
5/4	125	137	3552	90.2	94.4

SPEED TORQUE

	RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES
LOCKED ROTOR	0	203	299	695
PULL UP	1545	182	269	632
BREAKDOWN	3408	256	377	387
FULL LOAD	3563	100	147	110

AMPERES SHOWN FOR 460. VOLT CONNECTION. IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE

REMARKS: TYPICAL DATA
XE MOTOR-NEMA NOM. EFF. 94.1 %
GUARANTEED MIN. EFF. 93.0%


BALDOR
A MEMBER OF THE ABB GROUP

DR. BY J.J.HARRISON
CK. BY W.L.SMITH
APP. BY E.J.CHRISTIAN
DATE 12/09/03

A-C MOTOR PERFORMANCE DATA

A40WG0022-R003
ISSUE DATE 03/03/17

REL S.O.	RPM 3565	S.F. 1.15	ROTOR 418142005PE
FRAME 405TS	VOLTS 230/460	NEMA DESIGN B	TEST S.O. TYPICAL DATA
HP 100	AMPS 220/110	CODE LETTER F	TEST DATE ---
TYPE P	DUTY CONT	ENCLOSURE TEFC	STATOR RES.@ 25 °C .0131/.0526
PHASE/HERTZ 3/60	AMB °C/INSUL 40/F	E/S 596932	OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

BALDOR
A MEMBER OF THE ABB GROUP

DR. BY	J.J.HARRISON
CK. BY	W.L.SMITH
APP. BY	E.J.CHRISTIAN
DATE	12/09/03

A-C MOTOR PERFORMANCE CURVES

A40WG0022-R003


ISSUE DATE 03/03/17


DUTY MASTER ALTERNATING CURRENT MOTORS


617429-502


ENCLOSURE: TOTALLY ENCLOSED | SQUIRREL-CAGE INDUCTION | COOLING: FAN COOLED

MOUNTING: FOOT, F-1 | G405TS/G404TS FRAME MOUNTING | ENCLOSURE ENHANCEMENT: SEVERE DUTY









1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.

MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

DIMENSIONS ARE IN INCHES; SEE SHEET 2 FOR DIMENSIONS IN MILLIMETERS.
WEIGHT (LBS): 1160, MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

SHEET NUMBER 1 OF 2

617429-502

REV. DESC: UPDATE DS QUALITY			
REV: C	VERSION: 03	REVISED: 09:15:12 06/28/2017	TDR: 000001033374
MODEL NO. 617429-502			REF:
BY: USJEDIL	Material:	C	BALDOR

G405TS/404TS TEFC F1 FOOT CAST IRON CONDUIT BOX/SEVERE DUTY


617429-502


DUTY MASTER ALTERNATING CURRENT MOTORS


617429-502


ENCLOSURE: TOTALLY ENCLOSED | SQUIRREL-CAGE INDUCTION | COOLING: FAN COOLED

MOUNTING: FOOT, F-1 | G405TS/G404TS FRAME MOUNTING | ENCLOSURE ENHANCEMENT: SEVERE DUTY









1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .08 T.I.R.

DIMENSIONS ARE IN MILLIMETERS.
WEIGHT (KGS): 530, MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

SHEET NUMBER 2 OF 2

617429-502


REV. DESC: UPDATE DS QUALITY			
REV: C	VERSION: 03	REVISED: 09:15:12 06/28/2017	TDR: 000001033374
MODEL NO. 617429-502			REF:
BY: USJEDIL	Material:	C	G405TS/404TS TEFC F1 FOOT CAST IRON CONDUIT BOX/SEVERE DUTY


BALDOR

617429-502

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED





(N. P. 1575-B)

REV. DESC: ADJUST TEXT DARKNESS		
REV. LTR: B	VERSION: 02	TDR: 000001285318
FILE: \RAG\00022\453	REVISED: 09:36:26 09/24/2026	BY: USJOSUL
MTL: –		

ABB

CONN DIAG – STANDARD 9 LEAD, DELTA-CONNECTED

SH1 of 1

416820-002