

ABB BALDOR RELIANCE III

Customer information packet

ECP4411TR-4

125HP, 1188RPM, 3PH, 60HZ, 445T, TEFC, F1

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	445T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	125.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Mobil SHC 220 (Athens Only)
Constant Torque Speed Range	15-60
Current @ Voltage	146.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.0 %
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3
Heater Indicator	No Heater
High Voltage Full Load Amps	146.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Motor Lead Quantity/Wire Size	3 @ 1 AWG
Motor Standards	NEMA

Part Detail

Revision	N
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A44WG3350
Layout	617427-001
Eff. date	12-10-2025
CD Diagram	416820-036
Poles	06
Leads	3#1
Proprietary	False
Created date	12-05-2013

Motor Type	A44090M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	44.75 IN
Power Factor	84
Product Family	General Industrial
Pulley End Bearing Type	Roller
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	3.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1188 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP2496L	
MOBILITH SHC 220	

NP3238

CAT NO	ECP4411TR-4			SPEC NO.		A44-5205-3350							
HP	125	AMPS	146	VOLTS		460		DESIGN	B				
FRAME	445T	RPM	1188	HZ	60	AMB	40	SF	1.15				
D.E. BRG.DATA	NU222		O.D.E. BRG.DATA			6318		PH	3	DUTY	CONT	INSUL.CLASS	F
D.E. BRG.	110RU02M30X28			TYPE	P	ENCL	TEFC	CODE	G				
O.D.E. BRG.	90BC03J30X			POWER FACTOR			84		NEMA NOM EFFICIENCY			95	
3/4 LOAD EFF.	95.3		MAX CORR KVAR			30.0		GUARANTEED EFFICIENCY			94.1		
TEMP CODE	T3		TEMP =		200								
CHP HZ	60-90		CT HZ	15-60		VT HZ	0-60						
INVERTER-TEMP-CODE	T3												
SER.NO.				MOTOR WEIGHT									

ABB BALDOR RELIANCE III S/O		CUSTOMER INFORMATION PACKET					ECP4411TR-4 - 125HP, 1188RPM, 3PH, 60HZ, 445T, TEFC, F1				
		FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS				
		445T	125	P	3/60	1188	460				
AMPS		DUTY	AMB °C/ INSUL		S.F.	NEMA DESIGN	CODE LETTER		ENCLOSURE		
146		CONT	40/F		1.15	B	G		TEFC		
E/S		ROTOR	TEST S.O.		TEST DATE		STATOR RES. @25 °C OHMS (BETWEEN LINES)				
498802		418143098ME	---		---		.0377				
PERFORMANCE											
LOAD		HP	AMPERES		RPM		% POWER FACTOR		% EFFICIENCY		
NO LOAD		0	44.6		1200		4.33		0		
1/4		31.3	64.2		1197		49.1		92.9		
2/4		62.5	86.3		1195		71.2		95.3		
3/4		93.7	114		1192		80.3		95.6		
4/4		125	146		1189		84.1		95.4		
5/4		156	180		1186		85.6		94.9		
SPEED TORQUE											
			RPM		TORQUE % FULL LOAD		TORQUE LB.-FT.		AMPERES		
LOCKED ROTOR			0		136		751		976		
PULL UP			168		120		665		938		
BREAKDOWN			1148		267		1474		561		
FULL LOAD			1189		100		552		146		
AMPERES SHOWN FOR 460 VOLT CONNECTION. IF OTHER CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.											
TYPICAL DATA NEMA NOMINAL EFFICIENCY = 95.0 PCT.											
			DRAWN BY: <u>W. L. SMITH</u> CHECKED BY: <u>J.J.HARRISON</u> APPROVED BY: <u>W. L. SMITH</u> DATE: <u>04/20/10</u>			AC MOTOR PERFORMANCE DATA		A44WG3350-R001 DATE ISSUED 08/09/19			

FRAME 445T

RPM 1188

S.F. 1.15

ROTOR 418143098ME

HP 125

VOLTS 460

NEMA DESIGN B

TEST S.O. TYPICAL DATA

TYPE P

AMPS 146

CODE LETTER G

TEST DATE ---

PHASE / HERTZ 3/60

DUTY CONT

ENCLOSURE TEFC


STATOR RES. @ 25°C .0377

AMB °C / INSUL 40/F

E/S 498802

OHMS (BETWEEN LINES)

NEMA NOMINAL EFFICIENCY = 95.0 PCT.



AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.



DRAWN BY: W. L. SMITH
 CHECKED BY: J.J. HARRISON
 APPROVED BY: W. L. SMITH
 DATE: 04/20/10

AC MOTOR
 PERFORMANCE
 DATA

A44WG3350-R001

ISSUE DATE 08/09/19

FRAME 445T

RPM 1188

S.F. 1.15

ROTOR 418143098ME

HP 125

VOLTS 460

NEMA DESIGN B

TEST S.O. TYPICAL DATA

TYPE P

AMPS 146

CODE LETTER G

TEST DATE ---

PHASE / HERTZ 3/60

DUTY CONT


ENCLOSURE TEFC

STATOR RES. @ 25°C .0377

AMB °C / INSUL 40/F

E/S 498802

OHMS (BETWEEN LINES)



THERMAL LIMIT CURVE
NEMA NOMINAL EFFICIENCY = 95.0 PCT.

AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.



DRAWN BY: W. L. SMITH
 CHECKED BY: J.J.HARRISON
 APPROVED BY: W. L. SMITH
 DATE: 04/20/10

AC MOTOR
PERFORMANCE
DATA

A44WG3350-R001

ISSUE DATE 08/09/19

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION



ENCLOSURE: TOTALLY ENCLOSED

FRAME G445T ABOVE NEMA RATINGS

COOLING: FAN COOLED

MOUNTING: FOOT

INCLUDES 444T FRAME MOUNTING HOLES



1. GROUND HOLES QTY 1 1/2-13 TAP; QTY 1 3/8-16 TAP
2. VARIES +.00-.06
3. VARIES +.000-.001
4. ON STANDARD MOTORS THIS IS CONDUIT SIZE. ON XT AND CORROSION PROOF MOTOR THIS IS PIPE TAP.
5. MOTOR WEIGHTS MAY VARY BY 1.5% DEPENDING ON RATING.
6. OBSTRUCTION MUST NOT ENCROACH ON AIR INLET

CONDUIT BOX LOCATED ON OPPOSITE SIDE WHEN F-2.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF
STANDARD SHAFT EXTENSION IS .003" T.I.R. TO 5 INCH DIA.

[5] WEIGHT (LBS): 2130

DRIVE END AIR DEFLECTOR IS ONLY INCLUDED WHEN NECESSARY.

DIMENSIONS ARE IN INCHES; SEE SHEET 2 FOR DIMENSIONS IN MILLIMETERS

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

 SHEET NUMBER
1 OF 2

100-2272119

REV. DESC: SHEET 2 NEEDS METRIC FOOT HOLE DIMENSION			
REV: E	VERSION: 05	REVISED: 09-22-56 06/12/2014	TDR: 000000857938
MODEL NO. 617427-001		REF:	
BY: RAGRA	Material:		

BALDOR

G445T444T STD - FOOTED - SIDE/CENTER C/B

617427-001

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION



ENCLOSURE: TOTALLY ENCLOSED

FRAME G445T ABOVE NEMA RATINGS

COOLING: FAN COOLED

MOUNTING: FOOT

INCLUDES 444T FRAME MOUNTING HOLES



1. GROUND HOLES QTY 1 1/2-13 TAP; QTY 1 3/8-16 TAP
2. VARIES +0,-1.5
3. VARIES +.00,-.03
4. ON STANDARD MOTORS THIS IS CONDUIT SIZE. ON XT AND CORROSION PROOF MOTOR THIS IS PIPE TAP.
5. MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
6. OBSTRUCTION MUST NOT ENCROACH ON AIR INLET

CONDUIT BOX LOCATED ON OPPOSITE SIDE WHEN F-2.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF
STANDARD SHAFT EXTENSION IS .08 MM T.I.R. TO 127 MM DIA.

[5] WEIGHT (KGS): 970

DRIVE END AIR DEFLECTOR IS ONLY INCLUDED WHEN NECESSARY.

DIMENSIONS ARE IN MILLIMETERS; SEE SHEET 1 FOR DIMENSIONS IN INCHES

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

SHEET NUMBER
2 OF 2

100-2272119

REV. DESC: SHEET 2 NEEDS METRIC FOOT HOLE DIMENSION	
REV: E	VERSION: 05
MODEL NO. 617427-001	REVISED: 09-22-56 06/12/2014
BY: RAGRA	TDR: 00000857938
Material:	REF:


BALDOR

G445T444T STD - FOOTED - SIDE/CENTER C/B

617427-001

416820-036

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575-BA)

416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682		REVISED: 11: 54: 06 04/30/2010
MTL: -		BY: RAGRA

BALDOR

CONN DIAG - STANDARD 3 LEAD
SH 1 of 1