

ABB BALDOR RELIANCE III

Customer information packet

ECP44156T-4

150HP, 1190RPM, 3PH, 60HZ, 447T, A44120M, TEFC

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	447T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	150.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	15-60
Current @ Voltage	170.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.8 %
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3
Heater Indicator	No Heater
High Voltage Full Load Amps	170.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	F
Lifting Lugs	No Lifting Lugs
Motor Lead Quantity/Wire Size	3 @ 1/0 AWG
Motor Standards	NEMA

Part Detail

Revision	M
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A44WG3369
Layout	617427-002
Eff. date	10-24-2024
CD Diagram	416820-036
Poles	06
Leads	3#1/0
Proprietary	False
Created date	08-16-2012

Motor Type	A44120M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	48.24 IN
Power Factor	86
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	3.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1190 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP3238															
CAT NO	ECP44156T-4				SPEC NO.	P44G3945									
HP	150	AMPS	170			VOLTS	460		DESIGN	B					
FRAME	447T	RPM	1190	HZ	60	AMB	40	SF	1.15						
D.E. BRG.DATA	6318	O.D.E. BRG.DATA				6318	PH	3	DUTY	CONT	INSUL.CLASS	F			
D.E. BRG.	90BC03J30X				TYPE	P	ENCL	TEFC	CODE	F					
O.D.E. BRG.	90BC03J30X				POWER FACTOR			86	NEMA NOM EFFICIENCY			95.8			
3/4 LOAD EFF.	95.8	MAX CORR KVAR				25.0	GUARANTEED EFFICIENCY			95.0					
TEMP CODE	T3	TEMP =	200												
CHP HZ	60-90	CT HZ	15-60		VT HZ	0-60									
INVERTER-TEMP-CODE	T3														
SER.NO.					MOTOR WEIGHT										

REL. S.O.	FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS			
	447T	150	P	3/60	1190	460			
AMPS	DUTY	AMB °C/ INSUL.	S.F.	NEMA DESIGN	CODE LETTER	ENCL.			
170	CONT	40/F	1.15	B	F	FCXE			
E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES. @25 °C OHMS (BETWEEN LINES)					
833241	418143080ME	---	---	.0324					
PERFORMANCE									
LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY				
NO LOAD	0	42.5	1200	3.70	0				
1/4	37.6	65.5	1197	56.6	94.9				
2/4	75.1	94.9	1194	76.9	96.3				
3/4	112	130	1191	83.9	96.2				
4/4	150	170	1188	86.3	95.8				
5/4	188	213	1184	86.8	95.1				
SPEED TORQUE									
		RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES				
LOCKED ROTOR		0	121	799	1025				
PULL UP		180	97.2	644	1002				
BREAKDOWN		1150	236	1563	592				
FULL LOAD		1188	100	663	170				
AMPERES SHOWN FOR 460. VOLT CONNECTION. IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE REMARKS: CALCULATED DATA NEMA NOMINAL EFFICIENCY = 95.4 PCT.									
		DR. BY W. L. SMITH		A-C MOTOR PERFORMANCE DATA					
		CK. BY J. J. HARRISON							
		APP. BY W. L. SMITH							
		DATE 04/27/10							
				A44WG3369-R001 ISSUE DATE 04/27/10					

FRAME 447T

RPM 1190

VOLTS 460

NEMA DESIGN B

TEST S.O. CALCULATED DATA

HP 150

AMPS 170

CODE LETTER F

TEST DATE ---

TYPE P

DUTY CONT

ENCLOSURE FCXE


STATOR RES. @ 25 °C .0324

PHASE/HERTZ 3/60

AMB °C/INSUL 40/F

E/S 833241

OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

BALDOR

DR. BY W. L. SMITH
CK. BY J. J. HARRISON
APP. BY W. L. SMITH
DATE 04/27/10

**A-C MOTOR
PERFORMANCE
CURVES** A44WG3369-R001
ISSUE DATE 04/27/10

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION


ENCLOSURE: TOTALLY ENCLOSED

FRAME G447T ABOVE NEMA RATINGS

COOLING: FAN COOLED

MOUNTING: FOOT

INCLUDES 445T FRAME MOUNTING HOLES



1. GROUND HOLES QTY 1 1/2-13 TAP; QTY 1 3/8-16 TAP
2. VARIES $\pm .00$, $-.06$
3. VARIES $\pm .000$, $-.001$
4. ON STANDARD MOTORS THIS IS CONDUIT SIZE. ON XT AND CORROSION PROOF MOTOR THIS IS PIPE TAP.
5. MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
6. OBSTRUCTION MUST NO ENCROACH ON AIR INLET.
7. AIR DEFLECTOR INSTALLED WHEN REQUIRED.

CONDUIT BOX LOCATED ON OPPOSITE SIDE WHEN F-2.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF
STANDARD SHAFT EXTENSION IS $.003$ " T.I.R. TO 5 INCH DIA.

[5] WEIGHT (LBS): 2515

DRIVE END AIR DEFLECTOR IS ONLY INCLUDED WHEN NECESSARY.

DIMENSIONS ARE IN INCHES; SEE SHEET 2 FOR DIMENSIONS IN MILLIMETERS

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

SHEET NUMBER
1 OF 2

0007-27-119

REV. DESC: CHANGING ENCLOSURE TO "TOTALLY ENCLOSED" WAS "UL..."
REV: A VERSION: 01 REVISED: 08/25/13 02/15/2013 TDR: 000000786306
MODEL NO. 617427-002 REF:
BY: MGHWC Material:

BALDOR

G447T/445T STD - FOOTED - SIDE/CENTER C/B

617427-002

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION


ENCLOSURE: TOTALLY ENCLOSED

FRAME G447T ABOVE NEMA RATINGS

COOLING: FAN COOLED

MOUNTING: FOOT

INCLUDES 445T FRAME MOUNTING HOLES



1. GROUND HOLES QTY 1 1/2-13 TAP; QTY 1 3/8-16 TAP
2. VARIES $\pm .00$, $-.06$
3. VARIES $\pm .000$, $-.001$
4. ON STANDARD MOTORS THIS IS CONDUIT SIZE. ON XT AND CORROSION PROOF MOTOR THIS IS PIPE TAP.
5. MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
6. OBSTRUCTION MUST NO ENCROACH ON AIR INLET.
7. AIR DEFLECTOR INSTALLED WHEN REQUIRED.

CONDUIT BOX LOCATED ON OPPOSITE SIDE WHEN F-2.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF
STANDARD SHAFT EXTENSION IS .08 MM T.I.R. TO 127 MM DIA.

5 WEIGHT (KGS): 1140

DRIVE END AIR DEFLECTOR IS ONLY INCLUDED WHEN NECESSARY.

DIMENSIONS ARE IN MILLIMETERS; SEE SHEET 1 FOR DIMENSIONS IN INCHES

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.


REV. A	VERSION: 01	REVISED: 08/25/13 02/15/2013	TDR: 000000786306
MODEL NO. 617427-002	BY: MGHWC	Material:	REF:

BALDOR

G447T/445T STD - FOOTED - SIDE/CENTER C/B

416820-036

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575-BA)

416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682	REVISED: 11: 54: 06 04/30/2010	
MTL: -	BY: RAGRA	

BALDOR

CONN DIAG - STANDARD 3 LEAD
SH 1 of 1