

ABB BALDOR RELIANCE III

Customer information packet

ECP4316T-5

75HP, 1780RPM, 3PH, 60HZ, 365T, A36070M, TEFC

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	365T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	75.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	30-60
Current @ Voltage	69.000 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.4 %
Enclosure Modification	841
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3
Heater Indicator	No Heater
High Voltage Full Load Amps	69.0 a
Insulation Class	F
Inverter Code	Inverter Ready

Part Detail

Revision	AA
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG4078
Layout	617428-034
Eff. date	02-13-2025
CD Diagram	416820-036
Poles	04
Leads	3#4
Proprietary	False
Created date	10-19-2010

KVA Code	G
Lifting Lugs	No Lifting Lugs
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A36070M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	33.49 IN
Power Factor	86
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	2.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1780 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP4033LUA

CAT #	ECP4316T-5		SER			CC						
SPEC	P36G3424		RATING	40C AMB-CONT								
HZ	VOLTS		AMPS	RPM	HP	CODE	G	SF	DES	PF	NEMA NOM. EFF	
60	575		69	1780	75	G		1.15	B	86 %	95.4 %	
										%	%	
PH	3	CL	F	MAX RPM	2700	MAX CORR KVAR	16					
BRG	DE	6313	ODE	6313	ENCL	TEFC	FR	365T	IP	55		
GREASE	POLYREX EM			MTR WT	930	LBS						
CL I DIV 2 GRPS A,B,C,D				CL I ZONE 2 GRPS				IIA,IIB,IIC	TEMP T	200	C	
INV READY	CT	15-60	HZ	4:1	VT	0-60	HZ	1000:1	CHP	60-90	HZ	1.5:1
INV TEMP CL	200	C	USABLE AT	N/A								
SFA	80											

Record #71925 - Typical performance - not guaranteed values

Winding	A36WG4078
Type	A3670M
Enclosure	TEFC

Nameplate data

Rated Output			75
Volts			575
Full Load Amps			69
R.P.M.			1780
Hz	60	Phase	3
KVA Code			G
S.F.			1.15
NEMA Nom. Eff.	95.4	Power Factor	86
Duty			CONT
S.F. Amps			

575 V, 60 Hz:
Single Voltage Motor

Full Load Torque	220 LB-FT
Start Configuration	direct on line
Breakdown Torque	619 LB-FT
Pull-up Torque	339 LB-FT
Locked-rotor Torque	431 LB-FT
Starting Current	437 A
No-load Current	22.31
Line-line Res. @ 25°C	0.14 Ω
Temp. Rise @ Rated Load	61°C
Temp. Rise @ S.F. Load	77°C
Locked-rotor Power Factor	32.1
Rotor inertia	16.2 lb-ft ²

Load Characteristics 575 V, 60 Hz, 75 HP


% of Rated Load	NL	25	50	75	100	125	150	SF
Power Factor	4	54	76	83	86	86	85	86
Efficiency	0	93.7	95.9	95.7	95.4	94.6	93.7	94.8
Speed	1799	1797	1792	1787	1782	1777	1770	1779
Line amperes	22.31	27.39	38.79	53.01	68.52	85.75	105	78.9

SPEED TORQUE / SPEED CURRENT CURVES




A36WG4078

75HP 575V 60HZ




Record: 71925



416820-036

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575-BA)

416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682	REVISED: 11:54:06 04/30/2010	
MTL: -	BY: RAGRA	

BALDOR
CONN DIAG - STANDARD 3 LEAD
SH 1 of 1