

ABB BALDOR RELIANCE III

Customer information packet

ECP83587T-4

2HP, 1755RPM, 3PH, 60HZ, 145T, 0526M, TEFC, F1

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	145T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSA US UR NEMA_PREMIUM NEMA PREMIUM CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.800 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.8 a

Part Detail

Revision	L
Type	AC
Mech. spec.	05E811
Base	
Status	PRD/A
Elec. spec.	05WGX549
Layout	05LYE811
Eff. date	10-22-2025
CD Diagram	CD0006
Poles	04
Leads	3#18 Y
Proprietary	False
Created date	03-11-2022

Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	L
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0526M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.87 IN
Power Factor	74
Product Family	Chem Process S/P 32-8 IEEE 841
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1755 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4328									
CAT.NO.	ECP83587T-4								
SPEC.	05E811X549G1								
HP	2 TE				IP	56			
VOLTS	460								
AMPS	2.8								
R.P.M.	1755								
FRAME	145T		HZ		60		PH	3	
SER.F.	1.15	CODE	L	DES.	B	CLASS		F	
RATING	40C AMB-CONT								
SN									
DE	6205		ODE		6205				
NEMA NOM. EFF.	86.5		P.F.		74				
GUAR. MIN. EFF.	84		CC		010A				
T. CODE	T4		TEMP=		135				

NP3186						
SPEC.	05E811X549G1					
ABMA DE BRG	25BC02X30X					
ABMA ODE BRG	25BC02X30X					
GREASE	POLYREX EM					
MOTOR WEIGHT	61	ROTOR BARS	27	STATOR BARS	36	
MAX. R.P.M.	2700	MAX. KVAR	0.64			
	SFA 3.2					
INV.TYPE	PWM					
T=	135					
CHP	60	TO	90			
CT	1.3	TO	60			
VT	0-	TO	60			
HTR-VOLTS	HTR-AMPS					
HTR-WATTS				MAX. SPACE HEATER TEMP.		

AC Induction Motor Performance Data

Record # 84197

Typical performance - not guaranteed values

Winding: 05WGX498-R001				Type: 0532M		Enclosure: TEFC	
Nameplate Data				460 V, 60 Hz: Single Voltage Motor			
Rated Output (HP)		2		Full Load Torque		5.999 LB-FT	
Volts		460		Start Configuration		direct on line	
Full Load Amps		2.8		Breakdown Torque		24.4 LB-FT	
R.P.M.		1755		Pull-up Torque		15.1 LB-FT	
Hz		60		Phase		3	
NEMA Design Code		B		KVA Code		L	
Service Factor (S.F.)		1.15		No-load Current		24.9 A	
NEMA Nom. Eff.		86.5		Power Factor		75	
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load	
S.F. Amps						Temp. Rise @ S.F. Load	
						Locked-rotor Power Factor	

Load Characteristics 460 V, 60 Hz, 2 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	34	54	67	75	80	83	78
Efficiency	78.8	86.1	87.9	88.1	87.4	86.3	87.7
Speed	1789.6	1780.5	1770.9	1760.1	1749.1	1737.3	1754
Line amperes	1.78	2.04	2.4	2.85	3.36	3.9	3.16


ABB Motors and Mechanical Inc.


WINDING # 05WGX498

Typical performance - not guaranteed values.




2 HP 3 PH 60 HZ 1755 RPM 460 V 0532M

TORQUES (LB-FT): PO=24.4 PU=15.1 LR=16.7 LRA=24.9





CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10: 24: 49 02/19/2019

BY: ENBRIRO

MTL: —



BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1