

ABB BALDOR RELIANCE III

Customer information packet

ECP4413T-4

150HP, 3570RPM, 3PH, 60HZ, 445TS, A4478M, TEFC

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	445TS
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	150.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	10-60
Current @ Voltage	164.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.0 %
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3
Heater Indicator	No Heater
High Voltage Full Load Amps	164.0 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Motor Lead Quantity/Wire Size	6 @ 2 AWG
Motor Standards	NEMA

Part Detail

Revision	AA
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A44WG3535
Layout	617427-493
Eff. date	02-16-2026
CD Diagram	416820-036
Poles	02
Leads	3#2 (02 per group)
Proprietary	False
Created date	08-16-2012

Motor Type	A4478M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	40.83 IN
Power Factor	90
Product Family	Other
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	2.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3570 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP3238																
CAT NO	ECP4413T-4				SPEC NO.		P44G3944									
HP	150	AMPS		164		VOLTS		460		DESIGN		B				
FRAME	445TS	RPM		3570		HZ		60	AMB		40	SF		1.15		
D.E. BRG.DATA	6313		O.D.E. BRG.DATA				6313		PH		3	DUTY		CONT	INSUL.CLASS	F
D.E. BRG.	65BC03J30X				TYPE		P	ENCL		TEFC	CODE		G			
O.D.E. BRG.	65BC03J30X				POWER FACTOR				90		NEMA NOM EFFICIENCY				95	
3/4 LOAD EFF.	95.7		MAX CORR KVAR				20.0		GUARANTEED EFFICIENCY				94.1			
TEMP CODE	T3		TEMP =		200											
CHP HZ	60-75		CT HZ		10-60		VT HZ		0-60							
INVERTER-TEMP-CODE	T3															
SER.NO.					MOTOR WEIGHT											

ABB BALDOR RELIANCE III							CUSTOMER INFORMATION PACKET							ECP4413T-4 - 150HP, 3570RPM, 3PH, 60HZ, 445TS, A4478M, TEFC						
S/O			FRAME			HP			TYPE			PHASE/ HERTZ			RPM			VOLTS		
			445			150			P			3/60			3570			460		
AMPS			DUTY			AMB °C/ INSUL			S.F.			NEMA DESIGN			CODE LETTER			ENCLOSURE		
164			CONT			40/F			1.15			B			G			TEFC		
E/S			ROTOR			TEST S.O.			TEST DATE			STATOR RES. @25 °C OHMS (BETWEEN LINES)								
0			0			---			---			.0292								
PERFORMANCE																				
LOAD			HP			AMPERES			RPM			% POWER FACTOR			% EFFICIENCY					
NO LOAD			0			34.7			3600			6.89			0					
1/4			37.5			59.2			3593			63.9			92.9					
2/4			75.1			90.3			3585			81.7			95.3					
3/4			113			125			3578			87.8			95.7					
4/4			150			164			3570			89.9			95.6					
5/4			187			204			3562			90.4			95.2					
SPEED TORQUE																				
						RPM			TORQUE % FULL LOAD			TORQUE LB.-FT.			AMPERES					
LOCKED ROTOR						0			138			304			1081					
PULL UP						1350			110			242			997					
BREAKDOWN						3461			280			618			552					
FULL LOAD						3570			100			221			164					
AMPERES SHOWN FOR 460 VOLT CONNECTION. IF OTHER CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.																				
CALCULATED DATA NEMA NOMINAL EFFICIENCY = 95.0 PCT.																				
						DRAWN BY: <u>CD</u> CHECKED BY: <u>CD</u> APPROVED BY: <u>R. MCELVEEN</u> DATE: <u>1/18/11</u>						AC MOTOR PERFORMANCE DATA			A44WG3535-R001 DATE ISSUED 03/04/20					

FRAME 445

RPM 3570

S.F. 1.15

ROTOR 0

HP 150

VOLTS 460

NEMA DESIGN B

TEST S.O. CALCULATED DATA

TYPE P

AMPS 164

CODE LETTER G

TEST DATE ---

PHASE / HERTZ 3/60

DUTY CONT

ENCLOSURE TEFC



STATOR RES. @ 25°C .0292

AMB °C / INSUL 40/F

E/S 0

OHMS (BETWEEN LINES)

NEMA NOMINAL EFFICIENCY = 95.0 PCT.



AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.





DRAWN BY: CD
CHECKED BY: CD
APPROVED BY: R. MCELVEEN
DATE: 1/18/11

AC MOTOR
PERFORMANCE
DATA

A44WG3535-R001


ISSUE DATE 03/04/2014





416820-036

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575-BA)

416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682		REVISED: 11: 54: 06 04/30/2010
MTL: -	BY: RAGRA	

BALDOR

CONN DIAG - STANDARD 3 LEAD
SH 1 of 1