

DUTY MASTER ALTERNATING CURRENT MOTORS





SQUIRREL-CAGE INDUCTION

ENCLOSURE: TOTALLY ENCLOSED

MOUNTING: FOOT, F-1

GL449T/G449T FRAME MOUNTING HOLES

COOLING: FAN COOLED



- 1 GROUND HOLES QTY (1) 1/2-13 TAP; QTY (1) 3/8-16 TAP
- 2 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
 MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

DIMENSIONS ARE IN INCHES; SEE SHEET 2 FOR DIMENSIONS IN MILLIMETERS.
 WEIGHT (LBS): 3875, MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
 CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: UPDATE DS QUALITY			
REV: D	VERSION: 04	REVISED: 09:36:15 01/16/2018	TDR: 000001056307
MODEL NO. 617423-006		REF: -	
BY: USJEDIL	Material: -		

BALDOR

GL449/449T F1 FOOT TEFC/CAST IRON BOX W/ LEAD THROAT

DUTY MASTER ALTERNATING CURRENT MOTORS





SQUIRREL-CAGE INDUCTION

ENCLOSURE: TOTALLY ENCLOSED

MOUNTING: FOOT, F-1

GL449T/G449T FRAME MOUNTING HOLES

COOLING: FAN COOLED



- 1 GROUND HOLES QTY (1) 1/2-13 TAP; QTY (1) 3/8-16 TAP
- 2 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
 MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .08 T.I.R.

DIMENSIONS IN MILLIMETERS.
 WEIGHT (KG): 1758, MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
 CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: UPDATE DS QUALITY			
REV: D	VERSION: 04	REVISED: 09:36:15 01/16/2018	TDR: 000001056307
MODEL NO. 617423-006		REF: -	
BY: USJEDIL	Material: -		

BALDOR

GL449/449T F1 FOOT TEFC/CAST IRON BOX W/ LEAD THROAT