ABB BALDOR RELIANCE

Customer information packet

ECP82276T-5

7.5HP, 1180RPM, 3PH, 60HZ, 254T, TEFC, F1
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/18/2026 12:09:46 AM

Specifications

Enclosure	TEFC
Frame	254T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CCSA US
	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1
Current @ Voltage	8.400 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	841
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C

Part Detail

Revision	N
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	09WGZ844
Layout	09LYJ287
Eff. date	11-14-2023
CD Diagram	CD0006
Poles	06
Leads	3#12
Proprietary	False
Created date	11-27-2018

Heater Indicator	No Heater
High Voltage Full Load Amps	8.4 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	IP56
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Termination	Ring Terminals
Motor Standards	NEMA
Motor Type	0954M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	24.78 IN
Power Factor	71
Product Family	Chem Process S/P 32-8 IEEE 841
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4332

CAT.NO.	ECP82276T-5			**P/N**					**ENCLOSURE**	TEFC				
SPEC.	09-0000-0863			**CC**	010A	**FRAME**	254T		**S/N**					
HP	7.5			**CLASS**	F	**HZ**	60	**ODE BRG**	6309	**DE BRG**	6309			
RPM	1180	**RPM MAX**	1800	**PH**	3	**DES**	B	**D.E. BRG.**	45BC03X30X					
VOLT	575			**KVA-CODE**	H			**O.D.E. BRG.**	45BC03X30X					
AMP	8.4			**MOTOR WEIGHT**	348	**GREASE**	POLYREX EM							
RATING	40C AMB-CONT			**MAX. KVAR**	3.4	**BLANK**								
NEMA-NOM-EFF	91	**# OF ROTOR BARS**	27	**SER.F.**	1.15	**IP**	56							
G.MIN.EFF	90.2	**# OF STATOR SLOTS**	36	**PF**	71	**INV.TYPE**	PWM							
TEMP CODE	T3C	**INVERTER-TEMP-CODE**	180											
TEMP =	160	**C HP FR**	60	**C HP TO**	90									
CT HZ FROM	1	**CT HZ TO**	60											
HTR-VOLTS		**HTR-AMPS**		**HTR-WATTS**		**MAX. SPACE HEATER TEMP.**		**VT HZ FROM**	O	**VT HZ TO**	60			

AC Induction Motor Performance Data
Record # 93181
Typical performance - not guaranteed values

Winding: 09WGZ844-R001	**Type:** 0954M	**Enclosure:** TEFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			7.5	**Full Load Torque**	32.4 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			8.4	**Breakdown Torque**	90.2 LB-FT
R.P.M.			1180	**Pull-up Torque**	35.9 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	52.7 LB-FT
NEMA Design Code	B	**KVA Code**	H	**Starting Current**	50.8 A
Service Factor (S.F.)			1.15	**No-load Current**	4.25 A
NEMA Nom. Eff.	91.7	**Power Factor**	71	**Line-line Res. @ 25ºC**	1.6 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	32°C
S.F. Amps				**Temp. Rise @ S.F. Load**	38°C
				Locked-rotor Power Factor	26.1
				Rotor inertia	4.34 lb-ft²

Load Characteristics 575 V, 60 Hz, 7.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	35	55	65	71	75	75	73
Efficiency	83.6	90.3	91.3	91	91.6	90.5	91.6
Speed	1196	1191	1188	1183	1177	1170	1179
Line amperes	4.67	5.65	6.81	8.37	10.1	12.5	9.41


ABB Motors and Mechanical Inc.


WINDING # 09WGZ844

7.5 HP 3 PH 60 HZ 1180 RPM 575 V 0954M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=90.2 PU=35.9 LR=52.7 LRA=50.8





NOTE:
DIMENSIONS IN [ ] ARE MM.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: REVISED TO CORRECT DIMS			
REV: M	VERSION: 12	REVISED: 03:01:00 07/09/2021	TDR: 000001172526
MODEL NO. 09LYJ287			REF: -
BY: USSADEL11			B


BALDOR - RELIANCE®


HOR TEFC 254-6T IEEE-841 VERT JACK SCRWS,DOWEL PROV

09LYJ287


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1