

ABB BALDOR RELIANCE III

Customer information packet

ECP83764T-5

3HP, 1165RPM, 3PH, 60HZ, 213T, 0736M, TEFC, F1

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	213T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CL I GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1.8
Current @ Voltage	3.600 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	AA
Type	AC
Mech. spec.	07J415
Base	
Status	PRD/A
Elec. spec.	07WGY746
Layout	07LYJ415
Eff. date	10-01-2025
CD Diagram	CD0006
Poles	06
Leads	3#14
Proprietary	False
Created date	03-26-2010

Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	3.6 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0736M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	19.50 IN
Power Factor	70
Product Family	Chem Process S/P 32-8 IEEE 841
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1165 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4328									
CAT.NO.	ECP83764T-5								
SPEC.	07J415Y746G1								
HP	3 TE				IP	56			
VOLTS	575								
AMPS	3.6								
R.P.M.	1165								
FRAME	213T		HZ		60		PH	3	
SER.F.	1.15	CODE	K	DES.	B	CLASS		F	
RATING	40C AMB-CONT								
SN									
DE	6307		ODE		6206				
NEMA NOM. EFF.	89.5		P.F.		70				
GUAR. MIN. EFF.	87.5		CC		010A				
T. CODE	T3C		TEMP=		160				

NP3186									
SPEC.	07J415Y746G1								
ABMA DE BRG	35BC03XP30X								
ABMA ODE BRG	30BC02XP30X								
GREASE	POLYREX EM								
MOTOR WEIGHT	211	ROTOR BARS		27	STATOR BARS		36		
MAX. R.P.M.	1800	MAX. KVAR		1.3					
INV.TYPE	PWM								
T=	160								
CHP	60	TO	90						
CT	1.8	TO	60						
VT	0-	TO	60						
HTR-VOLTS	N/A	HTR-AMPS		N/A					
HTR-WATTS			MAX. SPACE HEATER TEMP.					N/A	

AC Induction Motor Performance Data

Record # 92788

Typical performance - not guaranteed values

Winding: 07WGY746-R005			Type: 0736M		Enclosure: TEFC		
Nameplate Data			575 V, 60 Hz: Single Voltage Motor				
Rated Output (HP)		3	Full Load Torque		13.5 LB-FT		
Volts		575	Start Configuration		direct on line		
Full Load Amps		3.6	Breakdown Torque		50.2 LB-FT		
R.P.M.		1165	Pull-up Torque		23.7 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		30.9 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		25.6 A
Service Factor (S.F.)		1.15	No-load Current		1.98 A		
NEMA Nom. Eff.		89.5	Power Factor	70	Line-line Res. @ 25°C		4.15 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		30°C	
S.F. Amps				Temp. Rise @ S.F. Load		36°C	
				Locked-rotor Power Factor		22.9	
				Rotor inertia		0.895 lb-ft²	

Load Characteristics 575 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	33	52	63	70	73	75	72
Efficiency	81.8	88.2	89.3	89.5	88.8	87.7	89.2
Speed	1193	1186	1179	1171	1160	1149	1164
Line amperes	2.12	2.51	3.02	3.61	4.31	5.11	4.03


ABB Motors and Mechanical Inc.


WINDING # 07WGY746

Typical performance - not guaranteed values.

3 HP 3 PH 60 HZ 1165 RPM 575 V 0736M

TORQUES (LB-FT): PO=50.2 PU=23.7 LR=30.9 LRA=25.6





CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10: 24: 49 02/19/2019

BY: ENBRIRO

MTL: -



BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1