ABB BALDOR RELIANCE

Customer information packet

ECP84111T-4

25HP, 1180RPM, 3PH, 60HZ, 324T, TEFC, F1
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/18/2026 11:39:59 PM

Specifications

Enclosure	TEFC
Frame	324T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	25.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSA US
	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1
Current @ Voltage	32.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	841
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3

Part Detail

Revision	K
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	12WGY445
Layout	12LYG135
Eff. date	11-03-2025
CD Diagram	CD0006
Poles	06
Leads	3#8
Proprietary	False
Created date	12-12-2018

Heater Indicator	No Heater
High Voltage Full Load Amps	32.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	IP56
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Termination	Ring Terminals
Motor Standards	NEMA
Motor Type	1264M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	30.74 IN
Power Factor	79
Product Family	Chem Process S/P 32-8 IEEE 841
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4332

CAT.NO.	ECP84111T-4			**P/N**				**ENCLOSURE**	TEFC			
SPEC.	12-0000-0361			**CC**	010A	**FRAME**	324T	**S/N**				
HP	25			**CLASS**	F	**HZ**	60	**ODE BRG**	6312	**DE BRG**	6312	
RPM	1180	**RPM MAX**	1800	**PH**	3	**DES**	B	**D.E. BRG.**	60BC03X30X			
VOLT	460			**KVA-CODE**	G			**O.D.E. BRG.**	60BC03X30X			
AMP	32			**MOTOR WEIGHT**	638	**GREASE**	POLYREX EM					
RATING	40C AMB-CONT			**MAX. KVAR**	9	**BLANK**						
NEMA-NOM-EFF	93	**# OF ROTOR BARS**	42	**SER.F.**	1.15	**IP**	56					
G.MIN.EFF	91.7	**# OF STATOR SLOTS**	54	**PF**	79	**INV.TYPE**	PWM					
TEMP CODE	T3	**INVERTER-TEMP-CODE**	200									
TEMP =	200	**C HP FR**	60	**C HP TO**	90							
CT HZ FROM	1	**CT HZ TO**	60									
HTR-VOLTS		**HTR-AMPS**		**HTR-WATTS**		**MAX. SPACE HEATER TEMP.**		**VT HZ FROM**	O	**VT HZ TO**	60	

AC Induction Motor Performance Data
Record # 47214
Typical performance - not guaranteed values

Winding: 12WGY445-R012	**Type:** 1264M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			25	**Full Load Torque**	111 LB-FT
Volts			460	**Start Configuration**	direct on line
Full Load Amps			32	**Breakdown Torque**	283 LB-FT
R.P.M.			1180	**Pull-up Torque**	131 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	156 LB-FT
NEMA Design Code	B	**KVA Code**	G	**Starting Current**	178 A
Service Factor (S.F.)			1.15	**No-load Current**	12.4 A
NEMA Nom. Eff.	93	**Power Factor**	79	**Line-line Res. @ 25ºC**	0.29206 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	48°C
S.F. Amps				**Temp. Rise @ S.F. Load**	60°C
				Locked-rotor Power Factor	27.6
				Rotor inertia	12.2 LB-FT2

Load Characteristics 460 V, 60 Hz, 25 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	47	67	76	79	81	81	80
Efficiency	90.3	93.2	93.6	93.2	92.3	91	92.7
Speed	1194.5	1190.4	1185.5	1180.1	1173.8	1165.5	1176
Line amperes	14.4	19	24.7	31.6	39.1	48.1	36.1


ABB Motors and Mechanical Inc.


WINDING # 12WGY445

25 HP 3 PH 60 HZ 1180 RPM 460 V 1264M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=283 PU=131 LR=156 LRA=178





12LYG135
(1232 - 1272) = 30.74[781]
14.24[362]
APPROXIMATE CENTER OF GRAVITY ±.50
1.91[49]
5.25[133]
.50 KEY 3.88 [99] LONG
.84[21]
Ø2.125[53.98] 2.124[53.95]
.0015 A
INPRO SEAL (EA. END)
DRAIN FITTING (EA. END)
.38-16 TAP (GND LOC.) (EA. END)
.44[11]
10.50[267]
.44[11]
2 HOLES EA. END Ø.38 THRU
10.50[267]
1.00[25]
12.00[305]
5.25[133]
1.88[48]
3.54[90]
3.54[90]
14.00[356]
4 HOLES .38-16 TAP THRU (JACK SCREWS) (2 EA. END)
17.87[454]
14.26[362]
8.46[215]
PLUG (EA. END)
APPROXIMATE CENTER OF GRAVITY ±.50
3.22[82]
16.23[412]
.29[7]
8.00 +.00 -.06 [203 0 -2]
4.25[108]
.005
.90[23]
8 HOLES Ø.66
.44[11]
.44[11]
6.25[159]
6.25[159]
LEAD HOLE 2.00 NPT
2.00[51]
2.00[51]
11.75[298]
7.25[184]
14.50[368]
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: UPDATE NP GRAPHICS TO MATCH NP USED ON CAT SPECS
REV: H
VERSION: 08
REVISED: 12:13:20 11/02/2022
TDR: 000001194199
MODEL NO. 12LYG135
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
HORZ TEFC 324-6T IEEE-841 W/312 BRGS, JACK SCRWS, DOWEL PROV
12LYG135


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1