

ABB BALDOR RELIANCE III

Customer information packet

ECP84117T-5

30HP, 1180RPM, 3PH, 60HZ, 326T, TEFC, F1

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	326T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CCSA US CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	1
Current @ Voltage	30.000 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	841
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3

Part Detail

Revision	K
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	12WGZ235
Layout	12LYG135
Eff. date	11-03-2025
CD Diagram	CD0006
Poles	06
Leads	3#10
Proprietary	False
Created date	12-12-2018

Heater Indicator	No Heater
High Voltage Full Load Amps	30.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	IP56
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Termination	Ring Terminals
Motor Standards	NEMA
Motor Type	1268M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	30.74 IN
Power Factor	80
Product Family	Chem Process S/P 32-8 IEEE 841
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4332

CAT.NO.	ECP84117T-5		P/N			ENCLOSURE	TEFC				
SPEC.	12-0000-0369		CC	010A	FRAME	326T	S/N				
HP	30		CLASS	F	HZ	60	ODE BRG	6312			
RPM	1180	RPM MAX	1800	PH	3	DES	B	D.E. BRG.	60BC03X30X		
VOLT	575		KVA-CODE	G		O.D.E. BRG.	60BC03X30X				
AMP	30		MOTOR WEIGHT	635		GREASE	POLYREX EM				
RATING	40C AMB-CONT		MAX. KVAR	9.8		BLANK					
NEMA-NOM-EFF	93	# OF ROTOR BARS	42	SER.F.	1.15	IP	56				
G.MIN.EFF	91.7	# OF STATOR SLOTS	54	PF	80	INV.TYPE	PWM				
TEMP CODE	T3		INVERTER-TEMP-CODE	200							
TEMP =	200	C HP FR	60	C HP TO	90						
CT HZ FROM	1	CT HZ TO	60								
HTR-VOLTS		HTR-AMPS		HTR-WATTS		MAX. SPACE HEATER TEMP.		VT HZ FROM	<input type="radio"/>	VT HZ TO	60


ABB Motors and Mechanical Inc.

WINDING # 12WGZ235

Typical performance - not guaranteed values.

30 HP 3 PH 60 HZ 1180 RPM 575 V 1268M

TORQUES (LB-FT): PO=340 PU=153 LR=188 LRA=174



CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIRO
MTL: -		© □

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1