

# ABB BALDOR RELIANCE III

---

## Customer information packet

ECP84413T-5

150HP, 3570RPM, 3PH, 60HZ, 445TS, A4478M, TEFC

Class - CLI GP A,B,C,D

Division - Division II

**Specifications**

<b>Enclosure</b>	TEFC
<b>Frame</b>	445TS
<b>Frame Material</b>	Iron
<b>Frequency</b>	60.00 Hz
<b>Haz Area Class and Group</b>	CLI GP A,B,C,D
<b>Haz Area Division</b>	Division II
<b>Motor Letter Type</b>	Three Phase
<b>Output @ Frequency</b>	150.000 HP @ 60 HZ
<b>Phase</b>	3
<b>Synchronous Speed @ Frequency</b>	3600 RPM @ 60 HZ
<b>Voltage @ Frequency</b>	575.0 V @ 60 HZ
<b>Agency Approvals</b>	CCSA US UR
<b>Ambient Temperature</b>	40 °C
<b>Auxiliary Box</b>	NO AUXILLARY BOX
<b>Base Indicator</b>	Rigid
<b>Bearing Grease Type</b>	Polyrex EM (-20F +300F)
<b>Constant Torque Speed Range</b>	10-60
<b>Current @ Voltage</b>	131.000 A @ 575.0 V
<b>Design Code</b>	B
<b>Drip Cover</b>	No Drip Cover
<b>Duty Rating</b>	CONT
<b>Efficiency @ 100% Load</b>	95.0 %
<b>Feedback Device</b>	NO FEEDBACK
<b>Haz Area Temp Code</b>	T3
<b>Heater Indicator</b>	No Heater
<b>High Voltage Full Load Amps</b>	131.0 a
<b>Insulation Class</b>	F
<b>Inverter Code</b>	Not Inverter
<b>KVA Code</b>	G
<b>Lifting Lugs</b>	Standard Lifting Lugs
<b>Motor Lead Quantity/Wire Size</b>	3 @ 1 AWG

**Part Detail**

<b>Revision</b>	B
<b>Type</b>	AC
<b>Mech. spec.</b>	
<b>Base</b>	
<b>Status</b>	PRD/A
<b>Elec. spec.</b>	A44WG4880
<b>Layout</b>	617434-659
<b>Eff. date</b>	12-10-2025
<b>CD Diagram</b>	416820-036
<b>Poles</b>	02
<b>Leads</b>	3#1
<b>Proprietary</b>	False
<b>Created date</b>	03-14-2022

<b>Motor Standards</b>	None
<b>Motor Type</b>	A4478M
<b>Mounting Arrangement</b>	F1
<b>No Load Current</b>	28.0 a
<b>Number of Poles</b>	2
<b>Overall Length</b>	41.22 IN
<b>Power Factor</b>	90
<b>Pulley End Bearing Type</b>	Ball
<b>Pulley Face Code</b>	Standard
<b>Service Factor</b>	1.15
<b>Shaft Diameter</b>	2.375 IN
<b>Shaft Ground Indicator</b>	No Shaft Grounding
<b>Shaft Rotation</b>	Reversible
<b>Shaft Slinger Indicator</b>	No Slinger
<b>Speed</b>	3570 rpm
<b>Speed Code</b>	Single Speed
<b>Starting Method</b>	Direct on line
<b>Thermal Device - Bearing</b>	None
<b>Thermal Device - Winding</b>	None

**Nameplate**

**NP4566**

<b>CAT NO</b>	ECP84413T-5	<b>SPEC NO.</b>	A44-0000-4880						
<b>HP</b>	150	<b>AMPS</b>	131	<b>VOLTS</b>	575	<b>DESIGN</b>	B		
<b>FRAME SIZE</b>	445TS	<b>RPM</b>	3570	<b>HZ</b>	60	<b>AMB</b>	40	<b>SF</b>	1.15
<b>D.E. BRG.DATA</b>	6313	<b>O.D.E. BRG.DATA</b>	6313	<b>PH</b>	3	<b>DUTY</b>	CONT	<b>INSUL.CLASS</b>	F
<b>D.E. BRG.</b>	65BC03J30X	<b>TYPE</b>	ENCL	TEFC	<b>CODE</b>	G			
<b>O.D.E. BRG.</b>	65BC03J30X	<b>POWER FACTOR</b>	90	<b>NEMA-NOM-EFFICIENCY</b>	95				
<b>3/4 LOAD EFF.</b>	95.7	<b>IP</b>	56	<b>MAX CORR KVAR</b>	20	<b>GUARANTEED EFFICIENCY</b>	94.1		
<b>TEMP CODE</b>	T3	<b>TEMP =</b>	200						
<b>CHP HZ</b>	60-75	<b>CT HZ</b>	10-60	<b>VT HZ</b>	0-60				
<b>INVERTER-TEMP-CODE</b>	T3								
<b>SER.NO.</b>		<b>MOTOR WEIGHT</b>							

---

**000613007EX**

---

<b>CAT NO</b>	ECP84413T-5	<b>SPEC NO.</b>	A44-0000-4880	
<b>NO. ROTOR BARS</b>	40	<b>GREASE TYPE</b>	POLYREX EM	
<b>NO. SLOTS</b>	48	<b>NL AMPS AT RATED VOLTAGE</b>	28	
<b>5 YEAR WARRANTY</b>		<b>WINDING RES @25 C</b>	0.045	<b>OHMS</b>
<b>MFG. DATE</b>		<b>SER.NO</b>		

---

REL. S.O.	FRAME	HP	TYPE	PHASE/HERTZ	RPM	VOLTS
	445TS	150	P	3/60	3570	575

AMPS	DUTY	AMB °C/ INSUL.	S.F.	NEMA DESIGN	CODE LETTER	ENCL.
131	CONT	40/F	1.15	B	G	TEFC

E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES. @25 °C OHMS (BETWEEN LINES)
498934	418143-8BE	---	---	.0457

**PERFORMANCE**

LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY
NO LOAD	0	27.7	3600	6.89	0
1/4	37.5	47.4	3593	63.9	92.9
2/4	75.1	72.2	3585	81.7	95.3
3/4	113	100	3578	87.8	95.7
4/4	150	131	3570	89.9	95.6
5/4	187	163	3562	90.4	95.2

**SPEED TORQUE**

	RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES
LOCKED ROTOR	0	138	304	865
PULL UP	288	110	242	797
BREAKDOWN	3461	280	618	442
FULL LOAD	3570	100	221	131

AMPERES SHOWN FOR 575. VOLT CONNECTION. IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE

REMARKS: CALCULATED DATA  
NEMA NOMINAL EFFICIENCY = 95.0 PCT.



DR. BY G. R. WEBB  
CK. BY W. L. SMITH  
APP. BY W. L. SMITH  
DATE 03/11/13


**A-C MOTOR  
PERFORMANCE A44WG4880-R001  
DATA** ISSUE DATE 03/11/13

FRAME 445TS  
HP 150  
TYPE P  
PHASE/HERTZ 3/60

RPM 3570  
VOLTS 575  
AMPS 131  
DUTY CONT  
AMB °C/INSUL 40/F

NEMA DESIGN B  
CODE LETTER G  
ENCLOSURE TEFC  
E/S 498934

TEST S.O. CALCULATED DATA  
TEST DATE ---  
STATOR RES. @ 25 °C .0457  
OHMS (BETWEEN LINES)





AMPERES SHOWN FOR 575 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.



DR. BY G. R. WEBB  
CK. BY W. L. SMITH  
APP. BY W. L. SMITH  
DATE 03/11/13

**A-C MOTOR  
PERFORMANCE CURVES** A44WG4880-R001  
ISSUE DATE 03/11/13





416820-036

**A-C MOTOR  
CONNECTION DIAGRAM  
STANDARD 3 LEAD CONNECTED**



(N.P. 1575-BA)

416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682	REVISED: 11: 54: 06 04/30/2010	
MTL: -	BY: RAGRA	

**BALDOR**

CONN DIAG - STANDARD 3 LEAD  
SH 1 of 1