ABB BALDOR RELIANCE

Customer information packet

ECR583004-PPN

M3BN 587MLA 4P B3 300HP

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
9/7/2026 9:41:47 AM

Department/Author	Date of issue	Lang.	Rev. date	Our ref.
MLA000/TISA	11.10.2018	En		3GZF021035-1234

Customer ref.	Saving Ident	Rev./Changed by	Pages
	TMAA-ASUG9J-TISA28	A	1/3

Driven Motor:

Catalog Number		**ECR583004-PPN**		
Motor type code		M3BN 587 MLA 4		
Motor product code		3GBN982410-ADKBA01		
Motor type		Squirrel cage Motor		
Mounting designation		IM 1001		
Protected by enclosure		IP66		
Method of cooling		TEFC		
Insulation		Class F (Shock Resistant)		
Service factor		SF1.15 TEMP RISE CLASS B		
Standards		NEMA		
International efficiency classification (IEC 60034-30)		IE3		
Ambient temperature, max.		40 °C		
Altitude, max.		3280 ft.a.s.l.		
Duty type		Continuous		
Temp. rise		Class B		
Connection of stator winding		Delta		
Rated output		300 HP		
Voltage		460 V		
Frequency		60 Hz		
Speed		1792 r/min		
Current		343 Amps		
Locked rotor Amps		770 %	Code H	
Locked rotor torque		250 %		
Breakdown torque		310 %		
No load current		123 Amps		
Rated torque		880 lb-ft		
Load characteristics	Load %	Current Amps	Efficiency %	Power Factor
	100	343	96,2	0,85
	75	269	96,4	0,81
	50	202	95,7	0,72
NEMA nominal efficiency			96,2 %	

Typical calculated values to NEMA. -

ABB Oy

Motors & Generators
Visiting Address
Strömbergin puistotie 5 A
VAASA
FINLAND
Postal Address
P.O.Box 633
FI-65101 VAASA
FINLAND
Telephone
+358 10 222 000
Telefax
+358 10 224 7372

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
©Copyright 2018 ABB

Motor type code: M3BN 587 MLA 4

Rated output	300 HP	Power Factor	0,85
Voltage	460 V	Rated torque	880 lb-ft
Frequency	60 Hz	Locked rotor Amps	770 %
Speed	1792 r/min	Locked rotor torque	250 %
Current	343 Amps	Breakdown torque	310 %



ABB Oy

Motors & Generators
Visiting Address
Strömbergin puistotie 5 A
VAASA
FINLAND
Postal Address
P.O.Box 633
FI-65101 VAASA
FINLAND
Telephone
+358 10 222 000
Telefax
+358 10 224 7372

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
©Copyright 2018 ABB

PWM
Switch. freq. 3kHz
FWP 460VD 60Hz

Drive1

Rated power	75 HP
Rated voltage	117 V
Nominal frequency	15,3 Hz
Type of connection	Delta
Rated torque	876 lb-ft
Speed	450 rpm
Current	345 Amps

Drive2

Rated power	300 HP
Rated voltage	460 V
Nominal frequency	60,4 Hz
Type of connection	Delta
Rated torque	876 lb-ft
Speed	1800 rpm
Current	377 Amps

Constant torque 450 – 1800rpm

ABB Oy

Motors & Generators
Visiting Address
Strömbergin puistotie 5 A
VAASA
FINLAND
Postal Address
P.O.Box 633
FI-65101 VAASA
FINLAND
Telephone
+358 10 222 000
Telefax
+358 10 224 7372

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
©Copyright 2018 ABB

Diagram of connection
Anschluss-Schema
Schema de branchement



Connection of terminals
Anschluss des Motors
Branchement des bornes



Y-connection
Y-Schaltung
Connection etoile





D-connection
D-Schaltung
Connection triangle



Direction of rotation with phase sequence shown in picture
Drehrichtung nach Schaltbild
Direction de rotation avec branchement ci-dessus

Direction of rotation with reversed phase sequence
Drehrichtung mit umgekehrter Phasenfolge
Direction de rotation avec sequence de phase reversée

Motor No Maschine Nr No du moteur	
ABB Oy, Motors	3GZF321100-1 E

Connection Diagram				Document No: 3GZF321100-1 E	
Description:	3-PHASE SQUIRREL-CAGE MOTOR				
Unit:	Motors	Issued by:	M Prusi	Replaces:	
Date:	21.09.2005	Approved by:	Jari Raittila	Replaced by:	
ABB Oy		Customer Reference:			



1TB1...1TB2 BIMETAL DETECTORS, TYPE NCC
BIMETALL-THERMOSCHALTER, TYP NCC
SONDES BIMETALLIQUES, TYPE NCC

Motor No
Maschine Nr
Moteur No

ABB Oy, Electrical Machines
LV Motors

3GZF321200-35 B

Accessory Connection Diagram

Document No: 3GZF321200-35 B

Description: BIMETAL DETECTORS

Unit:	Electrical Machines, LV Motors	Issued by:	K.Högkvist	Replaces:
Date:	16.01.2002	Approved by:	M.Prusi	Replaced by:

ABB Oy Customer Reference:



PTC-THERMISTORS
PTC-TEMPERATURFÜHLER
SONDES THERMIQUE PTC

Motor No
Maschine Nr
Moteur No

ABB Oy, Motors | 3GZF321200-1 D

Accessory Connection Diagram

Document No: 3GZF321200-1 D

Description: PTC-THERMISTORS

Unit:	Motors	Issued by:	K.Högkvist	Replaces:
Date:	30.11.2005	Approved by:	M.Prusi	Replaced by:

ABB Oy | Customer Reference:



Additional information:

Dimension Print	Motor Type: M3BN 587ML_4.. B3, B6, B7, B8, V5, V6	Document No: 3GZF500098-174 A 14 BN 587 A
Description: SQUIRREL CAGE MOTOR, CABLE ENTRY LHS, SPECIAL SHAFT, SLOTTED FEET HOLES. DIMENSIONS IN INCHES, MOTOR SIZES 586/587.		

Unit:	ABB Oy, Motors and Generators	Issued by:	N.Palokangas	Replaces:
Date:	21.11.2019	Approved by:	S.Tikkanen	Replaced by:

ABB Oy	Customer Reference:	ABB