

ABB BALDOR RELIANCE III

Customer information packet

ECR91256TR-4

125HP, 1190RPM, 3PH, 60HZ, 445T, A44090M, TEFC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	445T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	125.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Mobil SHC 220 (Athens Only)
Constant Torque Speed Range	6-60
Current @ Voltage	153.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.4 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	153.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	No Lifting Lugs
Max Speed	3000 rpm
Motor Lead Quantity/Wire Size	3 @ 2 AWG
Motor Standards	NEMA

Part Detail

Revision	G
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A44WG5185
Layout	617427-315
Eff. date	12-10-2025
CD Diagram	416820-036
Poles	06
Leads	3#2
Proprietary	False
Created date	02-06-2015

Motor Type	A44090M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	44.75 IN
Power Factor	80
Product Family	Crusher / Chipper
Pulley End Bearing Type	Roller
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	3.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1190 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

000613007PV												
CAT NO	ECR91256TR-4			SPEC NO.	P44G1808							
HP	125	AMPS	153		VOLTS	460		DESIGN	A			
RPM	1190	RPM MAX	3000	HZ	60	AMB	40	SF	1.15			
D.E. BRG.DATA	NU222			O.D.E. BRG.DATA	6318		PH	3	DUTY	CONT	INSUL.CLASS	F
FRAME	445T	I.P.	55	TYPE	P	ENCL	TEFC	CODE	H			
POWER FACTOR	80	3/4 LOAD EFF.			95.6		NEMA NOM EFFICIENCY			95.4		
CHP HZ	60-90	CT HZ	6-60	VT HZ	6-60							
SER.NO.				MOTOR WEIGHT								

NP2496L	
MOBIL SHC -220 GREASE	

REL. S.O.	FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS
	445	125	P	3/60	1190	460
AMPS	DUTY	AMB °C/ INSUL.	S.F.	NEMA DESIGN	CODE LETTER	ENCL.
153	CONT	40/F	1.15	A	H	TEFC
E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES. @25 °C OHMS (BETWEEN LINES)		
-	418143080HE	---	---	.0308		
PERFORMANCE						
LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY	
NO LOAD	0	59.9	1200	4.04	0	
1/4	31.3	71.4	1198	44.7	91.9	
2/4	62.6	93.2	1196	66.3	94.9	
3/4	93.7	121	1194	75.6	95.6	
4/4	125	153	1192	79.8	95.6	
5/4	156	187	1189	81.9	95.4	
SPEED TORQUE						
		RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES	
LOCKED ROTOR		0	268	1479	1047	
PULL UP		960	195	1077	806	
BREAKDOWN		1155	265	1459	555	
FULL LOAD		1192	100	551	153	
AMPERES SHOWN FOR 460. VOLT CONNECTION. IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE						
REMARKS: TYPICAL DATA XE MOTOR-NEMA NOM. EFF. 95.0 %						
		DR. BY CD		A-C MOTOR PERFORMANCE DATA A44WG5185-R001 ISSUE DATE 02/06/20		
		CK. BY T. KELATI				
		APP. BY T. KELATI				
		DATE 02/06/2015				
Page 6 of 1						

REL S.O.

 RPM **1190**

 S.F. **1.15**

 ROTOR **418143080HE**

 FRAME **445**

 VOLTS **460**

 NEMA DESIGN **A**

 TEST S.O. **TYPICAL DATA**

 HP **125**

 AMPS **153**

 CODE LETTER **H**

 TEST DATE **---**

 TYPE **P**

 DUTY **CONT**

 ENCLOSURE **TEFC**


 STATOR RES. @ 25 °C **.0308**

 PHASE/HERTZ **3/60**

 AMB °C/INSUL **40/F**

 E/S **-**

OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

BALDOR
A MEMBER OF THE ABB GROUP


DR. BY CD
CK. BY T. KELATI
APP. BY T. KELATI
DATE 02/06/2015

**A-C MOTOR
PERFORMANCE
CURVES**

A44WG5185-R001
ISSUE DATE 02/06/2015

617427-315

FRAMES G445T/444T



617427-319

DUTY MASTER ALTERNATING CURRENT MOTORS SQUIRREL-CAGE INDUCTION



617427-315

ENCLOSURE: TOTALLY ENCLOSED

MOUNTING: FOOT

FRAMES G445T/444T

COOLING: FAN COOLED



① OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.

MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .08 T.I.R.

CONDUIT BOX LOCATED ON OPPOSITE SIDE WHEN F-2, W-1, W-4, W-5, W-7, OR C-1 MOUNTING IS SPECIFIED

DIMENSIONS ARE IN MILLIMETERS FOR INCHES SEE SHEET 1

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

SHEET NUMBER
2 OF 2

51E-27-119

REV. DESC: NEW
REV: - VERSION: 00
MODEL NO. 617427-315
BY: RAGAHJ

REVISED: 09/06/36 12/05/2014

TDR: 000000881952


BALDOR

G445T/444T STD - FOOTED - SIDE/CENTER C.I. C/B ROLLER BRG

617427-315

416820-036

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575-BA)

416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682		REVISED: 11: 54: 06 04/30/2010
MTL: -		BY: RAGRA

BALDOR

CONN DIAG - STANDARD 3 LEAD
SH 1 of 1