ABB BALDOR RELIANCE

Customer information packet

ECP84413T-5

150HP, 3570RPM, 3PH, 60HZ, 445TS, A4478M, TEFC
Class - CLI GP A,B,C,D
Division - Division II

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/18/2026 7:37:06 PM

Specifications

Enclosure	TEFC
Frame	445TS
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	150.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CCSA US
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	10-60
Current @ Voltage	131.000 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.0 %
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3
Heater Indicator	No Heater
High Voltage Full Load Amps	131.0 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Motor Lead Quantity/Wire Size	3 @ 1 AWG

Part Detail

Revision	B
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A44WG4880
Layout	617434-659
Eff. date	12-10-2025
CD Diagram	416820-036
Poles	02
Leads	3#1
Proprietary	False
Created date	03-14-2022

Motor Standards	None
Motor Type	A4478M
Mounting Arrangement	F1
No Load Current	28.0 a
Number of Poles	2
Overall Length	41.22 IN
Power Factor	90
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	2.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3570 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP4566												
CAT NO	ECP84413T-5	**SPEC NO.**	A44-0000-4880									
HP	150	**AMPS**	131	**VOLTS**	575	**DESIGN**	B					
FRAME SIZE	445TS	**RPM**	3570	**HZ**	60	**AMB**	40	**SF**	1.15			
D.E. BRG.DATA	6313	**O.D.E. BRG.DATA**	6313	**PH**	3	**DUTY**	CONT	**INSUL.CLASS**	F			
D.E. BRG.	65BC03J30X	**TYPE**	**ENCL**	TEFC	**CODE**	G						
O.D.E. BRG.	65BC03J30X	**POWER FACTOR**	90	**NEMA-NOM-EFFICIENCY**	95							
3/4 LOAD EFF.	95.7	**IP**	56	**MAX CORR KVAR**	20	**GUARANTEED EFFICIENCY**	94.1					
TEMP CODE	T3	**TEMP =**	200									
CHP HZ	60-75	**CT HZ**	10-60	**VT HZ**	0-60							
INVERTER-TEMP-CODE	T3											
SER.NO.		**MOTOR WEIGHT**										

000613007EX					
CAT NO	ECP84413T-5	**SPEC NO.**	A44-0000-4880		
NO. ROTOR BARS	40	**GREASE TYPE**	POLYREX EM		
NO. SLOTS	48	**NL AMPS AT RATED VOLTAGE**		28	
5 YEAR WARRANTY		**WINDING RES @25 C**	0.045	**OHMS**	
MFG. DATE		**SER.NO**			

REL. S.O.	FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS
	445TS	150	P	3/60	3570	575

AMPS	DUTY	AMB °C/ INSUL.	S.F.	NEMA DESIGN	CODE LETTER	ENCL.
131	CONT	40/F	1.15	B	G	TEFC

E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES.@25 °C OHMS (BETWEEN LINES)
498934	418143-8BE	---	---	.0457

PERFORMANCE

LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY
NO LOAD	0	27.7	3600	6.89	0
1/4	37.5	47.4	3593	63.9	92.9
2/4	75.1	72.2	3585	81.7	95.3
3/4	113	100	3578	87.8	95.7
4/4	150	131	3570	89.9	95.6
5/4	187	163	3562	90.4	95.2

SPEED TORQUE

	RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES
LOCKED ROTOR	0	138	304	865
PULL UP	288	110	242	797
BREAKDOWN	3461	280	618	442
FULL LOAD	3570	100	221	131

AMPERES SHOWN FOR 575. VOLT CONNECTION. IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE

REMARKS: CALCULATED DATA
NEMA NOMINAL EFFICIENCY = 95.0 PCT.


BALDOR
A MEMBER OF THE ABB GROUP

DR. BY G. R. WEBB
CK. BY W. L. SMITH
APP. BY W. L. SMITH
DATE 03/11/13

A-C MOTOR PERFORMANCE DATA

A44WG4880-R001
ISSUE DATE 03/11/13

FRAME 445TS	RPM 3570	S.F. 1.15	ROTOR 418143-8BE
HP 150	VOLTS 575	NEMA DESIGN B	TEST S.O. CALCULATED DATA
TYPE P	AMPS 131	CODE LETTER G	TEST DATE ---
PHASE/HERTZ 3/60	DUTY CONT	ENCLOSURE TEFC	STATOR RES.@ 25 °C .0457
	AMB °C/INSUL 40/F	E/S 498934	OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 575 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

BALDOR
A MEMBER OF THE ABB GROUP

DR. BY	G. R. WEBB
CK. BY	W. L. SMITH
APP. BY	W. L. SMITH
DATE	03/11/13

A-C MOTOR PERFORMANCE CURVES A44WG4880-R001 ISSUE DATE 03/11/13


SHEET NUMBER 1 OF 2


DUTY MASTER ALTERNATING CURRENT MOTORS


617434-659


ENCLOSURE: TOTALLY ENCLOSED | SQUIRREL-CAGE INDUCTION | COOLING: FAN COOLED

MOUNTING: FOOT, F-1 SIDE | G444TS/G445TS FRAME MOUNTING HOLES | ENCLOSURE ENHANCEMENT: 841-XL









1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

DIMENSIONS ARE IN INCHES.
WEIGHT (LBS): 2130 ±15% DEPENDING ON RATING.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .0015" T.I.R.

REV. DESC: NEW DRAWING			
REV: -	VERSION: 00	REVISED: 01:22:33 12/17/2018	TDR: 000001093408
MODEL NO. 617434-659			REF: -
BY: USJEDIL	Material: _	C	G445/444TS TEFC F1 FOOT CI C/BOX/JACKSCREW/DOWEL PINS/INPROS

BALDOR

617434-659

617434-659


SHEET NUMBER 2 OF 2


DUTY MASTER ALTERNATING CURRENT MOTORS


617434-659


ENCLOSURE: TOTALLY ENCLOSED | SQUIRREL-CAGE INDUCTION | COOLING: FAN COOLED

MOUNTING: FOOT, F-1 SIDE | G444TS/G445TS FRAME MOUNTING HOLES | ENCLOSURE ENHANCEMENT: 841-XL









1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

DIMENSIONS ARE IN MILLIMETERS.
WEIGHT (KGS): 966 ±15% DEPENDING ON RATING.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .04 T.I.R.

REV. DESC: NEW DRAWING			
REV: -	VERSION: 00	REVISED: 01:22:33 12/17/2018	TDR: 000001093408
MODEL NO. 617434-659			REF: -
BY: USJEDIL	Material: _	C	G445/444TS TEFC F1 FOOT CI C/BOX/JACKSCREW/DOWEL PINS/INPROS


BALDOR

617434-659

617434-659

416820–036

A–C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575–BA)

416820–036

REV. DESC: LOADED TO BUS, C/R 335225			BALDOR
REV. LTR: –	VERSION: 00	TDR: 000000538207	
FILE: \MGA\00000\682		REVISED: 11:54:06 04/30/2010	CONN DIAG – STANDARD 3 LEAD
MTL: –		BY: RAGRA	SH 1 of 1