

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION

617434-845

ENCLOSURE: TOTALLY ENCLOSED





MOUNTING: FOOT, F-1 SIDE

FRAME G449T

INCLUDES G447T FRAME MOUNTING HOLES
CAST IRON C/BOX
SIMILAR TO ECP844256T-4

COOLING: FAN COOLED

ENCLOSURE ENHANCEMENT: 841-XL/661-XL



1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET

WEIGHT=3045 LBS $\pm 15\%$ DEPENDING ON RATING.

MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END
OF STANDARD SHAFT EXTENSION IS .0015 T.I.R

DIMENSIONS ARE IN INCHES.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION

REV. DESC: NEW	VERSION: 00	REVISED: 03:15:33 09/30/2019	TDR: 000001121301
MODEL NO. 617434-845			
BY: RAGHZT			

BALDOR

G449T TEFC F1 FT -841XL/661XL -INPRO -AIR DEFLECTOR -ROLLER

617434-845

617434-845