

ABB BALDOR RELIANCE III

Customer information packet

ECR91506TR-4

150HP, 1190RPM, 3PH, 60HZ, 447T, A44112M, TEFC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	447T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	150.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Mobil SHC 220 (Athens Only)
Constant Torque Speed Range	10-60
Current @ Voltage	180.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.8 %
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	180.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	No Lifting Lugs
Max Speed	3000 rpm
Motor Lead Quantity/Wire Size	6 @ 2 AWG

Part Detail

Revision	H
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A44WG5186
Layout	617427-355
Eff. date	04-08-2021
CD Diagram	416820-036
Poles	06
Leads	3#2 (02 per group)
Proprietary	False
Created date	02-06-2015

Motor Standards	NEMA
Motor Type	A44112M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	48.24 IN
Power Factor	82
Product Family	Crusher / Chipper
Pulley End Bearing Type	Roller
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	3.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1190 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

000613007PV															
CAT NO	ECR91506TR-4			SPEC NO.		P44G1811									
HP	150	AMPS		180		VOLTS		460		DESIGN		A			
RPM	1190	RPM MAX		3000		HZ		60	AMB		40	SF	1.15		
D.E. BRG.DATA	NU222		O.D.E. BRG.DATA				6318		PH		3	DUTY	CONT	INSUL.CLASS	F
FRAME	447T		I.P.		55	TYPE		P	ENCL		TEFC	CODE		H	
POWER FACTOR	82		3/4 LOAD EFF.				95.7			NEMA NOM EFFICIENCY				95.8	
CHP HZ	60-90		CT HZ		10-60		VT HZ		6-60						
SER.NO.				MOTOR WEIGHT				2459							

NP2496L	
MOBIL SHC -220 GREASE	

REL. S.O.	FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS
	447TY	150	P	3/60	1190	460
AMPS	DUTY	AMB °C/ INSUL.	S.F.	NEMA DESIGN	CODE LETTER	ENCL.
180	CONT	40/F	1.15	A	H	TEFC
E/S	ROTOR	TEST S.O.		TEST DATE	STATOR RES.@25 °C OHMS (BETWEEN LINES)	
-	418143080NE	---		---	.0259	
PERFORMANCE						
LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY	
NO LOAD	0	66.0	1200	4.40	0	
1/4	37.5	80.0	1198	47.8	91.9	
2/4	75.0	107	1196	69.2	95.0	
3/4	112	141	1194	77.8	95.7	
4/4	150	180	1191	81.3	95.7	
5/4	187	221	1189	83.0	95.5	
SPEED TORQUE						
		RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES	
LOCKED ROTOR		0	271	1793	1218	
PULL UP		960	192	1267	927	
BREAKDOWN		1152	261	1723	653	
FULL LOAD		1191	100	661	180	
AMPERES SHOWN FOR 460. VOLT CONNECTION. IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE						
REMARKS: TYPICAL DATA XE MOTOR-NEMA NOM. EFF. 95.8 %						
		DR. BY CD		A-C MOTOR PERFORMANCE A44WG5186-R001 DATA ISSUE DATE 05/08/19		
		CK. BY T. KELATI				
		APP. BY T. KELATI				
		DATE 02/06/2015				
		Page 6 of 10				

REL S.O.

 RPM **1190**

 S.F. **1.15**

 ROTOR **418143080NE**

 FRAME **447TY**

 VOLTS **460**

 NEMA DESIGN **A**

 TEST S.O. **TYPICAL DATA**

 HP **150**

 AMPS **180**

 CODE LETTER **H**

 TEST DATE **---**

 TYPE **P**

 DUTY **CONT**

 ENCLOSURE **TEFC**


 STATOR RES. @ 25 °C **.0259**

 PHASE/HERTZ **3/60**

 AMB °C/INSUL **40/F**

 E/S **-**

OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.


BALDOR
A MEMBER OF THE ABB GROUP

DR. BY CD
CK. BY T. KELATI
APP. BY T. KELATI
DATE 02/06/2015

**A-C MOTOR
PERFORMANCE
CURVES**

A44WG5186-R001
ISSUE DATE 05/08/19

REL. S.O.	RPM 1190	S.F. 1.15	ROTOR 418143080NE
FRAME 447TY	VOLTS 460	NEMA DESIGN A	TEST S.O. TYPICAL DATA
HP 150	AMPS 180	CODE LETTER H	TEST DATE ---
TYPE P	DUTY CONT	ENCLOSURE TEFC	STATOR RES. @ 25 °C .0259
PHASE/HERTZ 3/60	AMB °C/INSUL 40/F	E/S -	OHMS (BETWEEN LINES)



THERMAL LIMIT CURVE

REMARKS: XE MOTOR-NEMA NOM. EFF. 95.8 %

AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.



DR. BY	CD
CK. BY	T. KELATI
APP. BY	T. KELATI
DATE	02/06/2015

**A-C MOTOR
PERFORMANCE
CURVES**

A44WG5186-R001
ISSUE DATE 05/08/19 Page 8 of 11

SQUIRREL-CAGE INDUCTION

INCLUDES 445T FRAME MOUNTING HOLES



DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION



ENCLOSURE: TOTALLY ENCLOSED

FRAME G447T ABOVE NEMA RATINGS

COOLING: FAN COOLED

MOUNTING: FOOT

INCLUDES 445T FRAME MOUNTING HOLES



1. GROUND HOLES QTY 1 1/2-13 TAP; QTY 1 3/8-16 TAP
2. VARIES $+.00, -.06$
3. VARIES $+.000, -.001$
4. ON STANDARD MOTORS THIS IS CONDUIT SIZE. ON XT AND CORROSION PROOF MOTOR THIS IS PIPE TAP.
5. MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
6. OBSTRUCTION MUST NO ENCROACH ON AIR INLET.
7. AIR DEFLECTOR INSTALLED WHEN REQUIRED.

CONDUIT BOX LOCATED ON OPPOSITE SIDE WHEN F-2.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF
STANDARD SHAFT EXTENSION IS .08 MM T.I.R. TO 127 MM DIA.

[5] WEIGHT (KGS): 1140

DRIVE END AIR DEFLECTOR IS ONLY INCLUDED WHEN NECESSARY.

DIMENSIONS ARE IN MILLIMETERS; SEE SHEET 1 FOR DIMENSIONS IN INCHES

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

REV. DESC: NEW ISSUE			
REV: -	VERSION: 00	REVISED: 04/29/05 (02/09/2015)	TDR: 000000884510
MODEL NO. 617427-355		REF:	
BY: RAGGDM	Material:		

BALDOR

G447T/445T STD FOOTED SIDE/CENTER C/B WITH AIR DEFLECTOR

416820-036

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575-BA)

416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682		REVISED: 11: 54: 06 04/30/2010
MTL: -	BY: RAGRA	

BALDOR

CONN DIAG - STANDARD 3 LEAD
SH 1 of 1