

ABB BALDOR RELIANCE III

Customer information packet

ECR92504T-4

250HP, 1785RPM, 3PH, 60HZ, 449T, A44128M, TEFC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	449T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	250.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	15-60
Current @ Voltage	278.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	96.2 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	278.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	No Lifting Lugs
Max Speed	3600 rpm
Motor Lead Quantity/Wire Size	12 @ 2 AWG
Motor Standards	NEMA

Part Detail

Revision	J
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A44WG5111
Layout	617427-091
Eff. date	04-08-2021
CD Diagram	416820-036
Poles	04
Leads	3#2 (04 per group)
Proprietary	False
Created date	02-05-2015

Motor Type	A44128M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	53.24 IN
Power Factor	88
Product Family	Crusher / Chipper
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	3.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1785 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

000613007PV														
CAT NO	ECR92504T-4			SPEC NO.		P44G1815								
HP	250	AMPS		278	VOLTS		460		DESIGN	A				
RPM	1785	RPM MAX		3600	HZ	60	AMB	40	SF	1.15				
D.E. BRG.DATA	6318		O.D.E. BRG.DATA			6318		PH	3	DUTY	CONT		INSUL.CLASS	F
FRAME	449T	I.P.	55	TYPE	P	ENCL	TEFC	CODE	H					
POWER FACTOR	88	3/4 LOAD EFF.			96.1		NEMA NOM EFFICIENCY				96.2			
CHP HZ	60-90	CT HZ		15-60	VT HZ		6-60							
SER.NO.				MOTOR WEIGHT			2780							

NP2496L	
MOBIL POLYREX EM	


ABB BALDOR RELIANCE III S/O		CUSTOMER INFORMATION PACKET					ECR92504T-4 - 250HP, 1785RPM, 3PH, 60HZ, 449T, A44128M, TEFC				
		FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS				
		449T	250	P	3/60	1785	460				
AMPS		DUTY	AMB °C/ INSUL	S.F.	NEMA DESIGN	CODE LETTER	ENCLOSURE				
278		CONT	40/F	1.15	A	H	TEFC				
E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES. @25 °C OHMS (BETWEEN LINES)							
-	418143031HE	---	---	.0121							
PERFORMANCE											
LOAD	HP	AMPERES	RPM	% POWER FACTOR		% EFFICIENCY					
NO LOAD	0	70.0	1800	5.27		0					
1/4	62.5	96.7	1796	64.7		93.6					
2/4	125	148	1793	82.5		95.9					
3/4	187	210	1789	86.6		96.3					
4/4	250	278	1785	87.5		96.2					
5/4	312	348	1781	87.7		95.9					
SPEED TORQUE											
	RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES							
LOCKED ROTOR	0	249	1833	2030							
PULL UP	1450	191	1408	1351							
BREAKDOWN	1733	243	1785	913							
FULL LOAD	1785	100	736	278							
AMPERES SHOWN FOR 460 VOLT CONNECTION. IF OTHER CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.											
CALCULATED DATA XE MOTOR-NEMA NOM. EFF. 96.2 PCT.											
 A MEMBER OF THE ABB GROUP		DRAWN BY: <u>CD</u> CHECKED BY: <u>T. KELATI</u> APPROVED BY: <u>T. KELATI</u> DATE: <u>02/05/2015</u>		AC MOTOR PERFORMANCE DATA		A44WG5111-R001 DATE ISSUED 02/05/20					

FRAME 449T
HP 250
TYPE P
PHASE / HERTZ 3/60

CUSTOMER INFORMATION PACKET
RPM 1785
VOLTS 460
AMPS 278
DUTY CONT
AMB °C / INSUL 40/F

ECR92504T-4, 250HP, 1785RPM, 3PH, 60HZ, 460T, 449T, 250HP, TEFC
S.F. 1.15
NEMA DESIGN A
CODE LETTER H
ENCLOSURE TEFC
E/S -

ROTOR 418143031HE
TEST S.O. CALCULATED DATA
TEST DATE ---
STATOR RES. @ 25°C .0121
OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

FRAME 449T

RPM 1785

S.F. 1.15

ROTOR 418143031HE

HP 250

VOLTS 460

NEMA DESIGN A

TEST S.O. CALCULATED DATA

TYPE P

AMPS 278

CODE LETTER H

TEST DATE ---

PHASE / HERTZ 3/60

DUTY CONT


ENCLOSURE TEFC

STATOR RES. @ 25°C .0121

AMB °C / INSUL 40/F

E/S -

OHMS (BETWEEN LINES)



THERMAL LIMIT CURVE

AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION


ENCLOSURE: TOTALLY ENCLOSED

FRAME 449T ABOVE NEMA RATINGS

COOLING: FAN COOLED

MOUNTING: FOOT

INCLUDES 447T FRAME MOUNTING HOLES



1. GROUND HOLES QTY 1 1/2-13 TAP; QTY 1 3/8-16 TAP
2. VARIES +.01, -.05
3. VARIES +.000, -.001
4. ON STANDARD MOTORS THIS IS CONDUIT SIZE. ON XT AND CORROSION PROOF MOTOR THIS IS PIPE TAP.
5. MOTOR WEIGHTS MAY VARY BY 1.5% DEPENDING ON RATING.
6. OBSTRUCTION MUST NO ENCROACH ON AIR INLET

CONDUIT BOX LOCATED ON OPPOSITE SIDE WHEN F-2.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF
STANDARD SHAFT EXTENSION IS .003" T.I.R. TO 5 INCH DIA.

[5] WEIGHT (LBS): 3080

DRIVE END AIR DEFLECTOR IS ONLY INCLUDED WHEN NECESSARY.

DIMENSIONS ARE IN INCHES

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

 SHEET NUMBER
1 OF 2

1607-27-091

REV. DESC: ADD C DIMENSION			
REV: B	VERSION: 02	REVISED: 02-45-42 09/29/2015	TDR: 000000942902
MODEL NO. 617427-091			
BY: USBRCHA2			

BALDOR

G449/447T SIDE MOUNT C-BOX, TEFC

617427-091

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION


ENCLOSURE: TOTALLY ENCLOSED

FRAME 449T ABOVE NEMA RATINGS

COOLING: FAN COOLED

MOUNTING: FOOT

INCLUDES 449T FRAME MOUNTING HOLES



1. GROUND HOLES QTY 1 1/2-13 TAP; QTY 1 3/8-16 TAP
2. VARIES +.00,-1.524
3. VARIES +.000,-.0254
4. ON STANDARD MOTORS THIS IS CONDUIT SIZE. ON XT AND CORROSION PROOF MOTOR THIS IS PIPE TAP.
5. MOTOR WEIGHTS MAY VARY BY 1.5% DEPENDING ON RATING.
6. OBSTRUCTION MUST NO ENCROACH ON AIR INLET

CONDUIT BOX LOCATED ON OPPOSITE SIDE WHEN F-2.
IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF
STANDARD SHAFT EXTENSION IS .0762 T.I.R. TO 127 MM DIA.

5 MASS (KGS): 1395

DRIVE END AIR DEFLECTOR IS ONLY INCLUDED WHEN NECESSARY.

DIMENSIONS ARE IN MILLIMETERS, SEE SHEET 1 FOR DIMENSIONS IN INCHES

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

 SHEET NUMBER
2 OF 2

1607-27-091

REV. DESC: ADD C DIMENSION	REV. B	VERSION: 02	REVISED: 02-45-42 09/29/2015	TDR: 000000942902
MODEL NO. 617427-091	BY: USBRCHA2			


BALDOR

G449/447T SIDE MOUNT C-BOX, TEFC

617427-091

416820-036

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 3 LEAD CONNECTED



(N.P. 1575-BA)

416820-036

REV. DESC: LOADED TO BUS, C/R 335225		
REV. LTR: -	VERSION: 00	TDR: 000000538207
FILE: \MGA\00000\682	REVISED: 11: 54: 06 04/30/2010	
MTL: -	BY: RAGRA	

BALDOR

CONN DIAG - STANDARD 3 LEAD
SH 1 of 1