

ABB BALDOR RELIANCE III

Customer information packet

ECS101A3K1P5DD4

1.5KW, 1500RPM, 3PH, 50HZ, D90D, 3524B, TEFC, B

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	D90D
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Brushless Wound Field PM Rotor
Output @ Frequency	1.500 KW @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	380.0 V @ 50 HZ
Agency Approvals	CE CULUS UKCA WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	5
Current @ Voltage	2.360 A @ 380.0 V
Design Code	-
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	87.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Frame Prefix	D
Heater Indicator	No Heater
High Voltage Full Load Amps	2.4 a

Part Detail

Revision	B
Type	AC
Mech. spec.	35EE440
Base	
Status	PRD/A
Elec. spec.	35WGG963
Layout	35LYEE440
Eff. date	11-15-2024
CD Diagram	CD0006B03
Poles	04
Leads	3#16 13" LONG LEADS Y
Proprietary	False
Created date	04-30-2024

Insulation Class	F
Inverter Code	03
KVA Code	-
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	IEC
Motor Type	3524B
Mounting Arrangement	B5
Number of Poles	4
Overall Length	16.42 IN
Power Factor	95
Product Family	General Purpose
Pulley Face Code	D-Flange
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.945 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3968B01A01											
CAT.NO.	ECS101A3K1P5DD4										
SPEC.	35EE440G963					YR					
FRAME	D90D		IP		55	WT.		44			
KW	1.5	HZ		50		PH		3	DUTY-IPM		CONT
INS CL	F	CLASS RISE						AMB-C		40	
EFF. CL	IE5	EFF		87.7		COSØ			95		
VOLTS	380			FLA		2.36					
1/MIN	1500				1/MIN MAX				3000		
BEMF (V)	247				RS (OHMS)				11.7		
LD (MH)	78.9				LQ (MH)				406		
VPWM	CP =		50		TO		133				
CT	5	TO		50	VT		5	TO		50	
MATCHED INV	ECIN4A4P1										
DE	6205			ODE		6203					
SERIAL #											

NP3978A00					
PART NO.	ECIN4A4P1				
U1	400	PH	3	HZ	50
I1	2.9	W/EXT. CHOKE			2.7
SERIAL #					

Volts	380	Max RPM	4000	Conn Diag.	CD0006B03	Leads	3
Amps	2.2	Max Amps		Cs Diagram	CS1126	BEMF	296
KW	1.5	VFD#	ECIN4A44P1			LD	78.9
RPM	1500	S.F.	1.00			LQ	406
Phase/Hz	3/50	Rating	40C AMB-CONT			Rs	11.7387 Meas. L-L

60034-2-3 Motor Performance at Standardized Operating Points

	RPM	% Speed	LB-FT	% Torque	KW	Efficiency	Loss (% FL)	Watts Loss (W)
P1	1361	90%	7.0	100%	1.4	88.8	11.51%	173
P2	755	50%	7.0	100%	0.8	84.6	9.15%	137
P3	363	25%	7.0	100%	0.4	74.2	8.40%	126
P4	1358	90%	3.5	50%	0.7	91.2	4.40%	66
P5	755	50%	3.5	50%	0.4	87.8	3.50%	53
P6	755	50%	1.8	25%	0.2	89.4	1.51%	23
P7	363	25%	1.8	25%	0.1	84.3	1.13%	17

61800-9-2 PDS Performance at Reference Operating Points


	RPM	% Speed	LB-FT	% Torque	KW	System Efficiency	Loss (% FL)	Watts Loss (W)
P1	1511	100%	7.0	100%	1.5	85.4	17.18%	258
P2	755	50%	7.0	100%	0.8	81.3	11.59%	174
P3	245	17%	7.0	100%	0.2	61.1	10.37%	155
P4	1509	100%	3.5	50%	0.8	88.4	6.59%	99
P5	755	50%	3.5	50%	0.4	82.9	5.18%	78
P6	245	17%	3.5	50%	0.1	65.2	4.36%	65
P7	755	50%	1.8	25%	0.2	81.9	2.80%	42
P8	245	17%	1.8	25%	0.1	64.1	2.29%	34

Points not taken in certified order.

	DR By:	R & D	AC MOTOR PERFORMANCE CURVES	35WGG963 35E5209G963 Test - 111107
	CK By:	USTOSAN		
	APP By:	USJAROB1		
	Date:	08/08/2024		

Volts	380	Max RPM	4000	Conn Diag.	CD0006B03	Leads	3
Amps	2.2	Max Amps		Cs Diagram	CS1126	BEMF	296
KW	1.5	VFD #	ECIN4A44P1			LD	78.9
RPM	1500	S.F.	1.00			LQ	406
Phase/Hz	3/50	Rating	40C AMB-CONT			Rs	11.7387 Meas L-L

Constant Duty Operating Range


BALDOR • RELIANCE

DR By: R & D

CK By: USTOSAN

APP By: USJAROB1

Date: 08/08/2024
**AC MOTOR
PERFORMANCE
CURVES**
35WGG963

35E5209G963

Test - 111107

